

GCS92HU

2-Port 4K KVM Switch with HDMI, USB and Audio Connections



- One USB keyboard, mouse and one HDMI monitor control two HDMI computers
- Superior video quality – up to 4K DCI (4096 x 2160 @ 60Hz)
- Computer selection via remote port selector
- HDMI compliant; [HDCP 2.2](#) compliant
- Supports USB hot-plugging

2-Port 4K KVM Switch with HDMI Connection, USB and Audio

One of the most compact KVMs IOGEAR has to offer, the 2-Port 4K KVM Switch with HDMI Connection, USB and Audio is a must-have for users with two computers using one monitor, keyboard and mouse. It is perfect for a home office or small to medium-sized business that need to conserve workspace and streamline desktop setups.


4K Video

This 4K KVM supports up to 4096 x 2160 @60Hz resolution on large widescreen HDMI displays giving the user high-quality images on screen every time. It is perfect for users in the finance, medical, computer programming and graphics fields.

- One USB keyboard, mouse and one HDMI monitor control two HDMI computers
- Superior video quality – up to 4K DCI (4096 x 2160 @ 60Hz)
- Computer selection via remote port selector
- HDMI compliant; [HDCP 2.2](#) compliant
- Supports USB hot-plugging
- The console USB ports can be used for USB peripheral sharing
- Multiplatform support – Windows, Mac and Linux
- Plug and play
- Bus-powered – no external power adapter required¹

Note: 1. The GCS92HU may require an external power supply via the USB Micro-B Power Port. For the USB Micro-B cable connecting to the USB Micro-B Power Port, it requires a separate purchase based on the type of the power supply you use.





Requirements

Package Contents

Console

- HDMI monitor
- Standard 104-key wired USB keyboard
- Standard 2 or 3 button wired USB mouse
- Speakers and Microphones (optional)

- 1x GCS92HU 2-Port 4K KVM Switch with HDMI Connection, USB and Audio
- 1x Quick Start Guide
- 1x Warranty Card

Computers

- HDMI port
- USB Type-A port
- Audio ports (optional)

Operating Systems

- Windows[®]7, 8.1, 10+
- Mac OS X 9.0+
- Oracle[®] Solaris
- Linux[®], UNIX, and other USB supported systems

Specifications

Function	GCS92HU
Computer Connections	
Direct	2
Port Selection	Remote Pushbutton
Console Connectors	
Monitor	
Keyboard	1 x USB Type A
Mouse	1 x USB Type A
Audio	1 x 3.5mm Mini Stereo Jack (Green)
Microphone	1 x 3.5mm Mini Stereo Jack (Pink)
CPU Connectors	
Monitor	2 x HDMI
Keyboard & Mouse	2 x USB 2.0 Type A
Audio	2 x 3.5mm Mini Stereo Jack(Green)
Microphone	2 x 3.5mm Mini Stereo Jack(Pink)
LEDs	
KVM	2 x White
Video Resolution	up to 4096 x 2160 @60Hz
Environment	
Operation Temperature	0-50C (32-122 F)
Storage Temperature	-20-60C (-4-140F)
Humidity	0-80% RH, Non-condensing
Housing	
Case	Plastic
Cable Length	KVM cables: 48" (121.92cm)

Dimensions	GCS92HU
Unit Dimensions	
Height	1.06" (2.69cm)
Length	3.375" (8.57cm)
Depth	3.25" (8.27cm)
Unit Package Dimensions	
Height	8.875" (22.5cm)
Length	6.125" (15.56cm)
Depth	2.18" (5.54cm)
Master Carton	
Height	6.75" (17.15cm)
Length	15.25" (38.74cm)
Depth	8" (20.3cm)
Master Carton Qty.	6
Weight	
Master Carton Wt.	7.0 lb. (3.18kg)
Unit Pack Wt.	1.05 lb (0.48 kg)
Unit Wt.	0.8 lb (0.36 kg)