



5MP Day & Night Fixed IR Vandal Resistant Dome IP Camera



Features

- 5 megapixel CMOS image sensor
- 5MP H.265/HEVC and H.264/AVC high-performance video compression
- Simultaneous streaming of H.265 and H.264 encoded streams
- Smart H.264/H.265 supported
- 3D noise reduction (MCTF)
- 2D WDR function
- HDR function up to 120dB
- Digital PTZ supported
- IVS supported
- Tampering / Motion / Network lost detection event function
- SMART event
- High efficiency IR LED, radiant distance up to 30m
- Day & Night (IR cut removable)
- ONVIF Profile S and Profile T
- supported IP67 rain and dust resistant
- Vandal resistant approve

Specifications

Model	P2R6552E2
Min. illumination/Low Light Mode (Colour)	Color : 0.01 Lux at F1.6 ; B/W : 0.004 Lux at F1.6 ; 0 Lux with IR LED ON
Focal Length	2.8mm
Iris	F1.6
Iris Control	Fixed IRIS
Angle of View	92.8° (H) 68.8° (V) 116.5° (D)
Peak wavelength	850nm
Beam Spread	60° , 90°
Max IR distance	30M
Pick Up Element	1/2.8" CMOS image sensor
Effective pixels	2616 (H) × 1964 (V) = 5,137,824 (Pixels)
CE	Yes, EMI CLASS B
FCC	Yes, EMI CLASS B
IP Rating	IP67
Vandal Resistant Rating / IK Rating	IK10
CPU	Intel® Core™ i7 or higher grade
OS	Windows 7 or above
RAM	8GB or above, Dedicated Graphics Card
Web browser	Microsoft® Internet Explorer® 9 or above
Video Compression	H.265/HEVC main profile, H.264 main and high profile , Motion JPEG
Video streaming	RTP/HTTP, RTP/TCP, RTP/UDP, Multicast 4 configurable streams in H.265 and H.264 and Motion JPEG, configurable frame rate and bandwidth
Number of streams	4
Video bitrate	128Kbps – 12Mbps; Frame rate and bit rate controllable on-the-fly; VBR / CBR / GOP supported, Fixed bitrate, Smart H.264/H.265

Encryption	Base64 HTTP encryption, HTTPS encryption, DDNS via HTTPS
Authentication	Digest HTTP authentication, RTSP authentication, TLS, 802.1x, DDNS via HTTPS
Address Filter	IP address filter, MAC address filter
Access	Multiple user access levels with password protection
User accounts	10 user accounts available
Multi IP address	Yes
Resolution	5MP(2592 × 1944), 4MP(2304 × 1728), 3.1MP(2048 × 1536), 3MP(2304 × 1296), 2MP(1920 × 1080), 1.3MP(1280 × 960), 1MP(1280 × 720), D1(720 × 480, 720 × 576), VGA(640 × 480), CIF(352 × 240)
Maximum Frame Rate	Normal mode: up to 25 fps @ 2592 × 1944 HDR mode: up to 25 fps @ 2592 × 1944
Scanning System	Progressive Scan
Infrared Cut Filter	Auto / Day (Color) / Night (Mono) / Schedule
White Balance	ATW-NARROW / ATW-WIDE / AWC(MANUAL)
Back Light Compensation	Yes
Electrical Shutter	1/30(1/25)s – 1/30000s
Sense Up	Off / x2 / x4 / x8 / x16
Sense Up+	Yes
Auto Gain Control	60 dB Variable Gain
S / N Ratio	More than 50dB (AGC off)
3D Noise Reduction	Off / 1 – 32 Selectable
2D WDR	Off / Auto / x2 / x3 / x4 (by normal mode) Support Onvif
High Dynamic Range(HDR)	Up to 120dB (by HDR mode, 2 shutter line interleave)
Privacy Masking	Off / On (4 zones)
Image Effects	Brightness, Contrast, Hue, Saturation, Sharpness, Mirror, Flip, Rotation, Overexposure Reduction
EV (Exposure Value)	Adjustable

Lens distortion correction (LDC)	Yes
Mobile Application	Integrated to LILIN mobile app (LILIN Viewer) iPhone, iPad, Android support
Video Management	ONVIF Profile S / ONVIF Profile T / IVS events, LILIN Navigator Enterprise 2.0 support, Third party VMS through LILIN HTTP API
SD Card Compatible List	<p>Micron - 32GB,64GB,128GB,256GB,512GB, 1TB (SDXC, U1, C10)</p> <p>Transcend - 4GB SD,8GB SDHC,32GB SDHC C10,128GB SDXC C10</p> <p>SanDisk - 8GB SDHC, 32GB, 64GB, 128GB SDHC C10</p> <p>Kingston - 64GB SDXC C10</p>
Maintenance	Firmware update via HTTP and IP Scan; Firmware available at website
IVS Basic 1.0	Motion Detection, Tampering Detection, Advanced Motion Detection, Traffic Light Detection, Tripwire Detection, Object Counting
IVS Advanced 2.1 (Optional)	Unattended Object Detection, Missing Object Detection, Crowd Detection, Loitering Detection, Face Detection
IVS Advanced 2.2 (Optional)	Detection Zone for Car and Human
Alarm event triggers	Motion / Tamper / Network lost detection / SmartEvent
Alarm event actions	FTP / SMTP / HTTP post / SAMBA / SNMP Trap / Push Service notification
Languages	English, Traditional Chinese, Simplified Chinese, Spanish, Italian, Turkish, Russian, Korean, French, Arabic, Hungarian, Japanese
Network Interface/Ethernet	10/100 Mbps Base-T (Tx), RJ-45

ePTZ & Digital Zoom	Yes, ROI (Region of Interest)
OSD	Position configurable text overlay for date, time, camera ID, event status and watermark with customizable user demand data
CPU.Memory	Embedded SoC ARM Cortex-A9, 816MHz, 512MB DDR3L, 256MB flash memory
Network OS	Embedded Linux 3.10
Protocols	IPv4, IPv6, TCP, UDP, HTTP, HTTPS, SMTP, MQTT, QoS, SNMP V1/V2/V3, SNMP Trap and heart beat, NTP, DDNS, UPnP, FTP, ARP, DHCP, PPPoE, DNS, RTSP, RTCP, Telnet, ICMP, IGMP, ONVIF Profile S , ONVIF Profile T, SDDP, Bonjour , 802.1x, SSL/TLS
Max number of online users	10 simultaneous users
Video Display	LILIN Universal ActiveX , LILIN Java Applet
Watermark	BMP logo
Log	Event & operation log & IVS event log
Schedule	Support holiday list
Network Storage	NAS (Support SAMBA/CIFS)
Starting Temperature	-10°C - +50°C (14°F - 122°F)
Operating temperature	-40°C - +50°C (-40°F - 122°F)
Storage temperature	-25°C - +60°C (-13°F - 140°F)
Operating humidity	0% - 90% RH
Power Supply	DC12V ±10% / PoE (IEEE 802.3af compliant)
Power Consumption	DC12V, 7.2W / PoE, 9.5W
Dimensions	Ø115 × 91 mm
Weight	420g
Casing Material	Aluminum alloy