

Product data sheet

Specifications



EasyPDU, Metered-by-Outlet, ZeroU, 32A, 230V, (20) C13 & (4) C19

EPDU1132MBO

Overview

Lead time Usually in Stock

Main

Main Input Voltage	200 V 208 V 230 V
Main Output Voltage	230 V
Plug standard	IEC 60309 32 A 2P + E
Number of rack unit	0U
Cable length	3 m
Number of cables	1
Communication port protocol	SNMP
Provided equipment	Installation guide Safety guide Rack mounting brackets

Physical

Colour	Black
Height	1800 mm
Width	55 mm
Depth	56 mm
Net weight	7.12 kg
Mounting location	Side
Mounting preference	No preference
Mounting mode	Not rack-mountable
USB compatible	No
Mounting position	Vertical

Input

[In] rated current	32 A
Permissible voltage	200...240 V
Max line current	32 A

Input current limits	32 A
Load capacity	7360 VA
Network frequency	50/60 Hz
Plug standard	IEC 60309

Output

Number of power socket outlets	20 IEC 60320 C13 4 IEC 60320 C19
--------------------------------	-------------------------------------

Conformance

Product certifications	CE EAC TÜV RCM UKCA
------------------------	---------------------------------

Environmental

Ambient air temperature for operation	-5...45 °C
Relative humidity	5...95 %
Operating altitude	0...3000 m
Ambient air temperature for storage	-25...65 °C
Storage Relative Humidity	5...95 %
Storage altitude	0...15000 m

Batteries & Runtime

Communication network type	10/100BASE-T
----------------------------	--------------

Packing Units

Number of Units in Package 1	1
Package 1 Weight	8.29 kg
Package 1 Height	2030 mm
Package 1 width	195 mm
Package 1 Length	130 mm

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------