



## SPECIFICATIONS

Panel Size	27"
Panel Resolution	2560 x 1440 (WQHD)
Refresh Rate	240Hz
Response time	1ms (MPRT)
<b>DYNAMIC REFRESH RATE TECHNOLOGY</b>	FreeSync Premium Pro
Panel Type	VA
<b>Video interface</b>	1x DP(1.4) 2x HDMI (2.0) 1x USB Type-C (DisplayPort Alternate)
<b>Brightness (nits)</b>	400 nits (Typ.) 530 nits (HDR Peak)
<b>Viewing Angle</b>	178°(H) / 178°(V)
<b>Aspect Ratio</b>	16:9
<b>Audio interface</b>	1x Earphone out
<b>Contrast Ratio</b>	3000:1
<b>Pixel Pitch (H x V)</b>	0.2331 (V) x 0.2331 (V) mm
<b>Surface Treatment</b>	Anti-glare
<b>Display Colors</b>	1.07B(8bit + FRC)
<b>DCI-P3 / sRGB</b>	95% / 128%
<b>Video ports</b>	1x DP(1.2a) 2x HDMI(2.0b) 1x USB Type C (DP alt mode Type C with PD : 5V/3A) with USB 2.0 function
<b>USB ports</b>	2x USB2.0 Type A 1x USB2.0 Type B
<b>Audio ports</b>	1x Earphone out
<b>Active Display Area (mm)</b>	596.736(H) x 335.664 (V)
<b>Kensington Lock</b>	Yes
<b>VESA Mounting</b>	100 x 100 mm
<b>Power Type</b>	External Adaptor 20V 6A
<b>Power Input</b>	100~240V, 50~60Hz
<b>Signal Frequency</b>	91.2~386.2 KHz(H) / 48 ~240Hz(V)
<b>Adjustment (Tilt)</b>	-5° ~ 20°
<b>Adjustment (Swivel)</b>	-30° ~ 30°
<b>Adjustment (Height)</b>	0 ~ 100 mm
<b>Curved</b>	1000R
<b>Power consumption</b>	32 KWh/1000h

## FEATURES

- Curved Gaming™**  
View more of your game. MSI Curved Gaming™ monitors are perfect for gamers to play their games.
- 1000R - The Perfect Curve**  
Enjoy the most immersive gameplay with 1000R curvature rate.
- Gaming Intelligence**  
A new dawn of AI gaming, including Smart Brightness, Smart Crosshair, Night Vision AI, and Sound Tune.
- KVM**  
Control multiple devices via one set of keyboard, mouse, and MSI gaming monitor.
- Rapid Boost (240Hz + 1ms)**  
Experience smooth gaming with a blazing fast refresh rate that gives you the upperhand in fast moving games.
- QD Premium Color**  
QD Premium Color is the highest standard of gaming monitor. Quantum dot technology and Premium color mode provided most vivid color in gaming with industry leading color fidelity : Delta E ≤2.

<b>Adjustment (Pivot)</b>	NA
<b>Compatibility</b>	PC, Mac, PS5™, PS4™, Xbox, Mobile, Notebook * All trademarks and the registered trademarks are the property of their respective owners
<b>Carton Dimension (W X H X D)</b>	775 x 223 x 490 mm / 30.51 x 8.78 x 19.29 inch
<b>Weight (NW / GW)</b>	6.6 kg / 10.0 kg 14.55 lbs / 22.05 lbs
<b>Dimension (W x H x D)</b>	607.1 x 260.9 x 527.8 mm // 23.9 x 10.27 x 20.78 inch
<b>Frameless Design</b>	Yes
<b>HDR Support</b>	HDR 400
<b>Note</b>	Display Port: 2560 x 1440 (Up to 240Hz) HDMI: 2560 x 1440 (Up to 144Hz) Type C. 2560 x 1440(Up to 240Hz) *sRGB and DCI-P3 follow CIE1976 standard
<b>PIP / PBP Function</b>	Yes

## CONNECTIONS



1. Headset Hanger
2. Marco Key
3. 5-Way joystick navigator
4. Power Button
5. Power Jack
6. 1x HDMI w/CEC (2.0b)
7. 1x HDMI (2.0b)
8. 1x Display Port (1.2a)
9. 1x USB2.0 Type C
10. 1x Earphone out
11. 2x USB 2.0 Type A
12. 1x USB2.0 Type B Upstream Port
13. Kensington Lock