

## PERFORMANCE

### Processor

Intel® Core™ i7-12700H, 14C (6P + 8E) / 20T, P-core 2.3 / 4.7GHz, E-core 1.7 / 3.5GHz, 24MB

### Graphics

NVIDIA® GeForce RTX™ 3070 Ti 8GB GDDR6, Boost Clock 1485MHz, TGP 150W

### Chipset

Intel SoC Platform

### Memory

2x 16GB SO-DIMM DDR5-4800

### Memory Slots

Two DDR5 SO-DIMM slots, dual-channel capable

### Max Memory

Up to 32GB DDR5-4800 offering

### Storage

1TB SSD M.2 2280 PCIe® 4.0x4 NVMe®

### Storage Support

Up to two drives, 2x M.2 SSD

- M.2 2242 SSD up to 512GB
- M.2 2280 SSD up to 1TB

### Storage Slot

Two M.2 2280 PCIe Gen 4x4 slots, support M.2 2242/2280 SSD

### RAID Preset

None

### Card Reader

None

### Optical

None

### Audio Chip

High Definition (HD) Audio, Realtek® ALC3287 codec

### Speakers

Stereo speakers, 2W x2, Nahimic Audio

### Camera

HD 720p with E-camera Shutter

### Microphone

2x, Array

### Battery

Integrated 80Wh

### Max Battery Life

MobileMark® 2018: 4.01 hr (discrete mode) or 6.55 hr (hybrid mode)

### Power Adapter

300W Slim Tip (3-pin)

## DESIGN

### Display

16" WQXGA (2560x1600) IPS 500nits Anti-glare, 165Hz, 100% sRGB, Dolby® Vision™, HDR 400, G-SYNC®, DC dimmer, Low Blue Light, High Gaming Performance

### Touchscreen

None

### Color Calibration

Factory Color Calibration

### Keyboard

4-Zone RGB Backlit, English (US)

### Case Color

Storm Grey

### Surface Treatment

Anodizing

### Case Material

Aluminium (Top), Aluminium (Bottom)

### Dimensions (WxDxH)

359.9 x 264.4 x 19.9 mm (14.17 x 10.41 x 0.78 inches)

### Weight

Starting at 2.49 kg (5.49 lbs)

## SOFTWARE

### Operating System

Windows® 11 Home 64, English

### Bundled Software

Office Trial

## CONNECTIVITY

### Ethernet

100/1000M

### WLAN + Bluetooth®

Wi-Fi® 6E 11ax, 2x2 + BT5.1

### Standard Ports

- 2x USB 3.2 Gen 1
- 1x USB 3.2 Gen 1 (Always On)
- 1x USB-C® 3.2 Gen 2 (support data transfer and DisplayPort™ 1.4)
- 1x USB-C 3.2 Gen 2 (support data transfer, Power Delivery 135W and DisplayPort 1.4)
- 1x Thunderbolt™ 4 / USB4® 40Gbps (support data transfer and DisplayPort 1.4)
- 1x HDMI®, up to 8K/60Hz
- 1x Ethernet (RJ-45)
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Power connector

## SECURITY & PRIVACY

### Security Chip

Firmware TPM 2.0

### Fingerprint Reader

None

### Other Security

E-Camera shutter

## SERVICE

### Base Warranty

1-year, Depot

### Included Upgrade

None

## ACCESSORIES

### Bundled Accessories

None

## CERTIFICATIONS

### Green Certifications

- ErP Lot 3
- RoHS compliant

### Other Certifications

- TÜV Rheinland® High Gaming Performance (WQXGA display model only)
- TÜV Rheinland Low Blue Light (Hardware Solution)

## MODEL

**TopSeller** : No **Announce Date** : 2022-01-29

**EAN / UPC / JAN** : 196378964669 **End of Support** : 2028-02-10

· Lenovo reserves the right to change specifications or other product information without notice.  
· Battery life is an estimated maximum. Actual battery life may vary by hardware or system settings, active applications, battery conditioning, etc.  
· California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

## Premium Care - Advanced Support from Real People. Real Fast.



### REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



### REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



### HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



### PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



### Lenovo Powered USB-C Travel Hub

4X90S92381

Travel-Ready Productivity Powerhouse; One-stop travel docking is finally here. Connect and charge new and legacy devices wherever you happen to be. Sleek and compact, the Lenovo Powered USB-C Travel Hub fits unlimited...



### Lenovo USB-C 7-in-1 Hub

4X90V55523

Travel - Ready Productivity. One-stop travel docking is finally here. Connect and charge new and legacy devices wherever you happen to be. Sleek and compact, the Lenovo USB-C 7-in-1 Hub fits unlimited productivity i...

For a full list of accessories and services, please visit:  
<https://smartfind.Lenovo.com>

Lenovo

PSREF  
Product Specifications  
Reference