

- Male-to-male is not a standard USB cable configuration. It's used only in rare instances where a peripheral or patch bay employs a female connector instead of a USB-B port.
- This cable will not connect two PCs. File-sharing between computers requires special software-driven cables.

USB 3.2 Gen 1 SuperSpeed A/A Cable (M/M), Black, 6 ft. (1.83 m)

MODEL NUMBER: **U325X-006**



Connects a USB peripheral or patch bay to your computer, laptop or other USB-enabled device compatible with 5 Gbps speeds.

Features

USB Cable Connects USB Type-A Peripherals to Your Computer

This USB-A to USB-A cable is ideal for connecting external hard drives and other high-speed USB 3.2 Gen 1 peripherals to your computer, laptop or other compatible device, such as a Chromebook or Microsoft Surface.

Supports USB 3.2 Gen 1 Speeds for a Faster, More Efficient Signal

The U325X-006 supports USB 3.2 Gen 1 data transfer rates up to 5 Gbps—10 times faster than USB 2.0. Its bi-directional data interface allows data to flow both directions simultaneously, increasing theoretical bandwidth by 10 times for efficient power and little wait-time. The U325X-006 is also backward compatible with previous USB generations, so you can continue to use legacy USB 2.0 and USB 1.1 peripherals.

Filtering EMI/RFI Line Noise and Eliminating Cable Strain Help Your Equipment Perform Better

Foil and braid shielding blocks disruptive EMI (electromagnetic interference) and RFI (radio frequency interference) line noise that can disturb your electronics and inflict hardware damage or data loss. Twisted pair construction reduces crosstalk, which helps your connected components perform better and last longer. Integral strain relief gives the U325X-006 extra flexibility, reduces stress and helps the cable move freely without cracking or breaking loose from the connector.

Highlights

- Supports USB 3.2 Gen 1 speeds up to 5 Gbps to ensure fast data transfers
- Backward compatible with legacy USB 2.0 and USB 1.1 peripherals
- Foil/braid shielding protects against EMI/RFI line noise that can distort or destroy data
- Integral strain relief helps cable move freely without stress or cracking
- Plug-and-play operation with no drivers required for easy, immediate installation

Package Includes

- U325X-006 USB-A Cable (M/M), USB 3.2 Gen 1, Black, 6 ft. (1.8 m)

Specifications

| OVERVIEW | |
|------------|--------------|
| UPC Code | 037332274595 |
| Technology | USB; USB 3.x |



| | |
|--------------------------------------|-------------------------------|
| Host Connector | USB A (MALE) |
| USB Cable Type | Passive |
| PHYSICAL | |
| Material of Construction | PVC |
| Color | Black |
| Cable Jacket Color | Black |
| Connector Color | Black |
| Cable Jacket Material | PVC |
| Cable Jacket Rating | VW-1 |
| Cable Outer Diameter (OD) | 5.5mm |
| Cable Length (ft.) | 6 |
| Cable Length (m) | 1.83 |
| Cable Length (in.) | 72 |
| Unit Packaging Type | Polybag |
| ENVIRONMENTAL | |
| Operating Temperature Range | 32 TO 122 F (0 TO 50 C) |
| Storage Temperature Range | -4 TO 140 F (-20 TO 60 C) |
| Operating Humidity Range | 10% TO 90% RH, Non-Condensing |
| Storage Humidity Range | 10% TO 90% RH, Non-Condensing |
| CONNECTIONS | |
| Side A - Connector 1 | USB A (MALE) |
| Side B - Connector 1 | USB A (MALE) |
| Connector Plating | Nickel |
| Contact Plating | Gold |
| FEATURES & SPECIFICATIONS | |
| USB Specification | USB 3.2 Gen 1 (up to 5 Gbps) |
| STANDARDS & COMPLIANCE | |
| Product Compliance | RoHS; REACH |
| WARRANTY | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>