

Key Features

True 4K Ultra HD Resolution | Cinema SuperColor™ Technology | Ultra-Short Throw Projection | Long-lasting Laser Phosphor Light Source | Harman Kardon Sound with Dolby/DTS Support



Product Description

Combining stunning true 4K resolution with Wi-Fi-enabled streaming functionality, the ViewSonic® X2000B-4K smart laser projector delivers a cinematic experience with the ease and convenience of ultra-short throw projection. With a 0.22 ultra-short throw lens, this laser projector can be placed just a few inches away from a wall or screen, and project an immersive image up to 100". Setup is a breeze too; no matter how your home theater is configured, this projector delivers immersive images on flat screens, curved walls, and everything in between thanks to its flexible 4-corner adjustment capabilities. Whether simply placed on a media stand or mounted to the ceiling, this projector delivers vivid and razor-sharp images thanks to HDR/HLG support, Rec. 709 compatibility, and stunning true 4K Ultra HD 3840 x 2160 resolution. Dual integrated Harman Kardon customized speakers deliver room-filling audio for an immersive home theater experience. Embedded Wi-Fi connectivity enables screen mirroring directly from smart devices to the big screen, making content streaming easier than ever. Built with 2nd generation laser phosphor technology, the X2000B-4K is geared for instant entertainment and ready deliver up to 20,000 hours of stunning home entertainment.



01

02

03

04

05

06

07

08

09

10

1. Projection Lens

2. Power Button

3. Internal Speaker

4. USB 2.0 Type-A (x2)

5. Zoom Ring

6. AC In

7. LAN

8. AV In

9. Audio Out

10. HDMI (x2)



3840 x 2160
RESOLUTION



2,000 ANSI
LUMENS



0.22
THROW RATIO

Contact Sales

call: 888.881.8781

email: salesinfo@viewsonic.com

visit: viewsonic.com

Display:

Type:	DLP Laser
Resolution Type:	4K (3840x2160)
Resolution:	3840 x 2160
Brightness (Lumens):	2,000 ANSI
Display Size (in.):	65-150
Throw Distance:	0.082m-0.520m (100" @ 0.234m)
Throw Ratio:	0.22
Offset:	140% +/-5%
Lens:	Fixed Zoom
Light Source (watt):	Laser Phosphor system
Light Source Life, Normal (hours):	20000
Color Depth:	1.07 Billion Colors
Dynamic Contrast Ratio:	3,000,000:1
Aspect Ratio:	16:9

Video Signal:

Frequency Horizontal:	15K-135KHz
Frequency Vertical:	23-120Hz

Compatibility:

PC Resolution (max):	3840 x 2160
Mac® Resolution (max):	3840 x 2160

Connector:

USB 2.0 Type A(1), 3.5mm Audio Out(1), Audio-out (HDMI ARC)(1), HDMI 2.0 (with HDCP 2.2)(2), Wifi(5Gn), Bluetooth Audio-in(1 (BT4.2)), Bluetooth Audio-out(1 (BT4.2))

Audio:

Internal Speakers:	25W Cube x2 (10W tweeter + 15W woofer) (x2)
--------------------	---

Power:

Voltage:	100-120V+/- 10%, 50/60Hz
Consumption (typical):	250W
Stand-by:	<0.5

Controls:

Physical Controls:	Keypad, Power key
On Screen Display:	Display, Image, Power Management, Basic, Advanced, System, Information (See user guide for full OSD functionality)

Operating Conditions:

Temperature:	32-104° F (0 - 40° C)
--------------	-----------------------

Additional Hardware:

Kensington Lock Slot:	1
-----------------------	---

Weight (imperial):

Net (lbs):	15.0
Net Without Stand (lbs):	21.8

Weight (metric):

Net (kg):	6.8
Gross (kg):	9.9

Dimensions (imperial) (WxHxD):

Packaging (in.):	17.8 x 13.0 x 3.9
Physical (in.):	22.7 x 19.2 x 7.4

Dimensions (metric) (WxHxD):

Packaging (mm):	451.0 x 332.0 x 100.0
Physical (mm):	577.0 x 488.0 x 187.0

General:

Regulations:	cTUVus
PACKAGE CONTENTS:	X2000B-4K projector, power cable, remote control, Quick Start Guide
Warranty:	Three-year limited warranty on parts and labor, 1-year limited warranty on the light source, 1st year free Express Exchange* service. (One year Express Exchange Service requires product registration).
Recycle/Disposal:	Please dispose of in accordance with local, state or federal laws.
UPC:	766907016116

Copyright © ViewSonic Corporation 2000-2022. All rights reserved. (05/16/2022 02:51 AM PST)