

Product data sheet

Specifications



APC Smart-UPS 750VA 120V SHIPBOARD

SMT750X93

Main

Main Input Voltage	120 V
Main Output Voltage	120 V
Kw Rating	500 W
Rated power in VA	750 VA
Input Connection Type	NEMA 5-15P
Nb of power socket outlets	6 NEMA 5-15R
Number of cables	1
Battery Type	Lead-Acid battery
Provided equipment	User Manual

General

Product web sub-family	TAA compliance
Redundant	No

Physical

Height	6.34 in (161 mm)
Width	5.43 in (138 mm)
Depth	14.53 in (369 mm)
Net Weight	27.56 lb(US) (12.5 kg)
Mounting Location	Front
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Two post mountable	0
USB compatible	Yes

Input

Efficiency at full load	82...144 V 120 V
Input Frequency	50/60 Hz +/- 3 Hz

Output

Harmonic distortion	Less than 5%
Maximum configurable power in VA	750 VA
Max Configurable Power (Watts)	500 W
Transfer Time	6ms typical : 10ms maximum
Topology	Line Interactive
Waveform Type	Sine wave
Full load runtime	00:05:00
Half load runtime	00:15:00
Output frequency	50/60 Hz +/- 3 Hz for 60 Hz nominal sync to mains

Conformance

Product Certifications	CSA C22.2 No 107.1
Marking	UL
Standards	FCC Part 15 class A

Environmental

Acoustic level	41 dBA
Heat dissipation	90 Btu/h
Operating altitude	0...9842.52 ft (0...3000 m)
Ambient air temperature for operation	32...104 °F (0...40 °C)
Ambient Air Temperature for Storage	-4...131 °F (-20...55 °C)
Storage altitude	0.00...49212.60 ft (0...15000 m)
Relative Humidity	0...95 %
Storage Relative Humidity	0...95 %

Batteries & Runtime

Extendable Run Time	0
Included Battery Modules	0
Battery Slots Empty	0
Typical recharge time	3 h
RBC Quantity	1
Battery life	3...5 year(s)
Battery power in VAh	172 VAh runtime
Battery Charge Power (Watts)	15 W rated

Communications & Management

Audible Alarm	Alarm on 25 alarm conditions
Control panel	LED status display with load and battery bar-graphs and On Line : On Battery : Replace Battery : and Overload Indicators
Free slots	0

Surge Protection and Filtering

Surge energy rating	593 J
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : m

Ordering and shipping details

GTIN	731304433637
Package weight(Lbs)	30.91 lb(US) (14.02 kg)

Packing Units

Package 1 Height	11.85 in (30.1 cm)
Package 1 width	10.94 in (27.8 cm)
Package 1 Length	19.65 in (49.9 cm)

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery
----------	---