

ThinkVision P27u-20 62F1RAR6US

Product

ThinkVision P27u-20

Machine Type

62F1

Region

LA, NA

Display Size

27"

View Area

596.7x335.7 mm

Panel

In-Plane Switching

Aspect Ratio

16:9

Resolution

3840x2160

Pixel Pitch

0.1554x0.1554 mm

Dot / Pixel Per Inch

163 dpi

View Angle (H / V)

178 / 178

Response Time

4 ms (Extreme mode) / 6 ms (Typical mode)

Color Support

1.07 Billion

Refresh Rate

60 Hz

Brightness

450 nits

Contrast Ratio

1000:1

Color Gamut

99.5% Adobe RGB, 99.1% DCI-P3, 100% sRGB, 100% BT.709, 83.7% BT.2020

Curvature

None

Anti-glare

Yes

Video Connector

1x HDMI 2.0, 1x DP 1.2, 1x Thunderbolt 4 In, 1x Thunderbolt 4 Out

USB Port

3x USB 3.2 Gen 1 (1x BC 1.2), 1 x USB Type-C (Data & Power Delivery)

Camera

ThinkVision MC 50 monitor webcam

Microphone

None

Speakers

2x 3W, Optional soundbar support

Power Consumption (Typical / Maximum)

35W / 240W

Power Adapter

Integrated

Stand

Tilt, Swivel, Pivot, Height Adjust Stand

Color

Raven Black

Side Bezel Width

2 mm

Dimensions with Stand (HxWxD)

556.4x613.8x219.9 mm / 21.90x24.16x8.66 inches

Weight (Including Stand)

8 kg / 17.6 lbs.

Cables Included

DP cable for NA & Brazil only, USB Type-C to Type-A cable, Thunderbolt 4 cable

Environmental Certification

Energy Star Certified, TCO 9.0, EPEAT Gold, RoHS

Ergonomic Certification

TÜV Rheinland Eye Comfort

Base Warranty

3-year

Operating System Support

Support Windows 7, Windows 10

Sync Technology

None

Tiny Support / CPU / Platform

Tiny Support, Nano Support / None / None

Ethernet / Bluetooth / Wireless

Ethernet (10M/100M/1000M) / None / None

Touch Screen / Digitizer Pen / Battery

None / None / None

Display Ram / Storage / Card Slot

None / None / None

EAN / UPC / JAN

0196119196885 / 196119196885 / None

Announce Date

2021-10-29

 WWW.LENOVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product specifications Reference.

© Lenovo, 2022. All rights reserved.



Lenovo™

ThinkVision P27u-20

DISPLAY

Panel Size
27-inch

Screen Dimensions (W x H, mm)
608.8 mm x 355.3 mm

Panel Type
3-side NearEdgeless
In-Plane Switching

Active Area
596.7 mm x 335.7 mm

Backlight
WLED

Aspect Ratio
16:9

Resolution
3840 x 2160

Pixel Pitch
0.1554 mm x 0.1554 mm

Dot/Pixel Per Inch (DPI/PPI)
163

Viewing Angle (H x V @ CR 10:1)
178° / 178°

Response Time
4ms (Extreme Mode),
6ms (Normal Mode)

Refresh Rate
60 Hz

Brightness (Typical)
400 cd/m²

Brightness (Peak)
450 cd/m²

Contrast Ratio (Typical)
1000:1

Dynamic Contrast Ratio (Typical)
3M:1

Color Gamut
99.5% Adobe RGB (CIE 1931)
99.1% DCI-P3 (CIE 1976)
100% sRGB (CIE 1976)
100% BT.709 (CIE 1976)
83.7% BT.2020 (CIE 1976)

Color Support (Typical)
1.07 Billion

Color Depth
10-bit (8+FRC)

HDR Compliance
Yes (DisplayHDR™ 400)

Anti-glare
Yes

CONNECTIVITY

Video Signal
1 x Thunderbolt™ 4 In
1 x Thunderbolt™ 4 Out
2 x HDMI 2.0
1 x DP 1.2

Audio Signal
1 x Audio Out (3.5 mm)

USB Hub
Yes

Ethernet
Yes (10M/100M/1000M)

USB Upstream
2 x USB3.2 Gen1¹ (1 by USB Type-B,
1 by Thunderbolt™ 4)

USB Downstream
3 x USB3.1 Gen1¹
1 x USB Type-C (Data & Power Delivery)

MULTI-MEDIA

Integrated Speakers
Yes (2 x 3W)

Optional Soundbar Support
Yes (PN number: OA36190)

SPECIAL FEATURES

Factory Calibration
Yes (Avg. Delta E < 1)

KVM Switch
Yes

Software

Lenovo ThinkColour (Lenovo Display Control Center)²

Smart Sensor
Yes (Smart Light)

Others
Shading Hood³

POWER

Power Consumption (Typ. / Max.)
35W / 240W

Power Consumption Sleep/Off Mode
<0.5W

Power Consumption Switch-off Mode
<0.3W

ENERGY STAR Power Consumption (Pon/EETEC)
26W / 97kWh

Power Supply
Internal

USB Type-C Power Delivery (W)
Up to 27W⁴

TBT Power Delivery (W)
Yes (Up to 100W)

Smart Power
Yes

Voltage Required
AC 100 to 240 V (50-60 Hz)

MECHANICAL

Tilt Angle (Front / Back)
-5° / 35°

Swivel Angle (Left / Right)
-45° / 45°

Lift (Max. Range)
135 mm

Pivot
-90° / 90°

VESA Mount Capability
Yes (100 x 100 mm)

ThinkCentre M Series Tiny Support

Yes, by Tiny Monitor Clamp II (PN: 4XHOZ42451)³ & Tiny VESA Mount II (PN: 4XFON03161)³

ThinkCentre M Series Nano Support

Yes, by Nano Monitor Clamp II (PN: 4XHOZ42451)³ & Nano VESA Mount (PN: 4XFOV81630)³

Kensington Lock Slot
Yes

Cable Management
Yes

Bezel Color
Raven Black

Bezel Width (Side)
2.0 mm

Bezel Width (Top / Bottom)
2.0 / 23.6 mm

DIMENSIONS

Size Packed (D x H x W) (mm/inch)
187.0 x 510.0 x 732.0 mm
7.36 x 20.08 x 28.82 inches

Size Unpacked w/ Stand (D x H x W) (mm/inch) (Lowest Position)
219.9 x 421.4 x 613.8 mm
8.66 x 16.59 x 24.16 inches

Size Unpacked w/ Stand (D x H x W) (mm/inch) (Highest Position)
219.9 x 556.4 x 613.8 mm
8.66 x 21.90 x 24.16 inches

Size Unpacked w/o Stand (Head Only) (D x H x W) (mm/inch)
52.9 x 368.8 x 613.8 mm
2.08 x 14.52 x 24.16 inches

Weight Packed (kg / lbs.)
12.8 kg / 28.1 lbs.

Weight Unpacked (kg / lbs.)
8.0 kg / 17.6 lbs.

Weight (Monitor Head Only) (kg / lbs.)
5.4 kg / 11.9 lbs.

WHAT'S IN THE BOX

Monitor with stand
1 x Power cable (1.8m)
1 x DP cable (1.8m) for US & Canada only⁵
1 x HDMI cable (1.8m) for PRC SA only⁵
1 x USB Type-B to Type-A cable (1.8m)⁵
1 x Thunderbolt™ 4 cable (1.0m, 40 Gbps)
Factory calibration report
Quick setup guide

CERTIFICATION

ENERGY STAR Certification
Yes

CCC
Yes

TCO
9.0

EPEAT
Gold

RoHS (EU 2011/65/EU)
Yes

Windows Certification
Windows 7, Windows 10

China Energy Efficiency Standard
Tier 1

TÜV Rheinland Eye Comfort
Yes



¹ Depending on many factors such as the processing capability of peripheral devices, file attributes, and other factors related to system configuration and operating environments, the actual transfer rate using the various USB connectors on this device will vary and is typically slower than the data rates as defined by the respective USB specifications: 5 Gbit/s for USB 3.2 Gen 1; 10 Gbit/s for USB 3.2 Gen 2 & 20 Gbit/s for USB 3.2 Gen2x2.

² This software can only be used with Windows 10.

³ Sold separately.

⁴ Listed as maximum capacity of power delivery. Actual capacity of power delivery may vary depending upon devices connected or monitor configuration, and may decline with downstream USB ports connected or higher brightness setting.

⁵ Optional.

ThinkVision P27u-20

