

## **Key Features**

- 165Hz refresh rate for smooth gameplay
- 1ms (MPRT) response time for precision
- FreeSync Premium prevents screen tearing
- Full HD resolution for high detail
- 1500R curved screen for immersion



## **Product Description**

The ViewSonic VX2418C features a crisp Full HD display paired with a hyper-responsive 165Hz refresh rate for smooth gaming. The 1500R screen curvature provides a truly immersive viewing experience that lets you enjoy big, bold and stunning panoramic views. The 165Hz refresh rate loads more frames for sleek gameplay with less lag. A 1ms response time ensures your reactions are as fast as the game, helping you to claim more victories. FreeSync Premium virtually eliminates screen tearing and stuttering for the smoothest gaming experience possible.

Visit Us

www.viewsonic.com

1 of 2 11/23/2022, 4:59 PM

DISPLAY INPUT SIGNAL

HDMI (v1.4): 30 ~ 160KHz, DisplayPort (v1.2): 30 ~ 160KHz Display Size (in.): 24 Frequency Horizontal: 23.6

Viewable Area (in.): HDMI (v1.4): 48  $\sim$  144Hz, DisplayPort (v1.2): 48  $\sim$  165Hz Frequency Vertical: Panel Type: VA Technology

Resolution: 1920 x 1080 VIDEO INPUT

Resolution Type: TMDS - HDMI (v1.4), PCI-E -FHD (Full HD) Digital Sync: DisplayPort (v1.2)

Static Contrast Ratio: 3,000:1 (typ) **ERGONOMICS** 

Dynamic Contrast Ratio: 80M:1 Tilt (Forward/Back): -5° / 20° Light Source: LED

WEIGHT (IMPERIAL) Brightness: 250 cd/m² (typ) Net (lbs): 6.8

16.7M Colors: Net Without Stand (lbs): 5.7 Color Space Support: 8 bit (6 bit + FRC)

Gross (lbs): 9.7 Aspect Ratio: 16:9 WEIGHT (METRIC)

Response Time (MPRT): 1ms 3.1 Net (kg): Viewing Angles: 178° horizontal, 178° vertical Net Without Stand (kg): 2.6

Backlight Life (Hours): 30000 Hrs (Min) Gross (kg): 4.4 Curvature 1500R DIMENSIONS (IMPERIAL) (WXHXD) Refresh Rate (Hz): 165 Packaging (in.): 23.8 x 15.8 x 5.4

Adaptive Sync FreeSync Physical (in.): 21.3 x 16.3 x 8.2

Blue Light Filter: Yes Physical Without Stand (in.): 21.3 x 12.7 x 2.9 Flicker-Free: Yes DIMENSIONS (METRIC) (WXHXD)

NTSC: 72% size (Typ) sRGB: 102% size (Typ) Packaging (mm): 605 x 402 x 136 Color Gamut: Physical (mm): 540 x 413 x 209

Pixel Size: 0.272 mm (H) x 0.272 mm (V) Physical Without Stand (mm): 540 x 322 x 74 Anti-Glare, Hard Coating (3H) Surface Treatment:

COMPATIBILITY cTUVus, FCC-B, ICES003, CEC, NOM, Mexico Energy, CE, CE EMC, CB, RoHS, ErP, REACH, WEEE, EAC, UkrSEPRO, UKCA, BSMI 1920x1080 PC Resolution (max): Regulations:

GENERAL

1920x1080 Mac® Resolution (max):

VX2418C x1, 3-pin Plug (IEC C13 / CEE22) x1, DisplayPort Cable (v1.2; Male-Male) x1, AC/DC Adapter x1, Quick Start Guide x1 Windows 10/11 certified; macOS PC Operating System: PACKAGE CONTENTS:

Mac® Resolution (min): 1920x1080

CONNECTOR Please dispose of in accordance with local, state or federal laws. Recycle/Disposal: 3.5mm Audio Out:

\*Warranty offered may differ from market to market HDMI 1.4: 2 Warranty:

DisplayPort:

Power in: DC Socket (Center Positive)

**AUDIO** 

Eco Mode (Conserve): 15W Eco Mode (optimized): 19W Consumption (typical): 23W

25W Consumption (max): Voltage: AC 100-240V Stand-by: 0.5W

Power Supply: External Power Adaptor

ADDITIONAL HARDWARE Kensington Lock Slot:

CONTROLS Physical Controls: U, R, D, L, EN (power)

Input Select, Audio Adjust, ViewMode,

2Watts x2

Color Adjust, Manual Image Adjust, Setup Menu On Screen Display:

**OPERATING CONDITIONS** 

32°F to 104°F (0°C to 40°C) Temperature:

20% to 90% Humidity (non-condensing):

WALL MOUNT

Internal Speakers:

**POWER** 

100 x 100 mm VESA Compatible:

Copyright © ViewSonic Corporation 2000-2022, All rights reserved.