



Google Cloud
Partner

Taking Performance, Speed and Connectivity to a Whole New Level

The CTL Chromebook NL72 Series



The CTL NL72 Series is a “jack of all trades”. You can choose from 4 or 8 GB of RAM, 32 or 64 GB of storage, touch or non-touch, clamshell or tablet, and with or without a US1 pen. If you can't find the right model for you, it doesn't exist.



A True Workhorse

An Intel® Jasper Lake processor and up to 8GB memory and 64GB of storage give the Chromebook enough power to get important work done.




Flat-Out Better

A 180-degree lay-flat hinge offers flexible user interaction and reduces the chance of a broken hinge.



Faster and Smarter

Wi-Fi 6 ensures the fastest internet connection for multiple devices on the same network and Bluetooth 5.2 makes connecting to peripherals faster and easier.



Experience More

A unique 360° rotating camera enables flexible video creation and collaboration (NL72 Models only)



A Handy Solution

An integrated carry handle makes it easy to tote the device anywhere and reduces the chance of drops



Double Duty

USB-C ports are located on BOTH sides of the Chromebook for efficient data transfer, power delivery, and charging options

CTL Chromebook NL72 Series Awards and Recognition



The CTL Advantage

We build award-winning Chrome OS solutions backed by frictionless service and support. Our Chromebook and Cloud Computing Solutions support EdTech and Enterprise teams in over fifty countries across the globe.



Google Cloud
Partner

The CTL Chromebook NL72 Series

Versatile. Powerful. Dependable.

The CTL Chromebook NL72 Series features the latest in performance, speed, and connectivity.

Play All the Angles.
Rotating camera allows for 360° views.

Student Proof.
Spill and Drop Resistant with Anti-Peel Keys

Work and Play All Day.
Long Life Battery.

Peace of Mind.
Award-Winning Reliability and Performance with Long Google Life 2030 AUE.

Better. Faster. Stronger.
Intel® Jasper Lake Platform has 35% better overall application performance and 78% better graphics performance than previous generations.

Seeing is Believing.
HD 1366 x768 display.

An Added Touch of Protection
10-Point Multitouch Technology with 7H Hardened, Anti-Break Screen (NL72T, NL72TW, and NL72CT models only).

Retractable Carrying Handle

	NL72 4/64	NL72 8/64	NL72CT 4/64	NL72T	NL72TW
Display Size	11.6"	11.6"	11.6"	11.6"	11.6"
Resolution	1366x768	1366x768	1366x768	1366x768	1366x768
Platform	Jasper Lake	Jasper Lake	Jasper Lake	Jasper Lake	Jasper Lake
CPU	Intel N4500	Intel N5100	Intel N5100	Intel N4500	Intel N5100
CPU Specs	Dual Core, up to 2.8GHz	Quad Core, up to 2.8GHz	Quad Core, up to 2.8GHz	Dual Core, up to 2.8GHz	Quad Core, up to 2.8GHz
RAM	4 GB LPDDR4	8 GB LPDDR4	4 GB LPDDR4	4 GB LPDDR4	8 GB LPDDR4
Storage	64 GB eMMC	64 GB eMMC	64 GB eMMC	64 GB eMMC	64 GB eMMC
Camera	HD 720P	HD 720P	HD 720P	HD 720P	HD 720P
Wi-Fi	6 (Intel AX201)	6 (Intel AX201)	6 (Intel AX201)	6 (Intel AX201)	6 (Intel AX201)
Hinge	180°	180°	180°	360°	360°
Touch	Non-Touch	Non-Touch	Touch	Touch	Touch
USB 3.1 Ports	2	2	2	2	2
USB-C Ports	2	2	2	2	2
Weight (lbs.)	2.8	2.8	3.15	3.15	3.15
AUE	June 2030	June 2030	June 2030	June 2030	June 2030
SKU	CBUS1100016	CBUS1100015	CBUS1100021	CBUS1100017	CBUS1100011