

Manufacturer Part #	RaiderGE7712082
OS	Windows 11 Pro
CPU	Core i9-12900HX 8+8Core
CPU Speed	1.5-5.0 GHz
Color	Dark Grey
Screen Size	17.3" QHD, Anti-Glare Wide View Angle 240Hz 3ms DCI-P3 100%
Resolution	2560x1440 (16:9)
GPU	NVIDIA® GeForce RTX™ 3080 TI Laptop GPU Up to 1640MHz Boost Clock, 175W Maximum Graphics Power with Dynamic Boost. Max 250W CPU-GPU Power with MSI OverBoost Technology. *May vary by scenario.
Video Memory	16G GDDR6
Keyboard	SteelSeries per-Key RGB with Anti-Ghost key (102 Key)
Speaker	Sound by Dynaudio, 2x1W Speaker, 2x2W Duo Wave Woofer
Memory	32GB (16GB*2) DDR5 4800MHz
HDD Capacity	1TB NVMe SSD Gen4x4
HDD Interface	NVMe
LAN	Killer E3100G
WLAN	Killer WiFi 6E AX1675 (2x2 )
Bluetooth	BT 5.2
Card Reader	SD7.0
Webcam	1080p FHD Webcam
USB	1x USB3.2 Gen 2; 2x USB3.2 Gen 1
Type-C Port	1x Thunderbolt™ 4; 1x USB 3.2 Gen 2/DP
Video Port	1x HDMI (8K @ 60Hz / 4K @ 120Hz)
Audio Port	1 Audio Combo (1/8")
AC Power Adaptor	330W
Battery Pack	4 cell (99.9Whr)
Dimension	15.63"x 11.18"x 1.02"
Weight	6.39 lbs
Manufacturer Warranty	1 year Limited warranty (Include 1 Year Global)
Accessories	With MSI Dual Drive 128GB+MSI Lucky Figure Keychain + M99 mouse + backpack