

| | |
|-----------------------|--|
| Manufacturer Part # | CProX17059 |
| OS | Windows 11 Pro |
| CPU | Core i9-12900HX 8+8Core |
| CPU Speed | 1.5-5.0 GHz |
| Color | Black |
| Screen Size | 17.3" UHD, Anti-Glare Wide View Angle 4K 120Hz Thin Bezel, 100% DCI-P3 |
| Resolution | 3840x2160 (16:9) |
| GPU | NVIDIA RTX™ A3000 Up to 1640MHz Boost Clock, 175W Maximum Graphics Power with Dynamic Boost. Max. 230W CPU-GPU Power with MSI OverBoost Technology. *May vary by scenario. |
| Video Memory | 12GB GDDR6 |
| Keyboard | Per-key RGB Keyboard (99 key) |
| Speaker | Sound by Dynaudio, 2x2W Speaker |
| Memory | 32GB (16GB*2) DDR5 |
| HDD Capacity | 1TB NVMe SSD Gen4x4 |
| HDD Interface | NVMe |
| LAN | Killer E3100G |
| WLAN | Killer WiFi 6E AX1675 (2x2) |
| Bluetooth | BT 5.2 |
| Webcam | 1080p FHD Webcam |
| USB | 3x USB3.2 Gen 2 |
| Type-C Port | 2x Thunderbolt™ 4 |
| Video Port | 1x HDMI (8K @ 60Hz / 4K @ 120Hz); 1x Mini-DisplayPort |
| Audio Port | Mic-in/Headphone-out Combo |
| AC Power Adaptor | 330W |
| Battery Pack | 4 cell (99.9Whr) |
| Dimension | 15.63"x 12.99"x 0.91" |
| Weight | 6.82 lbs |
| Manufacturer Warranty | 3 year Limited warranty (Include 1 Year Global) + 3 year onsite warranty |
| Accessories | With MSI Dual Drive 128GB+MSI Lucky Figure Keychain + Bluetooth mouse |