ThinkVision T27i-30 63A4MAR1US

Product

ThinkVision T27i-30

Machine Type

63A4

Region

LA, NA

Display Size

27"

View Area

596.7×336.31 mm

Panel

In-Plane Switching

Aspect Ratio

16:9

Resolution

1920x1080

Pixel Pitch

0.3114x0.3114 mm

Dot / Pixel Per Inch

82 dpi

View Angle (H / V)

178 / 178

Response Time

4 ms (Extreme mode) / 6 ms (Typical mode)

Color Support

16.7 Million

Refresh Rate

60 Hz

Brightness

300 nits

Contrast Ratio

1000:1

Color Gamut

99% sRGB

Curvature

Anti-glare

None

Yes

Video Connector

1x HDMI 1.4, 1x DP 1.2, 1x VGA

USB Port

4x USB 3.2 Gen 1 (1x BC)

Camera

Modular Camera Support

Microphone

None

Speakers

Modular Soundbar support

Power Consumption (Typical / Maximum)

24W / 65W

Power Adapter

Integrated

Stand

Tilt, Swivel, Pivot, Height Adjust Stand

Color

Black

Side Bezel Width

2 mm

Dimensions with Stand (HxWxD)

544.3x611.9x204.5 mm / 21.43x24.09x8.05 inches

Weight (Including Stand)

6.9 kg / 15.2 lbs.

Cables Included

DP cable, USB Type-A to Type-B cable

Environmental Certification

Energy Star Certified, TCO 8.0, TCO Edge 2.0, EPEAT Gold, RoHS

Ergonomic Certification

Eyesafe Display, TÜV Low Blue Light (Hardware solution), TÜV Rheinland Eve Comfort

Base Warranty

3-year

Operating System Support

Support Windows 10, Windows 11

Sync Technology

None

Tiny Support / CPU / Platform

None / None / None

Ethernet / Bluetooth / Wireless

None / None / None

Touch Screen / Digitizer Pen / Battery

None / None / None

Display Ram / Storage / Card Slot

None / None / None

EAN/UPC/JAN

0196379785652 / 196379785652 / None

Announce Date

2022-05-24

WWW.LENOVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a



particular purpose.

https://psref.lenovo.com

Visit psref website for the latest version of Product specifications Reference.
© Lenovo, 2022. All rights reserved.



ThinkVision T27i-30 Monitor

DISPLAY

Panel Size 27-inch

Screen Dimensions 607.1 mm x 354.1 mm

Panel Type

3-side Borderless In-Plane Switching

Active Area

597.9 mm x 336.3 mm

Backlight WLED

Aspect Ratio

16:9

Resolution 1920 x 1080

Pixel Pitch

0.3114 mm x 0.3114 mm

Dot/Pixel Per Inch (DPI/PPI)

Viewing Angle (H x V @ CR 10:1) 178° / 178°

Response Time

4ms (Extreme Mode), 6ms (Normal Mode), 14ms (Off Mode)

Refresh Rate

60 Hz

1000:1

Brightness (Typical) 300 cd/m²

Contrast Ratio (Typical)

Dynamic Contrast Ratio (Typical)

Color Gamut (Coverage Ratio) 99% sRGB (CIE 1931)

Color Support (Typical)
16.7 Million

Color Depth 8-bit (6+FRC)

Anti-Glare Yes

CONNECTIVITY

Video Signal 1 x HDMI 1.4 1 x DP 1.2 1 x VGA

Audio Signal

1 x Audio Out (3.5 mm)

USB Hub

Yes

USB Upstream

1 x USB 3.2 Gen 11 (by USB Type-B)

USB Downstream

4 x USB 3.2 Gen11 (1 x BC 1.2)

SPECIAL FEATURES

Software

Lenovo ThinkColour (Lenovo Display Control Center)²

Natural Low Blue Light

Yes

Modular Camera/Speaker Support Yes (Optional Support³)

POWFR

Power Consumption (Typ. / Max.) 24W / 65W

Power Consumption Sleep/Off Mode < 0.5W

Power Consumption Switch-Off Mode < 0.3W

ENERGY STAR Power Consumption (Pon/ETEC)

15W / 50kWh

Power Supply Internal

Voltage Required
AC 100 to 240 V (50-60 Hz)

MECHANICAL

Tilt Angle (Front / Back) -5° / 23.5°

Swivel Angle (Left / Right) +45° / -45°

Lift Range 155 mm

Pivot -90° / 90°

VESA Mount Capability Yes (100 x 100 mm)

Kensington Lock Slot

103

Cable Management

Yes

Bezel Color

Black

Bezel Width (Side) 2.0 mm

Bezel Width (Top / Bottom) 2.0 / 17.6 mm

DIMENSION

Size Packed (D x H x W) (mm/inch) 525.0 x 148.0 x 690.0 mm 20.67 x 5.83 x 21.17 inches

Size Unpacked w/ Stand (Lowest Position) (D x H x W) (mm/inch)

204.5 x 389.3 x 611.9 mm 8.05 x 15.33 x 24.09 inches

Size Unpacked w/ Stand (Highest Position) (D x H x W) (mm/inch) 204.5 x 544.3 x 611.9 mm 8.05 x 21.43 x 24.09 inches

Size Unpacked w/o Stand (Head Only) (D x H x W) (mm/inch) 50.0 x 362.5 x 611.9 mm 1.97 x 14.27 x 24.09 inches

Weight Packed (kg / lb) 10.1 kg / 22.3 lbs.

Weight Unpacked (kg / lb) 6.9 kg / 15.2 lbs.

Weight (Monitor Head Only) (kg / lb) 4.9 kg / 10.8 lbs.

WHAT'S IN THE BOX

Monitor with Stand Yes

Power Cable (Cable Length)
1 x Power Cable (1.8m)

DP Cable (Cable Length)
1 x DP 1.2 Cable (1.8m)

USB Cable (Cable Length)
1 x USB Type-A to Type-B Cable (1.8m)

Quick Setup Guide

CFRTIFICATION

ENERGY STAR Certification

ccc

Yes

TCO Yes

> TCO Edge Yes

EPEAT Gold

RoHS Yes

> Windows Certification Windows 10, Windows 11

China Energy Efficiency StandardTier 2

TÜV Rheinland Eye Comfort

TÜV Low Blue Light (Hardware Solution)

Eyesafe Display Certification

















Depending on many factors such as the processing capability of peripheral devices, file attributes, and other factors related to system configuration and operating environments, the actual transfer rate using the various USB connectors on this device will vary and is typically slower than the data rates as defined by the respective USB specifications: 5 Gbit/s for USB 3.2 Gen 1; 10 Gbit/s for USB 3.2 Gen 2 & 20 Gbit/s for USB 3.2 Gen2x2.

This software can only be used with Windows 10 & Windows 11. | 3 Modular VoIP solution (ThinkVision MC30 Monitor Soundbar and ThinkVision MC60 Monitor Webcam) is sold separately.

^{© 2022} Lenovo. All rights reserved. These products are available while supplies last. Prices shown are subject to change without notice. For any questions concerning price, please contact your Lenovo Account Executive. Lenovo is not responsible for photographic or typographic errors. Warranty: For a copy of applicable warranties, write to: Warranty Information, 500 Park Offices Drive, RTP, NC 27709, U.S.A, Attn: Dept. ZPYA/B600. Lenovo makes no representation or warranty regarding third-party products or services. Trademarks: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkVantage, ThinkVision, and ThinkColour are trademarks or registered trademarks of Lenovo. Microsoft, Windows, and Vista are registered trademarks of Microsoft Corporation. Intel, the Intel logo, Intel Inside, Intel Core, and Core Inside are trademarks of Intel Corporation in the U.S. and/or other countries. Other company, product, and service names may be trademarks of others.











