

Manufacturer Part #	GF66856
OS	Windows 11 Home (MSI recommends Windows 11 Pro for business.)
CPU	Core i7-11800H 8 Core
CPU Speed	2.7 - 4.6GHz
Chipset	HM570
Color	Black
Screen Size	15.6" FHD, IPS-Level 144Hz 45%NTSC
Resolution	1920x1080 (16:9)
GPU	NVIDIA® GeForce RTX™ 3060 Laptop GPU Up to 1525MHz Boost Clock, 105W Maximum Graphics Power with Dynamic Boost. *May vary by scenario
Video Memory	6G GDDR6
Keyboard	Red keyboard with Anti-Ghost key (99 Key)
Audio	Nahimic 3 / Hi-Res Audio
Speaker	Speakers 2W*2
Memory	16GB (8G*2) DDR4 3200MHz
HDD Capacity	512GB NVMe SSD
HDD Interface	NVMe
Optical Drive Type	-
LAN	Gb LAN
WLAN	Intel Wi-Fi 6 AX201(2*2 ax)
Bluetooth	BT 5.1
Card Reader	-
Webcam	720p HD Webcam
USB	2x USB 3.2 Gen1; 1x USB 2.0
Type-C Port	1x USB 3.2 Gen1 Type C
Video Port	HDMI (supports 4K @ 60Hz)
Audio Port	1 Audio Combo (1/8")
AC Power Adaptor	180W
Battery Pack	3 cell (53Whr)
Dimension	14.13"x10.20"x0.98"
Weight	4.63 lbs
Manufacturer Warranty	1 year Limited warranty (Include 1 Year Global)