ThinkVision T27h-30 63A3GAR1US

Product

ThinkVision T27h-30

Machine Type

63A3

Region

LA, NA

Display Size

27"

View Area

596.74x335.7 mm

Panel

In-Plane Switching

Aspect Ratio

16:9

Resolution

2560x1440

Pixel Pitch

0.2331x0.2331 mm

Dot / Pixel Per Inch

109 dpi

View Angle (H / V)

178 / 178

Response Time

4 ms (Extreme mode) / 6 ms (Typical mode) / 14 ms (Off mode)

Color Support

16.7 Million

Refresh Rate

60 Hz

Brightness

350 nits

Contrast Ratio

1000:1

Color Gamut

99% sRGB

Curvature

None

Anti-glare

Yes

Video Connector

1x HDMI 2.0, 1x DP 1.4, 1x DP Out, 1x USB-C 3.2 Gen 1 (DP 1.4 Alt Mode)

USB Port

4x USB 3.2 Gen 1 (1x BC)

Camera

Modular Camera Support

Microphone

None

Speakers

Modular Soundbar support

Power Consumption (Typical / Maximum)

26W / 148W

Power Adapter

Integrated

Stand

Tilt, Swivel, Pivot, Height Adjust Stand

Color

Raven Black

Side Bezel Width

2 mm

Dimensions with Stand (HxWxD)

545.4x204.5x613.6 mm / 21.47x8.05x24.16 inches

Weight (Including Stand)

6.9 kg / 15.2 lbs.

Cables Included

DP cable (NA only), USB Type-C to Type-A (NA only), USB Type-C to Type-C cable

Environmental Certification

Energy Star Certified, TCO 8.0, TCO Edge 2.0, EPEAT Gold, RoHS

Ergonomic Certification

Eyesafe Display, TÜV Low Blue Light (Hardware solution), TÜV Rheinland Eye Comfort

Base Warranty

3-year

Operating System Support

Support Windows 10, Windows 11

Sync Technology

None

Tiny Support / CPU / Platform

None / None / None

Ethernet / Bluetooth / Wireless

1x RJ 45, Ethernet (10M/100M/1000M) / None / None

Touch Screen / Digitizer Pen / Battery

None / None / None

Display Ram / Storage / Card Slot

None / None / None

EAN/UPC/JAN

0196379715758 / 196379715758 / None

Announce Date

2022-06-03



Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



https://psref.lenovo.com

Visit psref website for the latest version of Product specifications Reference.
© Lenovo, 2022. All rights reserved.



ThinkVision T27h-30 Monitor

DISPLAY

Panel Size 27-inch

Screen Dimensions 608.8 mm x 355.1 mm

Panel Type

3-side Borderless In-Plane Switching

Active Area

596.7 mm x 335.7 mm

Backlight WLED

Aspect Ratio 16:9

Resolution

2560 x 1440

Pixel Pitch 0.2331 mm x 0.2331 mm

Dot/Pixel Per Inch (DPI/PPI) 109

Viewing Angle (H x V @ CR 10:1) 178° / 178°

Response Time

4ms (Extreme Mode), 6ms (Normal Mode), 14ms (Off Mode)

Refresh Rate 60 Hz

Brightness (Typical) 350 cd/m²

Contrast Ratio (Typical) 1000:1

Dynamic Contrast Ratio (Typical)

Color Gamut (Coverage Ratio) 99% sRGB (CIE 1931)

Color Support (Typical) 16.7 Million

Color Depth 8-bit

Anti-Glare Yes

CONNECTIVITY

Video Signal

1 x USB Type-C¹ (DP 1.4 Alt Mode) 1 x HDMI 2.0

1 x DP 1.4 1 x DP Out

Audio Signal

1 x Audio Out (3.5 mm)

USB Hub Yes

Ethernet

Yes (10M/100M/1000M)

USB Upstream

1 x USB 3.2 Gen 1² (by USB Type-C¹)

USB Downstream 4 x USB 3.2 Gen1² (1 x BC 1.2)

SPECIAL FEATURES

Software

Lenovo ThinkColour (Lenovo Display Control Center)³

Natural Low Blue Light

Modular Camera/Speaker Support Yes (Optional Support⁴)

POWER

Power Consumption (Typ. / Max.) 26W / 148W

Power Consumption Sleep/Off Mode < 0.5W

Power Consumption Switch-Off Mode < 0.3W

ENERGY STAR Power Consumption (Pon/ETEC)
23W / 71kWh

Power Supply Internal

USB Type-C¹ (DP Alt Mode) Power Delivery⁵ Up to 90W

Smart Power⁶

Voltage Required
AC 100 to 240 V (50-60 Hz)

MECHANICAL

Tilt Angle (Front / Back) -5° / 23.5°

Swivel Angle (Left / Right) -45° / 45°

Lift Range 155 mm

Pivot -90° / 90°

VESA Mount Capability Yes (100 x 100 mm)

Kensington Lock Slot Yes

Cable Management

Bezel Color Black

Bezel Width (Side) 2.0 mm

Bezel Width (Top / Bottom) 2.0 / 18.0 mm

DIMENSION

Size Packed (D x H x W) (mm/inch) 525.0 x 148.0 x 690.0 mm 20.67 x 5.83 x 21.17 inches

Size Unpacked w/ Stand (Lowest Position) (D x H x W) (mm/inch) 204.5 x 390.4 x 613.6 mm 8.05 x 15.37 x 24.16 inches

Size Unpacked w/ Stand (Highest Position) (D x H x W) (mm/inch) 204.5 x 545.4 x 613.6 mm 8.05 x 21.47 x 24.16 inches

Size Unpacked w/o Stand (Head Only) (D x H x W) (mm/inch)

50.0 x 363.5 x 613.6 mm 1.97 x 14.31 x 24.16 inches

Weight Packed (kg / lb) 10.1 kg / 22.3 lbs.

Weight Unpacked (kg / lb) 6.9 kg / 15.2 lbs.

Weight (Monitor Head Only) (kg / lb) 4.8 kg / 10.6 lbs.

WHAT'S IN THE BOX

Monitor with Stand

Power Cable (Cable Length)
1 x Power Cable (1.8m)

DP Cable (Cable Length)
1 x DP 1.4 Cable (1.8m) for US,
Canada, and Brazil only

USB Cable (Cable Length)

1 x USB Type-C¹ to Type-C¹ Cable (1.8m) 1 x USB Type-C¹ to Type-A Cable (1.8m) for US, Canada, and Brazil only

Quick Setup Guide Yes

CERTIFICATION

ENERGY STAR Certification

CCC

Yes

TCO Yes

> TCO Edge Yes

EPEAT Gold

RoHS (EU 2011/65/EU)

Windows Certification
Windows 10, Windows 11

China Energy Efficiency Standard Tier 2

TÜV Rheinland Eye Comfort

TÜV Low Blue Light (Hardware Solution)

Eyesafe Display Certification





















¹ USB Type-C and USB-C are registered trademarks of USB Implementers Forum. | ² Depending on many factors such as the processing capability of peripheral devices, file attributes, and other factors related to system configuration and operating environments, the actual transfer rate using the various USB connectors on this device will vary and is typically slower than the data rates as defined by the respective USB specifications: 5 Gbit/s for USB 3.2 Gen 2; 10 Gbit/s for USB 3.2 Gen 2 & 20 Gbit/s for USB 3.

© 2022 Lenovo. All rights reserved. These products are available while supplies last. Prices shown are subject to change without notice. For any questions concerning price, please contact your Lenovo Account Executive. Lenovo is not responsible for photographic or typographic errors. Warranty: For a copy of applicable warranties, write to: Warranty Information, 500 Park Offices Drive, RTP, NC 27709, U.S.A, Attn: Dept. ZPYA/B600. Lenovo makes no representation or warranty regarding third-party products or services. Trademarks: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkVantage, ThinkVision, and ThinkColour are trademarks or registered trademarks of Lenovo. Microsoft, Windows, and Vista are registered trademarks of Microsoft Corporation. Intel, the Intel logo, Intel Inside, Intel Core, and Core Inside are trademarks of Intel Corporation in the U.S. and/or other countries. Other company, product, and service names may be trademarks of others.











