



# Product Sheet

## Pop Mini Air RGB

English Version



# Index

<b>3</b>	<b>Overview</b>
<b>4</b>	<b>Key features</b>
<b>5-6</b>	<b>General specifications</b>
<b>7</b>	<b>Package contents</b>
	<b>Additional information</b>



# Key features

- Accommodates mATX / Mini ITX Motherboards
- Easily mounted tempered glass side panel lets you showcase your components
- Up to two HDDs and six SSDs (or one HDD and five SSDs with one optical bay in use)
- Comes with three of our 120 mm Aspect RGB fans (and supports two more for a total of five)
- Holds radiators up to 240 mm in the front, 240 mm in the top and 120 mm in the rear
- Two neatly concealed 5.25" bays with storage drawer and magnetic cover
- The easy-to-clean front mesh acts as a dust filter while allowing high airflow
- Easy cable management with multiple tie-down points, pre-mounted velcro straps and convenient extra-large pass-through holes
- Front I/O comes with two 3.0 USB 5 Gb/s ports, Mic and headphone jacks
- Newly developed addressable RGB controller and RGB power LEDs
- Optional USB-C upgrade kit (available separately) adds a full speed USB Type-C front port
- Comes with two ultra-versatile storage trays, each supporting a 3.5" and a 2.5" drive simultaneously
- Easy cable management with multiple tie-down points, pre-mounted velcro straps and convenient extra-large pass-through holes
- Unique, hexagonally patterned mesh front creates a striking visual effect



# General specifications

	Pop Mini Air
Dedicated 3.5" drive mounts	• 0
Dedicated 2.5" drive mounts	• 4 (2 included)
Combined 3.5/2.5" drive mounts	• 2 (2 Included)
5.25" drive mounts	• 2
Expansion slots	• 4
Motherboard compatibility	• mATX / Mini ITX
Power supply type	• ATX
Front interface	• 2x USB 3.0*, Audio, RGB controller
Total fan mounts	• 5x 120 mm or 2x 140 mm + 1x 120 mm
Front fan	• 2x 120/ 1x 140 mm (2x Aspect 12 RGB included)
Top fan	• 2x 120/ 1x 140 mm
Rear fan	• 1x 120 mm (1x Aspect 12 RGB included)
Bottom fan	• N/A
Dust filters	• Top (perforated plastic), PSU (nylon), Front (perforated steel)

# General specifications

	Pop Mini Air
Front radiator	• Up to 240 mm
Top radiator	• Up to 240 mm (Up to 46mm RAM height)
Rear radiator	• 1x 120 mm
Bottom radiator	• N/A
PSU max length	• 150 mm
GPU max length	• 365 mm with front fan mounted
CPU cooler max height	• 170 mm
Cable routing space	• 19 mm
Cable routing grommets	• No
Fixed velcro straps	• Yes, 2 pcs
Tool-less push-to-lock	• N/A
Captive thumbscrews	• HDD brackets, SSD brackets, Side panels
Left side panel	• Tempered glass
Right side panel	• Steel
Case dimensions (LxWxH)	• 432 x 215 x 393 mm
Net weight	• 5.96 kg
Package dimensions (LxWxH)	• 514 x 293 x 470 mm
Gross weight	• 7.24 kg

\* USB 3.1 Gen 2 Type-C add-on available separately

# Package contents

## Pop Mini Air

---

- Pop Mini Air case
- Accessory bag
- User manual

# Additional information

Product	SKU	EAN	UPC	JAN
Pop Mini Air RGB White TG Clear Tint	FD-C-POR1M-01	7340172703228	843276103224	4537694286343
Pop Mini Air RGB Black TG Clear Tint	FD-C-POR1M-06	7340172703600	843276103606	4537694289214