

SEE BEYOND THE GAME. VISUALIZE YOUR VICTORY.







# **SPECIFICATIONS**

Panel Size	27" (69cm)
Panel Resolution	1920 x 1080 (FHD)
Refresh Rate	170Hz
Response time	1ms (MPRT)
DYNAMIC REFRESH RATE TECHNOLOGY	FreeSync Premium
Panel Type	VA
Brightness (nits)	250
Viewing Angle	178° (H) / 178° (V)
Aspect Ratio	16:9
Contrast Ratio	3000:1
DCR	100000000:1
Pixel Pitch (H x V)	0.3108(H)x0.3108(V)
Surface Treatment	Anti-glare
Display Colors	16.7M
DCI-P3 / sRGB	93% / 117%
Video ports	1x DP(1.2a) 2x HDMI (1.4b)
Audio ports	1x Earphone out
Active Display Area (mm)	596.736(H) x 335.664(V)
Kensington Lock	Yes
VESA Mounting	100 x 100 mm
Power Type	External Adaptor 20V 2.25A
Power Input	100~240V, 50~60Hz
Signal Frequency	53 to 183 KHz(H) 48 to 170Hz(V)
Adjustment (Tilt)	-5° ~ 20°
Curved	1500R
Weight (NW / GW)	4.5 kg ; 9.92 lbs 6.4 kg ; 14.11 lbs
Frameless Design	Yes
Note	Display Port: 1920 x 1080 (Up to 170Hz) HDMI: 1920 x 1080 (Up to 144Hz)

## **FEATURES**



### **1ms Fast Response Time**

Eliminate screen tearing and choppy frame rates with 1ms  $\,$ response time.



### Frameless Design

With the narrow bezel, you will not even notice the monitor at all in the heat of the moment.



## **Wide Color Gamut**

Wide Color Game colors and details will look more realistic and refined, to | IGamut push game immersion to its limits.



Enjoy the most immersive gameplay with 1500R curvature rate.



### 170Hz High Refresh Rate

170 Hz Experience smooth gaming with 170Hz refresh rate, that gives you the upperhand in fast moving games.



## **Curved Gaming**

CURVED View more of your game with the 1500R curve rate that is perfect for gamers to play their games.

# **CONNECTIONS**



# MONITOR **G27C4 E2**

SEE BEYOND THE GAME. VISUALIZE YOUR VICTORY.



© 2022 Micro-Star Int'l Co.Ltd. MSI is a registered trademark of Micro-Star Int'l Co.Ltd. All rights reserved.

- 1. 5-way joystick navigator
- 2. 1x DC Jack
- 3. 2x HDMI (1.4b)
- 4. 1x Display Port (1.2a)
- 5. 1x Earphone out
- 6. 1x Kensington lock