

### cTILE 22 Gen2







# **cTILE 22 Gen2** Commercial Chrome All-in-One

AOPEN delivers its next generation commercial Chrome solution with the cTILE 22 Gen2. With the same powerful specifications of the AOPEN Chromebox Commercial 2, and built for 24/7/365 commercial environments, this *purpose-ready* all-in-one features a 22-inch touch screen that supports both Google Chrome Enterprise Upgrade and Chrome Education Upgrade in environments otherwise unsuitable for consumer Chrome devices.

#### cTILE 22 Gen2 features:

- Front panel IP65 dust and water resistant
- 21.5" at 1920x1080 px (16:9)
- 250 nits, VA panel
- VESA compatible mount (100 x 100)
- Tamper proof, fanless, and solid-state design
- Glove touch
- Supports Chrome Device Management

## cTILE 22 Gen2



Power knob Audio combo USB3.0 x 2 DC Jack LAN

#### Manufacturer Part Number: 91.CB200.2A10

Model name		cTILE 22 Gen2
Housing Material		Metal
Dimensions	W x H x D (mm)	525.4 x 332 x 51.8 mm
	W x H x D (inch)	20.7 x 13.1 x 2 inch
Weight		8.4 kg/ 18.5 Pound
CPU		Intel Kaby Lake - Celeron
Memory		Dual Channel, DDR4, 2666MHz, 4GB
Graphics		Intel HD graphic, integrated on CPU
Front Panel	Resolution	21.5" 1920 x 1080 (16:9)
	Maximum Brightness	250 nits
	Panel Type	VA
	Viewing angle	178°/178°
	Response time	25ms
	Contrast Ratio	3000:1
	Touch	PCT (10 points)
Audio		Maxim MX98090
LAN		1Gbps Ethernet

Storage			M.2 SSD 32G	
Security			Google TPM, Kensington lock	
Rear Panel I/O	Power Button		x 1	
	DC Jack		x 1	
	HDMI Out Port		-	
	USB 3.0 Port		x 2	
	Audio Set	Line-Out	Audio Combo Jack x 1	
		Mic-in		
	Others		Recovery buttom x 1	
IP Grade			Front IP65 / Rear IPX2	
Adapter			90W 19V 4.74A x 1	
Input Voltage			AC 110 ~ 240V	
Warranty			1 year	
Environment				
MTBF			50000 hours	
Operating Temperature			0 ~ 40°C (32 ~ 104°F)	
Storage Temperature			-20 ~ 60°C (-4 ~ 140°F)	
Relative Humidity			90% RH max	

Supports:



