

# ThinkVision M14d 63AAUAR6US

## Product

ThinkVision M14d

## Machine Type

63AA

## Region

LA, NA

## Display Size

14"

## View Area

301.5x188.5 mm

## Panel

In-Plane Switching

## Aspect Ratio

16:10

## Resolution

2240x1400

## Pixel Pitch

0.135x0.135 mm

## Dot / Pixel Per Inch

104 dpi

## View Angle (H / V)

178 / 178

## Response Time

6 ms (Extreme mode) / 8 ms (Normal mode)

## Color Support

16.7 Million

## Refresh Rate

60 Hz

## Brightness

300 nits

## Contrast Ratio

1500:1

## Color Gamut

100% sRGB

## Curvature

None

## Anti-glare

Yes

## Video Connector

2x USB-C 3.2 Gen 1 (DP 1.2 Alt Mode)

## USB Port

1x USB 2.0 (by USB-C)

## Camera

None

## Microphone

None

## Speakers

None

## Power Consumption (Typical / Maximum)

6W / 7.5W

## Power Adapter

External

## Stand

Tilt, Height Adjust Stand

## Color

Raven Black

## Side Bezel Width

4.9 mm

## Dimensions with Stand (HxWxD)

227.5x314.4x106.4 mm / 8.96x12.38x4.19 inches

## Weight (Including Stand)

0.6 kg / 1.3 lbs.

## Cables Included

USB-C cable

## Environmental Certification

Energy Star Certified, EPEAT Silver, RoHS

## Ergonomic Certification

Eyesafe Display, TÜV Low Blue Light (Hardware solution), TÜV Rheinland Low Blue Light, TÜV Rheinland Flicker Free

## Base Warranty

3-year

## Operating System Support

Support Windows 10, Windows 11

## Sync Technology

None

## Tiny Support / CPU / Platform

None / None / None

## Ethernet / Bluetooth / Wireless

None / None / None

## Touch Screen / Digitizer Pen / Controller

None / None / None

## Display Ram / Storage / Card Slot

None / None / None

## EAN / UPC / JAN

0196380023019 / 196380023019 / None

## Announce Date

2022-07-01

[WWW.LENOVO.COM](http://WWW.LENOVO.COM)

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.


Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product specifications Reference.

© Lenovo, 2022. All rights reserved.



Lenovo™

# ThinkVision M14d Mobile Monitor

## Display

**Panel Size**  
14-inch

**Screen Dimensions**  
306.6 mm x 204.5 mm

**Panel Type**  
In-Plane Switching

**Active Area**  
301.5 mm x 188.5 mm

**Backlight**  
WLED

**Aspect Ratio**  
16:10

**Resolution**  
2240 x 1400

**Pixel Pitch**  
0.135 mm x 0.135 mm

**Dot/Pixel Per Inch (DPI/PPI)**  
104

**Viewing Angle (H x V @ CR 10:1)**  
178° / 178°

**Response Time**  
6ms (Extreme Mode), 8ms (Normal Mode)

**Refresh Rate**  
60 Hz

**Brightness (Typical)**  
300 cd/m<sup>2</sup>

**Brightness (Peak)**  
375 cd/m<sup>2</sup>

**Contrast Ratio (Typical)**  
1500:1

**Dynamic Contrast Ratio (Typical)**  
3M:1

**Color Gamut (Coverage Ratio)**  
100% sRGB

**Color Gamut (Color Area Ratio)**  
105% sRGB

**Color Support (Typical)**  
16.7 Million

**Color Depth**  
8-bit

**Anti-Glare**  
Yes

## Connectivity

**Video Signal**  
2 x USB Type-C<sup>1</sup> Gen 1 (DP 1.2 Alt Mode)

**Audio Signal**  
1 x Audio Out (by USB Type-C<sup>1</sup>)

**USB Hub**  
Yes

**USB Upstream**  
1 x USB 2.0 (by USB Type-C<sup>1</sup>)

**USB Downstream**  
1 x USB 2.0 (by USB Type-C<sup>1</sup>)

## Special Features

**Software**  
Yes (Lenovo Display Control Center)<sup>2</sup>

**Natural Low Blue Light**  
Yes

## Power

**Power Consumption (Typ. / Max.)**  
6W / 7.5W

**Power Consumption Sleep/Off Mode**  
≤0.5W

**Power Consumption Switch-Off Mode**  
≤0.3W

**ENERGY STAR Power Consumption (Pon/ETEC)**  
6.85W / 22.71kWh

**Power Supply**  
External

**USB Type-C<sup>1</sup> (DP Alt Mode) Power Delivery<sup>3</sup>**  
Up to 65W

**USB Type-C<sup>1</sup> (Downstream) Power Delivery<sup>3</sup>**  
Up to 65W

**Voltage Required**  
5V or 9V or 15V DC 3A  
or 20V DC 5A Max.

## Mechanical

**Tilt Angle (Front / Back)**  
-5° / 95°

**Lift (Max. Range)**  
11 mm

**VESA Mount Capability**  
Yes (2 x Screws Holes, 100 mm)

**Kensington Lock Slot**  
Yes

**Bezel Color**  
Raven Black

**Bezel Width (Side)**  
4.9 mm

**Bezel Width (Top / Bottom)**  
4.9 / 18.9 mm

## Dimension

**Size Packed (D x H x W) (mm/inch)**  
277.0 x 76.0 x 384.0 mm  
10.91 x 2.99 x 15.12 inches

**Size Unpacked w/ Stand (Lowest Position) (D x H x W) (mm/inch)**  
106.4 x 216.5 x 314.4 mm  
4.19 x 8.52 x 12.38 inches

**Size Unpacked w/ Stand (Highest Position) (D x H x W) (mm/inch)**  
106.4 x 227.5 x 314.4 mm  
4.19 x 8.96 x 12.38 inches

**Size Unpacked w/o Stand (Head Only) (D x H x W) (mm/inch)**  
4.6 x 215.3 x 314.4 mm  
0.18 x 8.48 x 12.38 inches

**Weight Packed (kg / lbs.)**  
1.8 kg / 4.0 lbs.

**Weight Unpacked (kg / lbs.)**  
0.6 kg / 1.3 lbs.

**Weight (Monitor Head Only) (kg / lbs.)**  
0.4 kg / 0.8 lbs.

## What's in the Box

**Monitor with Stand**  
Monitor with Integrated Stand

**USB-C Cable (Cable Length)**  
1 x USB-C Cable (1.0 m)

**Quick Setup Guide**  
Yes

## Certification

**ENERGY STAR Certification**  
Yes

**CCC**  
Yes

**EPEAT**  
Silver

**Volatile Organic Compound Certification**  
Yes

**RoHS (2011/65/EU)**  
Yes

**Windows Certification**  
Windows 10, Windows 11

**China Energy Efficiency Standard**  
Tier 1

**TÜV Rheinland Low Blue Light**  
Yes

**TÜV Rheinland Flicker Free**  
Yes

**TÜV Low Blue Light (Hardware Solution)**  
Yes

**Eyesafe Display Certification**  
Yes



<sup>1</sup> USB Type-C<sup>®</sup> and USB-C<sup>®</sup> are registered trademarks of USB Implementers Forum. <sup>2</sup> This software can only be used with Windows 10 & Windows 11.

<sup>3</sup> Listed as maximum capacity of power delivery. Actual capacity of power delivery may vary depending upon devices connected or monitor configuration, and may decline with downstream USB ports connected or higher brightness setting.

© 2022 Lenovo. All rights reserved. These products are available while supplies last. Prices shown are subject to change without notice. For any questions concerning price, please contact your Lenovo Account Executive. Lenovo is not responsible for photographic or typographic errors. Warranty: For a copy of applicable warranties, write to: Warranty Information, 500 Park Offices Drive, RTP, NC 27709, U.S.A. Attn: Dept. ZPYA/B600. Lenovo makes no representation or warranty regarding third-party products or services. Trademarks: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkVantage, ThinkVision, and ThinkColour are trademarks or registered trademarks of Lenovo. Microsoft, Windows, and Vista are registered trademarks of Microsoft Corporation. Intel, the Intel logo, Intel Inside, Intel Core, and Core Inside are trademarks of Intel Corporation in the U.S. and/or other countries. Other company, product, and service names may be trademarks or service marks of others.

Specifications may vary depending upon region.

Smarter  
technology  
for all

Lenovo

# ThinkVision M14d

