

Product data sheet

Specifications



APC Back UPS, 750VA/410W, Tower, 120V, 4x NEMA 5-15R outlets, USB Type A + C Ports, User Replaceable Battery

BVK750M2

Overview

Lead time Usually in Stock

Main

Main Input Voltage 120 V

Other Input Voltage 108...150 V

Main Output Voltage 120 V

Rated power in W 410 W

Rated power in VA 750 VA

Output connection type 4 NEMA 5-15R

Number of cables 1

Battery Type Lead-Acid battery

Batteries & Runtime

Typical recharge time 6 h

Battery Voltage 12 V

Battery Capacity 9 Ah

Battery power in VAh 92 VAh

Battery graph comments Curve fit to measured runtime data. All measurements taken with new, fully charged batteries, at typical environmental conditions, with no electrical input and balanced resistive load (PF = 1.0) output.

Physical

Color Black

Height 6.30 in (160 mm)

Width 4.72 in (120 mm)

Depth 13.98 in (355 mm)

Product Weight 12.13 lb(US) (5.5 kg)

USB compatible Yes

Input

Plug standard 5-15P

Efficiency at full load 108...150 V

Input protection type	Circuit breaker
-----------------------	-----------------

Output

Max Configurable Power (Watts)	410 W
--------------------------------	-------

Output Frequency (sync to mains)	50/60 Hz
----------------------------------	----------

Waveform Type	Stepped approximation to a sinewave
---------------	-------------------------------------

Environmental

IP degree of protection	IP20 CSA C22.2 No 107.3
-------------------------	-------------------------

Communications & Management

Emergency Power Off (EPO)	Yes
---------------------------	-----

Surge Protection and Filtering

Surge energy rating	350 J
---------------------	-------

Ordering and shipping details

GTIN	731304449126
------	--------------

Packing Units

Unit Type of Package 1	PCE
------------------------	-----

Number of Units in Package 1	1
------------------------------	---

Package 1 Height	9.84 in (25 cm)
------------------	-----------------

Package 1 Width	7.76 in (19.7 cm)
-----------------	-------------------

Package 1 Length	16.93 in (43 cm)
------------------	------------------

Package 1 Weight	13.45 lb(US) (6.1 kg)
------------------	-----------------------

Offer Sustainability

REACH Regulation	REACH Declaration
------------------	-----------------------------------

EU RoHS Directive	Compliant EU RoHS Declaration
-------------------	--

Mercury free	Yes
--------------	-----

China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
-----------------------	--

RoHS exemption information	Yes
----------------------------	-----

WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
------	--

Contractual warranty

Warranty	3 years
----------	---------

Recommended replacement(s)