ThinkVision T23i-30 63B2MAR6US

Product

ThinkVision T23i-30

Machine Type

63B2

Region

LA, NA

Display Size

23"

View Area

509.1x286.4 mm

Panel

In-Plane Switching

Aspect Ratio

16:9

Resolution

1920x1080

Pixel Pitch

0.265x0.265 mm

Dot / Pixel Per Inch

96 dpi

View Angle (H / V)

178 / 178

Response Time

4 ms (Extreme mode) / 6 ms (Typical mode) / 14 ms (Off mode)

Color Support

16.7 Million

Refresh Rate

60 Hz

Brightness

250 nits

Contrast Ratio

1000:1

Color Gamut

75% NTSC

Curvature

None

Anti-glare

Yes

Video Connector

1x HDMI 1.4, 1x DP 1.2, 1x VGA

USB Port

4x USB-A 3.0

Network Connectivity

None

Camera

None

Microphone

None

Speakers

None

Power Consumption (Typical / Maximum)

15W / 48W

Power Adapter

Integrated

Stand

Tilt, Swivel, Pivot, Height Adjust Stand

Color

Raven Black

Side Bezel Width

2 mm

Dimensions with Stand (HxWxD)

493.8x522.0x199.7 mm / 19.44x20.55x7.86 inches

Weight (Including Stand)

5.2 kg / 11.5 lbs.

Cables Included

HDMI cable, USB Type-A to Type-B cable

Environmental Certification

Energy Star Certified, TCO 9.0, TCO Edge 2.0, EPEAT Gold, RoHS

Ergonomic Certification

Eyesafe Display, TÜV Low Blue Light (Hardware solution), TÜV Rheinland Low Blue Light, TÜV Rheinland Flicker Free, TÜV Rheinland Eve Comfort

Base Warranty

3-year

Operating System Support

Support Windows 10, Windows 11

Sync Technology

None

ThinkCentre M Series Support

None

Processor

None

Touch Screen

None

Controller

None

Display Ram / Storage / Card Slot

None / None / None

EAN/UPC/JAN

0196380369940 / 196380369940 / None

Announce Date

2022-08-01

WWW.LENOVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



https://psref.lenovo.com

Visit psref website for the latest version of Product specifications Reference.
© Lenovo, 2022. All rights reserved.



ThinkVision T23i-30 Monitor

Display

Panel Size 23-inch

Screen Dimensions 517.2 mm x 290.4 mm

Panel Type
3-side NearEdgeless In-Plane Switching

Active Area 509.1 mm x 286.4 mm

Backlight WLED

Aspect Ratio 16:9

Resolution 1920 x 1080

Pixel Pitch 0.265 mm x 0.265 mm

Dot/Pixel Per Inch (DPI/PPI) 96

Viewing Angle (H x V @ CR 10:1) 178° / 178°

Response Time 4ms (Extreme Mode), 6ms (Normal Mode), 14ms (Off Mode)

Refresh Rate 60Hz

Brightness (Typical) 250 cd/m²

Contrast Ratio (Typical) 1000:1

Dynamic Contrast Ratio (Typical) 3M:1

Color Gamut (Coverage Ratio) 72% NTSC (CIE 1931)

Color Support (Typical) 16.7 Million

Color Depth 8-bit (6+FRC)

Anti-Glare Yes

Connectivity

Video Signal 1 x HDMI 1.4 1 x DP 1.2 1 x VGA

Audio Signal 1 x Audio Out (3.5 mm)

USB Hub Yes

USB Upstream 1 x USB 3.0 Type-B

USB Downstream 4 x USB 3.0 Type-A

Special Features

Software
Lenovo ThinkColour (Lenovo Display
Control Center)*

Natural Low Blue Light

Power

Power Consumption (Typ. / Max.) 15W / 48W

Power Consumption Sleep/Off Mode < 0.5W

Power Consumption Switch-Off Mode < 0.3W

ENERGY STAR Power Consumption (Pon/ETEC)
11.88W / 37.05kWh

Power Supply Internal

Voltage Required
AC 90 to 264 V (50-60Hz)

Mechanical

Tilt Angle (Front / Back) -5° / 23.5°

Swivel Angle (Left / Right) +45° / -45°

Lift (Max. Range) 155 mm

Pivot -90° / 90°

VESA Mount Capability Yes (100 x 100 mm)

Kensington Lock Slot

Cable Management Yes

Bezel Color Raven Black

Bezel Width (Side) 2.0 mm

Bezel Width (Top / Bottom) 2.0 /17.3 mm

Dimension

Size Packed (D x H x W) (mm/inch) 150.0 x 421.0 x 592.0 mm 5.91 x 16.57 x 23.31 inches

Size Unpacked w/ Stand (Lowest Position) (D x H x W) (mm/inch) 199.7 x 338.8 x 522.0 mm 7.86 x 13.34 x 20.55 inches

Size Unpacked w/ Stand (Highest Position) (D x H x W) (mm/inch) 199.7 x 493.8 x 522.0 mm 7.86 x 19.44 x 20.55 inches

Size Unpacked w/o Stand (Head Only) (D x H x W) (mm/inch) 46.4 x 313.1 x 522.0 mm 1.83 x 12.33 x 20.55 inches Weight Packed (kg / lbs.) 7.3 kg / 16.1 lbs.

Weight Unpacked (kg / lbs.) 5.2 kg / 11.5 lbs.

Weight (Monitor Head Only) (kg / lbs.) 3.2 kg / 7.1 lbs.

What's in the Box

Monitor with Stand

Yes

Power Cable (Cable Length)
1 x Power Cable (1.8 m)

HDMI Cable (Cable Length)
1 x HDMI Cable (1.8 m)

USB Cable (Cable Length)
1 x USB 3.0 Type-A to Type-B Cable (1.8 m)

Quick Setup Guide

Warranty Booklet Yes

Certification

ENERGY STAR Certification

200

CCC Yes

TCO 9.0

TCO Edge 2.0

EPEATGold

Volatile Organic Compound Certification

RoHS (2011/65/EU)

Windows Certification
Windows 10, Windows 11

China Energy Efficiency Standard

TÜV Rheinland Eye Comfort

TÜV Rheinland Low Blue Light

TÜV Rheinland Flicker Free

TÜV Low Blue Light (Hardware Solution)

Eyesafe Display Certification Yes











Yes













* This software can only be used with Windows 10 & Windows 11.

© 2022 Lenovo. All rights reserved. These products are available while supplies last. Prices shown are subject to change without notice. For any questions concerning price, please contact your Lenovo Account Executive. Lenovo is not responsible for photographic or typographic errors. Warranty: For a copy of applicable warranties, write to: Warranty Information, 500 Park Offices Drive, RTP, NC 27709, U.S.A, Attn: Dept. ZPYA/B600. Lenovo makes no representation or warranty regarding third-party products or services. Trademarks: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkVantage, ThinkVision, and ThinkColour are trademarks or registered trademarks of Lenovo. Microsoft, Windows, and Vista are registered trademarks of Microsoft Corporation. Intel, the Intel logo, Intel Inside, Intel Core, and Core Inside are trademarks of Intel Corporation in the U.S. and/or other company, product, and service names may be trademarks or service marks of others.

Specifications may vary depending upon region.











