



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Safe-IT UL 2930 Medical-Grade Power Strip for Patient Care Vicinity, 6 Hospital-Grade Outlets, Safety Covers, Antimicrobial, 6 ft. Cord

MODEL NUMBER: PS-606-HGDG











Delivers power to movable plug-connected equipment attached to IV poles, crash carts and mobile medical workstations in patient care vicinities.

Features

UL 2930 Medical-Grade Power Strip Approved for Patient Care Vicinities

The PS-606-HGDG features six NEMA 5-15R-HG "green dot" hospital-grade outlets that supply power to medical equipment used inside patient care vicinities, including operating rooms, therapy rooms and imaging environments. It meets UL 2930 standards with a NEMA 5-15P-HG plug that provides redundant ground connection. The innovative input plug eliminates the need for an additional ground wire, which reduces cable clutter, the risk of tripping and potential shock risk to a patient in the event of a ground fault.

Antimicrobial Protection Helps Provide a Safer, Cleaner and Healthier Work Environment

The Safe-IT™ power strip is protected by an antimicrobial coating that helps resist the growth of bacteria, viruses, fungi, mold and mildew.

Premium Safety Features Help Ensure Proper Power Connections

With no central power switch, this power strip presents no danger of accidental shutoff and cutting off power to essential devices. Resettable 15-amp circuit breakers protect connected equipment against overloads. Locking plastic safety covers are included to block access to unused outlets.

Ready for Installation in Demanding Medical Environments

The six-foot cord gives you some leeway in positioning the power strip away from a standard NEMA 5-15R duplex wall outlet. Built-in mounting flanges and integrated keyhole slots let you mount the all-metal housing to benches, stands, mobile carts, IV poles or other areas containing multiple cord-and-plug-connected medical electrical equipment used in patient care vicinities.

Specifications

OVERVIEW	
UPC Code	037332262264

Highlights

- Medical-grade power strip approved for use inside and outside patient care vicinities
- Meets UL 2930 and NFPA 99 standards for enhancing patient, staff and visitor safety
- Input plug with dual ground connection eliminates need for extra ground wire
- 6 ft. power cord allows some flexibility in placing power strip away from wall outlet
- Antimicrobial protection helps resist the growth of bacteria, viruses, fungi, mold and mildew

Package Includes

- PS-606-HGDG UL 2930
 Medical-Grade Power Strip, 6
 Outlets, 6 ft. Cord
- (6) Outlet safety covers
- · Owner's manual



INPUT		
Nominal Input Voltage(s) Supported	120V AC	
Recommended Electrical Service	15A, 120V	
Input Plug Features	Hospital Grade Plug	
Input Cord Gauge Type	10 gauge; 12 gauge; SJT	
Voltage Compatibility (VAC)	120	
Input Plug Type	NEMA 5-15P-HG	
Input Plug Type Details	Redundant (double) ground connection	
Input Cord Length (ft.)	6	
Right-Angle Plug	No	
Input Cord Length (m)	1.83	
Integrated Cord Clip	No	
ОИТРИТ		
Frequency Compatibility	50 / 60 Hz	
Output (Watts)	1800	
Output Receptacles	(6) 5-15R-HG	
Circuit Breaker (amps)	15	
Overload Protection	2 x 15amp breakers (1 line, 1 neutral)	
Transformer Accommodation	(2) Yes	
Outlet Orientation	Single row of 6	
Right-Angle Outlets	No	
USER INTERFACE, ALERTS & CON	TROLS	
Switches	No power switch	
PHYSICAL		
Color	White	
Material of Construction	Metal	
Power Cord Color	White	
Form Factors Supported	IV poles, mobile carts, crash carts and mobile medical workstations	
Housing Color	White	
Included Mounting Accessories	Mounting tabs and flanges	
Mounting Holes or Slots	Yes	
Slot or Hole Mount Measurement (Center to Center)	Distance between keyhole tabs = 127mm; Distance between end tabs = 207.45mm	





Outlets Measurement (Center to Center)	Inner outlets = 32.5mm	
Receptacle Color	White	
Shipping Dimensions (hwd / in.)	3.43 x 10.43 x 17.60	
Shipping Dimensions (hwd / cm)	8.71 x 26.49 x 44.70	
Shipping Weight (lbs.)	4.30	
Shipping Weight (kg)	1.95	
Unit Dimensions (hwd / in.)	1.860 x 2.500 x 13.630	
Unit Dimensions (hwd / cm)	21.97 x 6.35 x 3.81	
Unit Weight (lbs.)	2.25	
Unit Weight (kg)	1.02	
Mounting Details	Includes flanges	
FEATURES & SPECIFICATIONS		
Antimicrobial	Yes	
Rotatable Outlets	No	
Built-in Cable Management	No	
Built-In Circuit Breaker	Yes	
Antibacterial	No	
STANDARDS & COMPLIANCE		
Product Certifications	UL 2930	
Product Compliance	NFPA 99: 10.2.3.6; RoHS	
WARRANTY		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies