

NMP599-W - 4K UHD NETWORK MEDIA PLAYER, ANDROID 7.1, GIGABIT LAN, WI-FI, HDMI 2.0 OUT, USB X 2, MICRO SD, AUDIO OUT, 16GB STORAGE, SIGNAGE MANAGER CMS+LICENSE, BLACK

Key Features

- 4K Ultra HD video playback
- Rich content harnessed live from the cloud
- Wireless connectivity and HTML5
- Deliver dynamic information at the point of service via the web, or from a network server
- Included content management software
- Portrait and landscape design templates
- 16GB of built-in memory
- Store and play hours and hours of stunning high-definition content
- Perfect for retail, hospitality, and point-of-sale advertising
- Deliver reliable messaging and dynamic multimedia for any of your large format displays
- Signage Manager content management software and perpetual license included per device



Product Description

Deploy compelling digital signage with extreme reliability and stunning visuals with the ViewSonic® NMP599-W high-definition wireless network media player. Your content shines with 4K Ultra HD video playback and access to rich content harnessed live from the cloud. Wireless connectivity and HTML5 support lets you easily deliver dynamic information at the point of service via the web, or from a network server. Manage content with ease thanks to the included content management software, as well as portrait and landscape design templates. And if you're worried about running out of storage, don't fret. Thanks to 16GB of built-in memory, the NMP599-W can store and play hours and hours of stunning high-definition content. Perfect for retail, hospitality, and point-of-sale advertising, the NMP599-W is the media player you can trust to deliver reliable messaging and dynamic multimedia for any of your large format displays. Signage Manager content management software and perpetual license included per device.

Specifications

More Information

Media Player Type	Media Player
CPU Processor Type	Rockchip RK3188 Quad-Core
CPU Processor Speed	1.6GHz max.
Operating System	Android™ 7.1
Real-time Clock (RTC)	Yes

W3C SMIL	Yes
HTML5, JavaScript and CSS	Yes
Widgets	Calendar, Clock, News and Web page integration
Graphic Chipset	MALI400MP4
RAM	2GB
Memory Type	DDR3L
Wifi	802.11b/g/n (2.4GHz)
Storage Capacity	16GB
Storage Type	eMMC
HDMI CEC	1
HDMI 2.0 Out	1
Ethernet LAN (RJ45)	1
3.5mm Audio Out	1
Micro USB	1
USB 2.0	2
Card Reader	Micro SD Reader
Voltage	100-120V+/- 10%, 50/60Hz, 0.5A
DC Adapter Output	12V, 1.5A
Temperature	-4-122° F (-20-50° C)
Humidity (non-condensing)	10-85%
Physical (in.)	5.65 x 5.04 x 1.32
Packaging (in.)	8.89 x 6.77 x 3.5
Physical (mm)	138.6 x 128.1 x 33.5
Packaging (mm)	226 x 172 x 89
Net (lbs)	1.05
Gross (lbs)	2.07
Net (kg)	476g
Gross (kg)	939g
Recycle/Disposal	Please dispose of in accordance with local, state or federal laws.
Regulations	FCC, CE, cTUVus, NOM, PSB, iDA, RCM
PACKAGE CONTENTS	HDMI cable, External WIFI Antenna, AC Adapter, Power plug (US), Velcro, Hardware Quick Start Guide, Software Quick Start Guide
Warranty	1-year limited warranty on parts and labor on-site service



Contact Sales

ViewSonic.com

888.881.8781

email:

salesinfo@viewsonic.com