ThinkVision T22i-30 63B0MAR6US

Product

ThinkVision T22i-30

Machine Type

63B0

Region

LA, NA

Display Size

21.5"

View Area

476.1x267.8 mm

Panel

In-Plane Switching

Aspect Ratio

16:9

Resolution

1920x1080

Pixel Pitch

0.274x0.274 mm

Dot / Pixel Per Inch

102 dpi

View Angle (H / V)

178 / 178

Response Time

4 ms (Extreme mode) / 6 ms (Typical mode) / 14 ms (Off mode)

Color Support

16.7 Million

Refresh Rate

60 Hz

Brightness

250 nits

Contrast Ratio

1000:1

Color Gamut

99% sRGB

Curvature

None

Anti-glare Yes

Video Connector

1x HDMI 1.4, 1x DP 1.2, 1x VGA

USB Port

4x USB-A 3.0

Camera

None

Microphone

None

Speakers

None

Power Consumption (Typical / Maximum)

15W / 48W

Power Adapter

Integrated

Stand

Tilt, Swivel, Pivot, Height Adjust Stand

Color

Raven Black

Side Bezel Width

2.0 mm

Dimensions with Stand (HxWxD)

487.4x498.3x194.7 mm / 19.19x19.62x7.67 inches

Weight (Including Stand)

4.9 kg / 10.8 lbs.

Cables Included

HDMI cable, USB Type-A to Type-B cable

Environmental Certification

Energy Star Certified, TCO 9.0, TCO Edge 2.0, EPEAT Gold, RoHS

Ergonomic Certification

Eyesafe Display, TÜV Low Blue Light (Hardware solution), TÜV Rheinland Low Blue Light, TÜV Rheinland Flicker Free, TÜV Rheinland Eve Comfort

Base Warranty

3-vear

Operating System Support

Support Windows 10, Windows 11

Sync Technology

None

Tiny Support / CPU / Platform

None / None / None

Ethernet / Bluetooth / Wireless

None / None / None

Touch Screen / Digitizer Pen / Controller

None / None / None

Display Ram / Storage / Card Slot

None / None / None

EAN/UPC/JAN

0196380285967 / 196380285967 / None

Announce Date

2022-08-01

WWW.LENOVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the



particular purpose.

https://psref.lenovo.com

implied warranties of merchantability or fitness for a

Visit psref website for the latest version of Product specifications Reference.
© Lenovo, 2022. All rights reserved.



Think Vision T22i-30 Monitor

Display

Panel Size 21.5-inch

Screen Dimensions 484.4 mm x 271.9 mm

Panel Type 3-side NearEdgeless In-Plane Switching

Active Area 476.1 mm x 267.8 mm

Backlight WLED

Aspect Ratio 16:9

Resolution 1920 x 1080

Pixel Pitch 0.274 mm x 0.274 mm

Dot/Pixel Per Inch (DPI/PPI)

Viewing Angle (H x V @ CR 10:1) 178° / 178°

Response Time

4ms (Extreme Mode), 6ms (Normal Mode), 14ms (Off Mode)

Refresh Rate 60Hz

Brightness (Typical) 250 cd/m²

Contrast Ratio (Typical) 1000:1

Dynamic Contrast Ratio (Typical)

Color Gamut (Coverage Ratio) 99.0% sRGB

Color Gamut (Color Area Ratio) 108.0% sRGB

Color Support (Typical) 16.7 Million

Color Depth 8-bit (6+FRC)

Anti-Glare Yes

Connectivity

Video Signal 1 x HDMI 1.4 1 x DP 1.2 1x VGA

Audio Signal 1 x Audio Out (3.5 mm)

USB Hub Yes

USB Upstream 1 x USB 3.0 Type-B

USB Downstream 4 x USB 3.0 Type-A

Special Features

Software Yes

Natural Low Blue Light

Power

Power Consumption (Typ. / Max.) 15W / 48W

Power Consumption Sleep/Off Mode < 0.5W (Sleep), < 0.3W (Off DC)

ENERGY STAR Power Consumption (Pon/ETEC) 11.0W / 34.41kWh

Power Supply Internal

Voltage Required AC 100 to 240 V (50-60Hz)

Mechanical

Tilt Angle (Front / Back) -5° / 23.5°

Swivel Angle (Left / Right) +45° / -45°

Lift (Max. Range) 155 mm

Pivot -90° / 90°

VESA Mount Capability Yes (100 x 100 mm)

Kensington Lock Slot Yes

Cable Management Yes

Bezel Color Raven Black

Bezel Width (Side) 2.0 mm

Bezel Width (Top / Bottom) 2.0 / 17.3 mm

Dimension

Size Packed (D x H x W) (mm/inch) 144.0 x 414.0 x 563.0 mm 5.67 x 16.30 x 22.17 inches

Size Unpacked w/ Stand (Lowest Posi-(D x H x W) (mm/inch) 194.7 x 332.4 x 498.3 mm 7.67 x 13.09 x 19.62 inches

Size Unpacked w/ Stand (Highest Position) (D x H x W) (mm/inch)

194.7 x 487.4 x 498.3 mm 7.67 x 19.19 x 19.62 inches

Size Unpacked w/o Stand (Head Only) (D x H x W) (mm/inch) 46.4 x 294.7 x 489.3 mm 1.83 x 11.60 x 19.26 inches

Weight Packed (kg / lbs.) 6.8 kg / 15.0 lbs.

Weight Unpacked (kg / lbs.) 4.9 kg / 10.8 lbs.

Weight (Monitor Head Only) (kg / lbs.) 3.0 kg / 6.6 lbs.

What's in the Box

Monitor with Stand Yes

Power Cable (Cable Length) 1 x Power Cable (1.8 m)

HDMI Cable (Cable Length) 1 x HDMI Cable (1.8 m)

USB Cable (Cable Length) 1 x USB 3.0 Type-A to Type-B Cable (1.8 m)

Quick Setup Guide Yes

Warranty Booklet Yes

Certification

ENERGY STAR Certification

CCC Yes

TCO 9.0

TCO Edge 2.0

EPEAT Gold

Tier 1

Yes

Volatile Organic Compound Certification

RoHS (2011/65/EU)

Windows Certification Windows 10 Windows 11

China Energy Efficiency Standard

TÜV Rheinland Eye Comfort

TÜV Rheinland Low Blue Light Yes

TÜV Rheinland Flicker Free Yes

TÜV Low Blue Light (Hardware Solution)

Eyesafe Display Certification







































