# ThinkVision P24h-30 63B3GAR6US

Product

ThinkVision P24h-30

Machine Type

63B3

Region

LA, NA

Display Size

23.8"

View Area

526.8x296.3 mm

Panel

In-Plane Switching

Aspect Ratio

16:9

Resolution

2560x1440

Pixel Pitch

0.205x0.205 mm

Dot / Pixel Per Inch

123 dpi

View Angle (H / V)

178 / 178

Response Time

4 ms (Extreme mode) / 6 ms (Typical mode)

Color Support

16.7 Million

Refresh Rate

60 Hz

Brightness

300 nits

Contrast Ratio

1000:1

**Color Gamut** 

99% sRGB, 99% BT.709

Curvature

None

Anti-glare

Yes

Video Connector

1x HDMI 2.0, 1x DP 1.4, 1x DP Out, 1x USB-C 3.2 Gen 1 (DP 1.4 Alt Mode)

**USB Port** 

4x USB 3.2 Gen 1 (1x BC 1.2)

Camera

Modular Camera Support

Microphone

None

Speakers

Modular Speaker Support

Power Consumption (Typical / Maximum)

27W / 161W

Power Adapter

Integrated

Stand

Tilt, Swivel, Pivot, Height Adjust Stand

Color

Raven Black

Side Bezel Width

2 mm

Dimensions with Stand (HxWxD)

503.8x539.5x199.7 mm / 19.83x21.24x7.86 inches

Weight (Including Stand)

5.7 kg / 12.6 lbs.

Cables Included

DP cable, USB Type-C to Type-C cable, USB Type-C to Type-A cable

**Environmental Certification** 

Energy Star Certified, TCO 9.0, TCO Edge 2.0, EPEAT Gold, RoHS

**Ergonomic Certification** 

Eyesafe Display, TÜV Low Blue Light (Hardware solution), TÜV Rheinland Low Blue Light, TÜV Rheinland Flicker Free, TÜV Rheinland Eye Comfort

Base Warranty

3-year

Operating System Support

Support Windows 10, Windows 11

Sync Technology

None

Tiny Support / CPU / Platform

None / None / None

Ethernet / Bluetooth / Wireless

1x RJ45, Ethernet (10M/100M/1000M) / None / None

Touch Screen / Digitizer Pen / Controller

None / None / None

Display Ram / Storage / Card Slot

None / None / None

EAN/UPC/JAN

0196380976766 / 196380976766 / None

Announce Date

2022-08-01



Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a



particular purpose.

#### https://psref.lenovo.com

Visit psref website for the latest version of Product specifications Reference.
© Lenovo, 2022. All rights reserved.



# Think Vision P24h-30 Monitor

# **Display**

Panel Size 23.8-inch

Screen Dimensions 534.9 mm x 303.1 mm

Panel Type 3-side NearEdgeless In-Plane Switching

Active Area 526.8 mm x 296.3 mm

Backlight WLED

Aspect Ratio 16:9

Resolution 2560 x 1440

Pixel Pitch 0.205 mm x 0.205 mm

Dot/Pixel Per Inch (DPI/PPI)
123

Viewing Angle (H x V @ CR 10:1) 178° / 178°

Response Time 4ms (Extreme Mode), 6ms (Normal Mode)

Refresh Rate 60 Hz

Brightness (Typical) 300 cd/m<sup>2</sup>

Contrast Ratio (Typical)

Dynamic Contrast Ratio (Typical) 3M:1

**Color Gamut (Coverage Ratio)** 99.0% sRGB (CIE 1931), 99.0% BT.709 (CIE 1976)

Color Gamut (Color Area Ratio) 111.0% sRGB

Color Support (Typical) 16.7 Million Color Depth 8-bit (6+FRC)

HDR Compliance Yes (HDR10)

Anti-Glare Yes

### Connectivity

Video Signal
1 x USB Type-C<sup>1</sup> Gen 1
(DP 1.4 Alt Mode)
1 x HDMI 2.0
1 x DP 1.4
1 x DP Out

Audio Signal 1 x Audio Out (3.5 mm)

USB Hub Yes

Ethernet Yes (10M/100M/1000M)

USB Upstream 1 x USB 3.2 Gen 1<sup>2</sup> (by USB Type-C<sup>1</sup>)

USB Downstream 4 x USB 3.2 Gen 1<sup>2</sup> (1 x BC1.2)

### Multimedia

Modular Camera/Speaker Support Yes (Optional Support<sup>3</sup>)

# **Special Features**

Factory Calibration
Yes (Delta-E Color Accuracy (<2))

Software Lenovo ThinkColour (Lenovo Display Control Center)<sup>4</sup>

Natural Low Blue Light

**Power** 

Power Consumption (Typ. / Max.) 27W / 161W

Power Consumption Sleep/Off Mode

Power Consumption Switch-Off Mode < 0.3W

ENERGY STAR Power Consumption (Pon/E<sub>TEC</sub>)
18W / 57kWh

Power Supply Internal

USB Type-C¹ (DP Alt Mode) Power Delivery<sup>5</sup>
Up to 100W

Smart Power Yes

Voltage Required AC 100 to 240 V (50-60 Hz)

#### Mechanical

Tilt Angle (Front / Back) -5° / 23.5°

Swivel Angle (Left / Right) -45° / 45°

Lift (Max. Range) 155 mm

**Pivot** -90° / 90°

VESA Mount Capability Yes (100 x 100 mm)

Kensington Lock Slot Yes

Cable Management Yes

Bezel Color Raven Black

Bezel Width (Side) 2.0 mm

Bezel Width (Top / Bottom) 2.0 / 18.0 mm **Dimension** 

Size Packed (D x H x W) (mm/inch) 160.0 x 420.0 x 620.0 mm 6.30 x 16.54 x 24.41 inches

Size Unpacked w/ Stand (Lowest Position) (D x H x W) (mm/inch) 199.7 x 348.8 x 539.5 mm 7.86 x 13.73 x 21.24 inches

Size Unpacked w/ Stand (Highest Position) (D x H x W) (mm/inch) 199.7 x 503.8 x 539.5 mm 7.86 x 19.83 x 21.24 inches

Size Unpacked w/o Stand (Head Only) (D x H x W) (mm/inch) 46.5 x 323.7 x 539.5 mm 1.83 x 12.74 x 21.24 inches

Weight Packed (kg / lbs.) 8.6 kg /19.0 lbs.

Weight Unpacked (kg / lbs.) 5.7 kg / 12.6 lbs.

Weight (Monitor Head Only) (kg / lbs.) 3.8 kg / 8.4 lbs.

### What's in the Box

Monitor with Stand Yes

Power Cable (Cable Length)
1 x Power Cable (1.8 m)

DP Cable (Cable Length)
1 x DP 1.2 Cable (1.8 m) (For NA, Brazil, and PRC WS: No for EMEA. AP. LAS. and PRC SA)

HDMI Cable (Cable Length)
1 x HDMI 2.0 Cable (1.8 m) (For PRC SA;
No for PRC WS, ROW NA, EMEA, AP, and LA)

USB-C¹ Cable (Cable Length)
USB Type-C¹ Gen 1 Cable (1.8 m)

USB Cable (Cable Length)
USB Type-C<sup>1</sup> to Type-A Cable (1.8 m)
(For NA and Brazil; No for PRC WS,
PRC SA, ROW EMEA, AP, and LAS)

Factory Calibration Report

Quick Setup Guide

Warranty Booklet Yes

### Certification

ENERGY STAR Certification Yes

CCC

Yes TCO 9.0

TCO Edge 2.0

**EPEAT** Gold

Volatile Organic Compound Certification Yes

RoHS (2011/65/EU)

Windows Certification
Windows 10. Windows 11

China Energy Efficiency Standard

Tier 1

TÜV Rheinland Eye Comfort Yes

TÜV Rheinland Low Blue Light Yes

**TÜV Rheinland Flicker Free** Yes

TÜV Low Blue Light (Hardware Solution)

Eyesafe Display Certification




























o 2022 Lenovo. All rights reserved. These products are available while supplies last. Prices shown are subject to change without notice. For any questions concerning price, please contact your Lenovo Account Executive. Lenovo is not responsible for photographic or typographic errors. Warranty: For a copy of applicable warranties, write to: Warranty Information, 500 Park Offices Drive, RTP, NC 27709, U.S.A, Attn: Dept. ZPYA/B600. Lenovo makes no representation or warranty regarding third-party products or services. Trademarks: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkVantage, ThinkVision, and ThinkColour are trademarks or registered trademarks of Lenovo. Microsoft, Windows, and Vista are registered trademarks of Corporation. Intel, the Intel logo, Intel Inside, Intel Core, and Core Inside are trademarks of Intel Corporation in the U.S. and/or other countries. Other company, product, and service names may be trademarks of others.

Smarter technology for all











