

### H1000 USB-C On-Ear Headset

Part Number: K83450WW | UPC Code: 0 85896 83450 2

## All day productivity.

If you wear your headset for hours on end throughout the workday, you need a comfortable design with professional features that maximize your productivity.

Kensington's universal plug & play H1000 USB-C Headset delivers premium productivity, comfort, and durability for an advanced audio experience. With a noise-canceling microphone, LED indicators for "busy" and mute, sidetone for better call engagement, and in-line music controls, the H1000 is designed to enhance your audio experience.

The H1000 is part of Kensington's Professional Video Conferencing ecosystem—providing an integrated experience so you spend more time being productive.

#### Features include:

- Works with Microsoft Teams, Zoom, Windows, macOS, Chrome OS and more
- Ergonomic on-ear design for all day comfort
- 270° rotating microphone can be worn on either the left or right
- Directional noise-canceling (DNC) microphone suppresses distracting sounds
- Quick access to volume, play/pause, mute, and busy buttons
- · Integrated busy light to minimize colleague interruptions
- Long 6ft (1.8m) USB-C cable provides freedom to stand during extended calls

# Kensington

#### H1000 USB-C On-Ear Headset

Part Number: K83450WW | UPC Code: 0 85896 83450 2



Plug & Play

Works with popular calling applications (Microsoft Teams, Zoom, and more) and operating systems (Windows, macOS, and Chrome OS).



**All-Day Comfort** 

Lightweight ergonomic on-ear design with adjustable leatherette headband, comfortable earpads, a rotating microphone (up to 270°) that can be worn on the right or left side, and a comfortable secure fit.



#### Advanced Sound Technology

A directional noise-canceling (DNC) microphone suppresses distracting sounds such as keyboard clicks and nearby voices, sidetone confirms you are being heard, and 40mm drivers deliver an advanced audio experience with HD voice support.



Pro In-Line Controls with LED Lights

Quick access to the volume, play/ pause, mute and integrated busy light buttons help you maximize productivity, while LED indicators provide reassuring visual confirmation of your status so you can stay focused.



Integrated Busy Light

The LED indicator on the back of the microphone turns red when activated to minimize colleague interruptions and maximize productivity.



6ft (1.8m) USB-C Cable

A long 6ft (1.8m) tangle-free nylon braided USB-C cable provides the dependability of a wired connection and the freedom to stand and stretch during extended calls.



## H1000 USB-C On-Ear Headset

Part Number: K83450WW | UPC Code: 0 85896 83450 2

#### Audio Specifications

|                        | Speaker Size               | 40mm Ø  |  |  |
|------------------------|----------------------------|---|--|--|
|                        | Speaker Impedance          | 32Ω ± 15%<br>102 ± 5dB (Input Power = 1mW at 1kHz)<br>10mW  |  |  |
|                        | Speaker Sensitivity        |   |  |  |
|                        | Rated Input Power          |   |  |  |
|                        | Maximum Input Power        | 30mW  |  |  |
|                        | Speaker Frequency Response | 20Hz - 20kHz  |  |  |
|                        | Microphone Type            | 1 directional microphone  |  |  |
|                        | Microphone Sensitivity     | -40 ± 3dB at 1kHz (0dB = 1V/Pa)   |  |  |
|                        | Microphone Frequency Range | 300-5kHz  |  |  |
|                        | Microphone Current         | 0.5μA max   |  |  |
| Product Specifications |                            |   |  |  |
|                        | Unit Dimensions            | 6.7 x 7.5 x 1.3in (170 x 191 x 33mm)  |  |  |
|                        | Inline Control Unit        | Volume adjustment, mute/unmute, busy light, play/pause  |  |  |
|                        | Rotatable Microphone       | 270°  |  |  |
|                        | Unit Weight                | 0.42lbs (0.19kg)  |  |  |
|                        | USB Cable Length           | 6ft (1.8m)  |  |  |
|                        | Color and Material         | Black/ABS housing<br>Braided cable<br>Inline control unit: PC, TPU, ABS<br>Headband cushion: PU, foam |  |  |
| Packaging Dimensions   |                            |   |  |  |
|                        | Packaging Style            | Brown box with retail sleeve  |  |  |
|                        | Packaging Dimensions(Unit) | 8.27 x 7.17 x 3.35in (210 x 182 x 85mm)   |  |  |
|                        | Packaging Weight(Unit)     | 0.62lbs (0.28kg)  |  |  |
|                        | Master Carton              | 5 pcs   |  |  |
|                        | Packaging Content          | Headset, Welcome Insert, Quick Instruction Guide<br>Warranty Card, Compliance Sheet                   |  |  |







## H1000 USB-C On-Ear Headset

Part Number: K83450WW | UPC Code: 0 85896 83450 2

| _            | 0  | _       |           |   |  |
|--------------|----|---------|-----------|---|--|
| DOMAG        | Χı | Ln۱     | /Iron     | mental                                  |  |
| 1 () () () ( | (X | 1 1 1 1 | /     ( / | 111111111111111111111111111111111111111 |  |

| TOWER & LITVITOTITE | iciitai                     |  |  |  |
|---------------------|-----------------------------|--|--|--|
|                     | Storage Temperature         | -40 to 60°C (-40 to 140°F)<br>-30 to 50°C (-22 to 122°F)<br>20% to 80% non-condensing                                |  |  |
|                     | Working Temperature         |  |  |  |
|                     | Relative Humidity           |  |  |  |
| Country of Origin,  | Regulatory, and Warranty    |  |  |  |
|                     | Country of Origin           | China FCC, IC, CE, UKCA, RCM, VCCI, Sound Pressure Level Test EN 50332-2, EU REACH, RoHS/WEEE, CA Prop 65, ACCO RSL. |  |  |
|                     | Certifications & Compliance |  |  |  |
|                     | Warranty                    | 2-Year limited   |  |  |
|                     |                             |  |  |  |



