



Simple, speedy, mobile-ready printing.

Introducing the Visioneer® Rabbit™ PC30dwn Printer/Copier. From Visioneer Inc., world-class developer of intelligent document capture solutions, the Rabbit™ PC30 is all about making the print experience quick and easy on any device, at home or in the office. For education, legal, financial services, manufacturing and government settings, the Rabbit™ PC30dwn provides versatility and value.

The monochrome laser Rabbit™ PC30dwn features LED print head technology with automatic double-sided (duplex) printing capability. With print speeds up to 30 pages per minute, Rabbit™ PC30dwn supports USB 2.0, Gigabit Ethernet and WiFi connectivity options for pain-free sharing. A 250-sheet input tray keeps you productive, while a sheet-fed manual tray handles special print jobs. The included convenience copier module makes document, card stock and plastic card copying a snap.

We know creativity comes in all shapes and sizes – and so do the tools we use to create. Your Rabbit™ PC30dwn printer is compatible with Windows®, Mac® and Linux® Ubuntu op-

erating systems, and mobile-ready for use with Mopria® Print Service and Apple® AirPrint. Full-version ABBYY® FineReader® PDF software is also included with your Rabbit™ PC30dwn, to create, edit, secure-sign, and search PDFs.

It is your creativity and productivity that matters most. Whether you're a student or educator, work from home or office or both, the Rabbit™ PC30dwn provides the versatility and ease-of-use you need. At Visioneer, we make the sharing part simple, so you can **#CreateAndGo**.



Included convenience copier module quickly copies documents, postcards, ID cards and more.

Visioneer® Rabbit™ PC30dwn Printer/Copier

SPECIFICATIONS

Model name	Visioneer Rabbit PC30dwn Printer/Copier		
Model number	92-0006		
Print technology	Laser (LED print head)		
Function	Print, copy		
Device color	White, black		
Print color	Monochrome		
Print speed	Simplex: 30 ppm; Duplex: 9 ppm/18 ipm		
Main paper tray capacity	250 sheets (70 g/m ² , plain paper)		
Manual paper tray	Sheet-fed		
Duplex printing	Automatic		
Operation panel	LED + buttons		
CPU	500 MHZ		
Memory	512 MB		
Printer language	GDI, PCL6		
Connectivity	USB 2.0, LAN 10/100/1000, WiFi 802.11 a/b/g/n/ac		
Supported operating systems	Windows 7, 10, 11; MacOS 11, 12, 13		
Drivers	Windows®, Linux®		
Mobile print compatibility	Apple® AirPrint, Mopria® Print Service (Android)		
Included software	ABBYY® FineReader® PDF for Windows or Mac		
Min/Max print size	Min: 3" x 5" (76 x 127mm); Max: 8.5" x 14" (216 x 356mm)		
Min/Max copy size	Min: 2" x 2" (51 x 51mm); Max: 8.5" x 14" (216 x 356 mm)		
Image processing functions	Crop, de-skew, blank page detection		
Copier image sensor	CIS		
Copier light source	LED		
Print resolution	600 dpi, 1200 dpi (enhanced mode)		
Copy resolution	600 dpi		
Printer dimensions	15.9" x 15" x 8" (404 x 380 x 204mm)		
Printer weight	18.7 lbs. (8.5kg)		
Monthly Duty Cycle	5,000 impressions		
System requirements	PC <ul style="list-style-type: none">• Intel i3 or equivalent CPU• 2 GB System Memory (RAM)• 350 MB Available HD Space• 1 GB HD Space for each additional app• USB 2.0 or 3.x Port• Windows 7 32-bit or later	Mac <ul style="list-style-type: none">• Intel i3 or equivalent CPU• 2 GB System Memory (RAM)• 350 MB Available HD Space• 1 GB HD Space for each additional app• USB 2.0 or 3.x Port• Mac OS X 10.14 or later	

Box contents: Visioneer Rabbit PC30dwn Printer/Copier, toner cartridge & drum unit, power supply and adapter, USB cable, Ethernet cable, Quick Install guide, warranty and registration cards

For more information about Visioneer products visit www.visioneer.com

©2022 Visioneer Inc. All rights reserved. Visioneer® and Rabbit™ are trademarks of Visioneer. All other trademarks are the property of their respective owners and are hereby acknowledged. Prices, features, applications, capabilities, appearance and availability of Visioneer products and services are subject to change without notice. 12/22

visioneer