



SPECIFICATIONS


Panel Size	23.8"
Panel Resolution	1920 x 1080 (Full HD)
Refresh Rate	60Hz
Response time	7ms
Panel Type	IPS
Type / Size	34"
Brightness (nits)	220 cd/m2
Viewing Angle	178°(H) / 178°(V)
Aspect Ratio	16:9
Curvature	Flat
Contrast Ratio	1000:1 (TYP)
Active Display Area (mm)	527.04(H) x 296.46(V)
Pixel Pitch (H x V)	0.2745(H) x 0.2745(V)
Surface Treatment	Anti-glare
Display Colors	16.7M
Video ports	1x HDMI (1.4) 1x D-Sub (VGA)
Kensington Lock	Yes
VESA Mounting	75 x 75 mm
Power Type	External Adaptor 12V 2.5A
Power Input	100~240V, 50~60Hz
VIDEO INTERFACE	1x DP(1.4) 2x HDMI (2.0) 1x Type C (DP)
sRGB	102% (CIE 1976)
PANEL SIZE	27"
Color Bit	6 bits + FRC
Operating System	Windows 10 Home - MSI recommends Windows 10 Pro
CPU	Up to the 9th generation Intel® Core™ i7 processors
PANEL RESOLUTION	1920 x 1080 (FHD)
REFRESH RATE	75Hz
AUDIO INTERFACE	1x Mic-in 1x Headphone-out 1x Audio combo
RESPONSE TIME	5ms (GTG)
Chipset	Intel® H310

FEATURES



VESA Mountable

To be mounted on the wall of your office & home with a VESA standard design which can make it completely invisible on a desk.



Display Kit Support

Providing the most convenient tool, the proper color & display mode to you while working with it everyday.



IPS Grade Panel

Instantly optimize the screen colors and brightness to ensure that you enjoy every detail at its best while creating your own on-line video



Full HD Resolution


Experience a breathtaking screen clarity that comes with Full HD (1920x1080) resolution



Anti-Glare Display Design

An anti-glare display makes viewing the display more pleasant for users and reduces eyestrain for users

Anti-Glare



23.8" Screen Size

View your applications, spreadsheets and more with a perfect 23.8 inches screen

System Memory	2 x U-DIMMs DDR4 2400/2666MHz Max. 32G
PANEL TYPE	IPS
BRIGHTNESS (NITS)	250 cd/m2
VIEWING ANGLE	178°(H) / 178°(V)
Sound	7.1 Channel HD Audio (Realtek ALC887)
Adjustment (Tilt)	-5° ~ 15°
Storage	1 x M.2 SSD (1 x Auto Switch)□ 2 x 3.5" HDD
ASPECT RATIO	16:9
CONTRAST RATIO	1000:1
sRGB	100% (CIE 1976)
ACTIVE DISPLAY AREA (MM)	597.888(H) x 336.312(V)
Wireless LAN	Intel® Wireless-AC AC3168 (Optional)
PIXEL PITCH (H X V)	0.3114(H) x 0.3114(V)
Bluetooth	4.2 (Optional)
SURFACE TREATMENT	Anti-glare
DISPLAY COLORS	16.7M
Dimension (W x H x D)	541.04 x 416.26 x 180.80 mm (21.30 x 16.39 x 7.12 inch)
COLOR BIT	8 bits
Carton Dimension (W X H X D)	627 x 405 x 122 mm (24.69 x 19.94 x 4.80 inch)
I/O (Front)	2 x USB 2.0□ 1 x Headphone Out□ 1 x Microphone
Weight (NW / GW)	2.61kg (5.75lbs) / 3.78kg (8.33lbs)
VIDEO PORTS	1x DisplayPort (1.2a) 1x HDMI (1.4)
I/O (Rear)	2 x USB3.1 Gen1 Type A 4 x USB2.0□ 1 x RJ45□ 1 x DVI-D 1 x VGA 1 x HDMI port 1 x PS/2 mouse/keyboard combo□ 3 x Audio Jacks
AUDIO PORTS	1x Headphone-out
LAN	Intel® WGI219V
KENSINGTON LOCK	Yes
AC Adapter / PSU	300W 80 Plus Bronze certified (TFX)
SPEAKER	2x 2W
Cooling System	Fan Cooler
Volume	13L / 22.87pt
VESA MOUNTING	75 x 75 mm
POWER TYPE	External Adaptor (12V 2.5A)
Dimension (WxDxH)	420.2 x 163.5 x 356.8mm□(16.54 x 6.44 x 14.05 inch)
WEIGHT (N.W./ G.W.)	6.36 kg (14.02 lbs) / 8.36 kg (18.43 lbs)
POWER INPUT	100~240V, 50~60Hz
ADJUSTMENT (TILT)	-5° ~ 20°
DIMENSION (W X H X D)	613.50 x 181.10 x 462.60 mm (24.15 x 7.13 x 18.21 inch)
CARTON DIMENSION (W X H X D)	687 x 119 x 458 mm (27.05 x 4.69 x 18.03 inch)
Accessories	1 x Warranty card□ 1 x Quick guide 1 x Power cord
WEIGHT (NW / GW)	3.9 kg (8.6 lbs) / 5.3 kg (11.68 lbs)
Compatibility	PC, Mac, PS5™, PS4™, Xbox, Mobile, Notebook * All trademarks and the registered trademarks are the property of their respective owners.

NOTE	HDMI: 1920 x 1080 (Up to 75Hz) DisplayPort: 1920 x 1080 (Up to 75Hz) FreeSync Support
Note	HDMI: 1920 x 1080 (Up to 60Hz) D-Sub: 1920 x 1080 (Up to 60Hz)

CONNECTIONS



1. 1x HDMI (1.4)
2. 1x D-Sub(VGA)
3. 1x DC Jack
4. 1x Kensington Lock