



SPECIFICATIONS

Panel Size	31.5" (80cm)
Active Display Area (mm)	698(H)x393(V)
Curvature	1500R
Panel Type	VA
Panel Resolution	1920x1080 (FHD)
Pixel Pitch (H x V)	0.364(H)x0.364(V)
Aspect Ratio	16:9
Brightness (nits)	250
Contrast Ratio	3000:1
DCR	10000000:1
Signal Frequency	53~91.5 KHz (H) / 48~75 Hz (V)
Refresh Rate	75Hz
Response time	1ms(MRPT)
Video ports	1 x Display Port (1.2a) 1 x HDMI (1.4b)
Audio ports	1x Headphoneout
Viewing Angle	178°(H)/178°(V)
Adobe RGB / DCI-P3 / sRGB	82%/77%/98%
Surface Treatment	Anti-glare
Display Colors	16.7M
Power Type	External Adaptor 12V 4A
Power Input	100~240V
Adjustment (Tilt)	-5° ~ 20°
Adjustment (Swivel)	-30° ~ 30°
Adjustment (Pivot)	N/A
Adjustment (Height)	N/A
Kensington Lock	Yes
Dimension (W x D x H)	709.4 x 263.5 x 519.1mm 709.4x 93.7 x 419.1mm(without stand)
Carton Dimension (W X D X H)	WW:960 x 160 x 489mm Outer:970 x 170 x 509mm
Frameless Design	Yes
VESA Mounting	100 x 100 mm
Weight (NW / GW)	5.3kg / 7.3kg
Note	Display Port:1920 x 1080 (75Hz) HDMI: 1920 x 1080 (75Hz) Adobe RGB, DCI-P3 and sRGB follow CIE1976 Standard

FEATURES



1500R

Enjoy the most immersive gameplay with 1500R curvature rate.



1ms Fast Response Time

Eliminate screen tearing and choppy frame rates with 1ms response time.



Night Vision

See every detail clearly in the dark, helping you find and attack enemies before they notice.



Wide Color Gamut

Game colors and details will look more realistic and refined, to push game immersion to its limits.



Frameless Design

With the narrow bezel, you will not even notice the monitor at all in the heat of the moment.

CONNECTIONS



1. 5-way joystick navigator
2. DC-in
3. 1 x Display Port (1.2a)
4. 1 x HDMI (1.4b)
5. Headphone-out
6. 1x Kensington Lock