

# Extension Cord Y Splitter, NEMA 5-15P to 2x NEMA 5-15R - 13A, 125V, 16 AWG, 1 ft. (0.3 m), Black

MODEL NUMBER: P022-001-13A-2











### **Highlights**

- Connects 2 devices to one AC outlet to save space and reduce cable clutter
- Recommended for powering dual computers, monitors or other compatible peripherals
- Adds 1 ft. to your existing power connection to provide flexibility in placing devices
- NEMA 5-15P plug connects to AC power; 5-15R ends connect to devices' cords

## **Package Includes**

P022-001-13A-2 Extension Cord Y Splitter, 1 ft. (0.3 m), Black

Extension cord splitter allows two devices with NEMA 5-15P plugs to share one AC power input cord and one NEMA 5-15R outlet.

#### **Features**

#### Y-Style Power Cord Splitter Connects 2 Devices with 5-15P Plugs to One AC Outlet

This extension cable splitter allows two devices with NEMA 5-15P plugs to share one AC input cord and one NEMA 5-15R outlet. The AC power splitter features a 5-15P plug for connecting to an AC power source and two 5-15R ends for connecting to devices' power cords. By connecting two devices to one outlet, the splitter frees up space in a PDU or surge protector and allows extra flexibility in placing equipment with respect to the power outlet.

#### **Dual Cable Powers a Wide Variety of Essential Electronics**

With this extension cord splitter, a single NEMA 5-15R outlet can power two devices, such as computers, monitors, printers, instrument amplifiers and other equipment compatible with a NEMA 5-15P plug. Ideal for areas where AC outlets are limited, such as rack cabinets, this extension cord Y splitter is compatible with power and extension cords.

# **Specifications**

OVERVIEW		
UPC Code	037332275189	
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU	
Country/Region	North America	
INPUT		
Maximum Input Amps	13	
Voltage Compatibility (VAC)	125	



PHYSICAL			
Plug Color	Black		
Cable Jacket Color	Black		
Cable Jacket Rating	FT2		
Power Cord Jacket Type	SJT		
Cable Outer Diameter (OD)	8.3 mm		
Number of Conductors	3		
Wire Gauge (AWG)	16		
Wire Gauge (OD - mm²)	1.31		
Cable Length (ft.)	1		
Cable Length (m)	0.30		
Shipping Dimensions (hwd / in.)	9.98 x 7.08 x 0.50		
Shipping Dimensions (hwd / cm)	25.35 x 17.98 x 1.27		
Shipping Weight (lbs.)	0.22		
Shipping Weight (kg)	0.10		
ENVIRONMENTAL			
Operating Temperature Range	-4° to 140°F (-20° to 60°C)		
Storage Temperature Range	-4° to 140°F (-20° to 60°C)		
Operating Humidity Range	20% TO 80% RH, NON-CONDENSING		
Storage Humidity Range	20% to 80% RH, Non-Condensing		
CONNECTIONS			
Side A - Connector 1	NEMA 5-15P		
Side B - Connector 1	(2) NEMA 5-15R		
FEATURES & SPECIFICATIONS			
Antibacterial	No		
Angled Plug	No		
High Voltage	No		
Locking Plug	No		
Coiled Power Cord	No		
STANDARDS & COMPLIANCE			
Product Certifications	cUL Listed; UL Listed		
Product Compliance	RoHS; REACH		



WARRANTY & SUPPORT	RRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty	



© 2023 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.