

Power Extension Cord, NEMA 5-15P to NEMA 5-15R - 13A, 120V, 16 AWG, 15 ft. (4.6 m), Black

MODEL NUMBER: P022-015-13A



13-amp extension cord connects two devices with 5-15P/5-15R power connectors or extends your existing power connection.

Features

15-Foot Extension Cord Connects Monitors, Printers, Servers and Other Equipment

This power extension cable is designed for small data center or office workstation applications that do not require a heavy-gauge connection. With a NEMA 5-15P plug on one end and a NEMA 5-15R receptacle on the other, this UL listed (UL 817) cord can be used to power a printer or monitor, attach a rack server to a PDU or extend an existing connection up to 15 feet (4.6 meters). The 15-foot length allows you more flexibility in placing equipment with respect to the power outlet.

Specifications

OVERVIEW	
UPC Code	037332275233
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	13
Voltage Compatibility (VAC)	125
PHYSICAL	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC

Highlights

- Recommended for powering printers, monitors and other essential peripherals
- Ideal for home/office applications, small server rooms and data centers
- Adds 15 ft. to your existing connection to provide more flexibility in placing devices
- UL listed cable is ideal replacement for worn-out or missing extension cord

Package Includes

P022-015-13A Power Extension Cord, NEMA 5-15P to NEMA 5-15R, 15 ft. (4.6 m), Black

Cable Jacket Rating	FT2
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	8.3mm
Number of Conductors	3
Wire Gauge (AWG)	16
Wire Gauge (OD - mm ²)	1.31
Cable Length (ft.)	15
Cable Length (m)	4.57
Shipping Dimensions (hwd / in.)	14.17 x 11.80 x 0.50
Shipping Dimensions (hwd / cm)	35.99 x 29.97 x 1.27
Shipping Weight (lbs.)	1.05
Shipping Weight (kg)	0.48
ENVIRONMENTAL	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	20% TO 80% RH, NON-CONDENSING
Storage Humidity Range	20% to 80% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	NEMA 5-15R
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	No
Locking Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



1000 Eaton Boulevard
Cleveland, OH 44122
United States



© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.