

Mini Bluetooth 5.0 (Class 2) USB Adapter

MODEL NUMBER: **U261-001-BT5**



Connects Bluetooth 5.0 wireless keyboards, mice, headsets, printers, smartphones and tablets to your computer's USB-A port.

Features

Add Bluetooth 5.0 Wireless Capability to Your Computer or Laptop

This low-profile Bluetooth 5.0 (Class 2) USB adapter connects to your PC or laptop's USB-A port to provide instant Bluetooth wireless capability. Compliant with Bluetooth 5.0 LE+EDR Class 2 standards, the U261-001-BT5 is ideal for wireless communication between your computer and up to seven Bluetooth 5.0 devices at the same time, including smartphones, tablets, keyboards, mice, headsets and printers.

Broadcasts a Wireless Signal up to 165 ft.

The USB adapter has a wireless range up to 165 feet (50 meters) and supports data transfer speeds up to 3 Mbps. Built-in security measures ensure your pairing, encryption and authentication information remains private.

Convenient Low-Profile Design Keeps You Connected as Long as You Like

This Bluetooth adapter protrudes less than 3/16 of an inch (about five millimeters) from the USB port, so it can remain connected while your laptop is inside a sleeve, briefcase or backpack. It's backward compatible with previous Bluetooth versions, so you can use the adapter to connect older devices.

Highlights

- Adds fast, reliable Bluetooth 5.0 LE+EDR Class 2 accessibility to your PC or laptop
- Supports data transfer speeds up to 3 Mbps to a wireless range up to 165 ft.
- Connects up to 7 devices simultaneously, including printers, speakers and headsets
- Backward compatible with previous Bluetooth versions, including 1.1, 1.2, 2.0, 3.0 and 4.0
- Built-in security keeps your pairing, encryption and authentication info confidential

System Requirements

- Computer with USB-A port
- Windows 8, 10 or 11 or Linux operating system

Package Includes

- U261-001-BT5 Mini Bluetooth 5.0 USB Adapter
- Quick Start Guide

Specifications

OVERVIEW	
UPC Code	037332272676
Technology	USB 2.0 (High Speed)
INPUT	
Bus Powered	Yes
POWER	



Power Consumption (Watts)	0.50
PHYSICAL	
Color	Black
Material of Construction	Steel, PVC
Unit Dimensions (hwd / in.)	0.240 x 0.540 x 0.740
Unit Dimensions (hwd / cm)	0.63 x 1.38 x 1.89
Unit Packaging Type	Box
Unit Weight (lbs.)	0.004
Unit Weight (kg)	0.00
ENVIRONMENTAL	
Operating Temperature Range	32 to 122 F (0 to 50 C)
Storage Temperature Range	-4 to 158 F (-20 to 70 C)
BTUs	1.2 BTU/Hr
Operating Humidity Range	20% to 90% RH, Non-Condensing
Storage Humidity Range	20% to 90% RH, Non-Condensing
COMMUNICATIONS	
Signal Range (ft.)	164
Signal Range (m)	50
Bluetooth Class	Class 2
Bluetooth Version	5.0
Modulation Type	GFSK (1MBPS), /4-DQPSK (2MBPS) and 8-DPSK (3MBPS)
Spread Spectrum	Frequency Hopping Spread Spectrum (FHSS)
RF Power Output	3.06dBm, GFSK
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
Driver Required	Yes
STANDARDS & COMPLIANCE	
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS; UKCA; WEEE
WARRANTY	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Warranty Period (Worldwide)	3-year limited warranty
----------------------------------------	-------------------------

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>