

USB Car Charger - 25W PD Charging, USB-C, Black

MODEL NUMBER: U280-C01-25-1B











Highlights

- 25W USB-C charger connects to the 12V DC power outlet in your car, truck or SUV
- Ideal for charging smartphones, tablets, e-readers and notebooks while traveling
- Prevents overheating and overcharging to shield your connected device from damage
- USB-C Power Delivery 3.0 port charges up to 4x faster than conventional USB chargers

Package Includes

U280-C01-25-1B USB Car Charger, Black

Quickly and safely charges and powers your tablet, smartphone or other compatible USB-C device from your vehicle's dashboard.

Features

USB Car Charger Safely Charges a Mobile Device While You're on the Move

This single-port USB-C car charger with Power Delivery (PD) 3.0 technology quickly and safely charges your smartphone, tablet, notebook, e-reader or power bank to ensure satisfactory battery charge when you reach your destination. The U280-C01-25-1B is compatible with Apple (including iPhone), Android (including Samsung), Windows and Amazon devices with USB-C or Thunderbolt 3 charging ports.

Plugs into the 12V DC Power Outlet in Your Vehicle

The compact charger connects to any standard 12V DC vehicle power outlet, such as the one on your dashboard. Just plug it in and connect your device's USB cable for fast, convenient mobile charging.

Specifications

OVERVIEW		
UPC Code	037332275332	
Product Type	Car Charger	
Charging Form Factor	Direct Plug-In	
Device Compatibility	Amazon Kindle; Chromebook; Laptop; Phone; Tablet	
Technology	USB	
INPUT		
Nominal Input Voltage(s) Supported	12V DC	
Input Connection Type	Automatic Vehicle Cigarette Lighter	



Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240	
Input Plug Type	Car Auxiliary Power Outlet	
OUTPUT		
Output Capacity (Watts)	25	
Overload Protection	Yes	
Overload i fotocilori	103	
POWER		
USB Power Delivery (PD) Charging Support	Yes	
USB Power Delivery (PD) Charging Specification	3.0	
CHARGING		
Number of Charging Ports	1	
Total Charging Amps	3A	
Total Charging Watts	25	
Charging Method	USB	
Charging Method Detail	USB-C PD 3.0 Charging up to 25W	
Charging Port Type	USB C (FEMALE)	
Charging Ports Details	5V 3A (15W), 9V 2.77A (25W) - PD 3.03.3V-5.9V 3A, 3.3V-11V 2.25A (25W) - PPS	
Charging Ports / Amps	3A	
Compatible Devices	Portable Speaker; Smartphone; Tablet	
PHYSICAL		
Color	White	
Material of Construction	Polycarbonate	
Unit Dimensions (hwd / in.)	5.560 x 2.960 x 2.640	
Unit Dimensions (hwd / cm)	2.19 x 1.17 x 1.04	
Unit Packaging Type	Polybag	
Unit Weight (lbs.)	0.04	
Unit Weight (kg)	0.02	
ENVIRONMENTAL		
Operating Temperature Range	32° to 104°F (0° to 40°C)	
Storage Temperature Range	-4° to 176°F (-20° to 80°C)	
Operating Humidity Range	20 to 90% RH, Non-Condensing	
Storage Humidity Range	5 to 90% RH, Non-Condensing	



CONNECTIONS		
Number of Ports	1	
Side A - Connector 1	Car Cigarette Lighter	
Side B - Connector 1	USB C (FEMALE)	
FEATURES & SPECIFICATIONS		
GaN Technology	No	
Overcurrent Protection	Yes	
Overvoltage Protection	Yes	
Over Current Protection	Yes	
Driver Required	No	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS; CE (Europe); REACH; WEEE; FCC (USA)	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	1-year limited warranty	



© 2023 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.