

Manufacturer Part #	RaiderGE7612655
OS	Windows 11 Pro
CPU	Core i9-12900HK 6+8Core
CPU Speed	1.8-5 GHz
Color	Titanium Blue
Screen Size	17.3" Thin Bezel FHD, IPS-Level 144Hz, 100% sRGB
Resolution	1920x1080 (16:9)
GPU	NVIDIA® GeForce RTX™ 3080 Laptop GPU Up to 1740MHz Boost Clock, 155W Maximum Graphics Power with Dynamic Boost. *May vary by scenario
Video Memory	8G GDDR6
Keyboard	Steel Series per-Key RGB with Anti-Ghost key (102 Key)
Audio	Nahimic 3 / Hi-Res Audio
Speaker	Sound by Dynaudio, 2x2W Speaker + 2x1W woofer
Memory	32GB (16G*2) DDR5 4800MHz
HDD Capacity	1TB+512GB NVMe SSD Gen4x4
HDD Interface	NVMe
LAN	Killer E3100G
WLAN	Killer WiFi 6E AX1675 (2x2)
Bluetooth	BT 5.2
Card Reader	SD7.0
Webcam	1080p FHD Webcam
USB	1x USB3.2 Gen 2; 2x USB3.2 Gen 1
Type-C Port	1x Thunderbolt™ 4; 1x USB 3.2 Gen 2/DP
Video Port	1x (8K @ 60Hz / 4K @ 120Hz) HDMI ; 1x Mini-DisplayPort
Audio Port	1 Audio Combo (1/8")
AC Power Adaptor	330W
Battery Pack	4 cell (99.9Whr)
Dimension	15.63"x 11.18"x 1.02"
Weight	6.39 lbs
Manufacturer Warranty	3 year on site warranty+ADP
Accessories	With Backpack