

GCS72CC

## 2-Port 4K USB-C KVM Switch with DisplayPort output



- One USB keyboard, mouse and one DisplayPort monitor control two USB-C computers
- Superior video quality – up to 4K DCI (4096 x 2160 @ 60Hz)
- Computer selection via remote port selector
- DisplayPort 1.2 compliant
- Supports USB hot-plugging
- The console USB ports can be used for USB peripheral sharing
- Multiplatform support – Windows, Mac and Linux
- Plug and play
- Bus-powered – no external power adapter required


### Flexible and Expandable

The 2-port 4K KVM Switch with displayPort/USB-C and Audio is designed with displayPort 1.2 technology, perfect for those who need to get the job done in the office and at home.

Need more USB ports? No problem! Plug in a USB hub to expand your peripheral sharing between your computers.

- |  |  |
|--|--|
| <ul style="list-style-type: none"> <li>• One USB keyboard, mouse and one DisplayPort monitor control two USB-C computers</li> <li>• Superior video quality – up to 4K DCI (4096 x 2160 @ 60Hz)</li> <li>• Computer selection via remote port selector</li> <li>• DisplayPort1.2 compliant</li> </ul> | <ul style="list-style-type: none"> <li>• Supports USB hot-plugging</li> <li>• The console USB ports can be used for USB peripheral sharing</li> <li>• Multiplatform support – Windows, Mac and Linux</li> <li>• Plug and play</li> <li>• Bus-powered – no external power adapter required</li> </ul> |
|--|--|





## Requirements

## Package Contents

### Console

- DisplayPort monitor
- Standard 104-key wired USB keyboard
- Standard 2 or 3 button wired USB mouse

- 1x GCS72CC
- 1x Quick Start Guide
- 1x Warranty Card

### Computers

- USB Type-C port

### Operating Systems

- Windows<sup>®</sup>7, 8.1, 10, 11
- Mac OS X 9.0+
- Linux<sup>®</sup>, UNIX<sup>®</sup>, and other USB supported systems

## Specifications

Function	GCS72CC	Dimensions	GCS72CC
<b>Computer Connections</b>		<b>Unit Package Dimensions</b>	
Direct	2	Height	8.75 in (22.3 cm)
<b>Port Selection</b>		Length	2.25 in (5.7 cm)
	Remote Port Selector	Width	6.25 in (15.9 cm)
<b>Console Connectors</b>		<b>Master Carton</b>	
Monitor	1 x DisplayPort	Height	7.25 in (18.4 cm)
Keyboard	1 x USB Type A	Length	15.2 in (38.6 cm)
Mouse	1 x USB Type A	Width	8.13 in (20.6cm)
<b>CPU Connectors</b>		Master Carton Qty.	6
Keyboard, Mouse, and Monitor	2x USB Type-C	<b>Weight</b>	
<b>LEDs</b>		Master Carton Wt.	4.75 lb (2.16 kg)
KVM	2 x White	Unit Pack Wt.	0.7 lb. (0.3 kg)
<b>Emulation</b>			
Keyboard	Pass Through		
Mouse	Pass Through		
<b>Video Resolution</b>			
	up to 4096 x 2160 @60Hz		
<b>Environment</b>			
Operation Temperature	32~122 F(0~50C)		
Storage Temperature	-4~140F (-20~60C)		
Humidity	0~80% RH, Non-condensing		
<b>Housing</b>			
Case	Plastic		
<b>Cable Length</b>			
	4 ft.		