

## EH412STx

Short throw, bright and compact projector





- Bright Full HD 1080p projector 4000 lumens for use any time of day
- Short throw lens 100" image from just a few feet away
- Easy connectivity HDMI and USB power
- Clear, powerful audio Built-in 10W speaker



Project bright, vibrant presentations effortlessly in Full HD 1080p any time of day. Designed for small meeting rooms and classrooms, this short throw projector boasts amazing color, long lamp life and energy-saving features to provide a lower overall cost of ownership.

Multiple inputs, USB power and a built-in speaker provide an easy set-up - perfect for connecting a laptop, PC or Blu-ray player for clear projected images with sound. You can even use the USB power to connect and power HDMI dongles such as Google Chromecast.

Portable and lightweight this compact projector can be installed or taken on the move for off-site meetings.

## **Specifications**

UPC - 796435 44 605 5	
Display/image	
Display technology	DLPTM
Resolution	1080p Full HD (1920x1080)
Brightness	4,000 lumens
Contrast ratio	50,000:1
Native aspect ratio	16:9
Aspect ratio - compatible	4:3,16:9
Keystone correction - vertical	+/-40°
Horizontal scan rate	15.38 ~ 91.15Khz
Vertical scan rate	50 ~ 85(120 for 3D)Hz
Uniformity	70%
Screen size	36.2" ~ 307.8" diagonal
Lamp info	30.2 * 007.0 Glagonal
	Lamp
Light source type	
Lamp watts	240 4000 (Drinkt) 10000 (Dringersin) 10000 (Eas) 15000 (Easi)
Lamp life hours (up to)	4000 (Bright), 12000 (Dynamic), 10000 (Eco), 15000 (Eco+)
Optical	0.40.4
Throw ratio	0.49:1
Projection distance	15.75" - 133.86"
Focal length (mm)	7.42mm/0.292"
Native offset	116%
Connectivity	
Connections	Inputs 1 x HDMI 2.0, 1 x HDMI 1.4a 3D support + MHL
	Outputs 1 x Audio 3.5mm, 1 x USB-A power 1.5A
	Control 1 x RS232
General	
Noise level (typical)	26dB
Noise level (max)	28dB
PC compatibility	2006 UHD, WUXGA, FHD, UXGA, SXGA, WXGA, HD, XGA, SVGA,
- o compaubility	VGA, Mac
2D compatibility	NTSC M/J, 3.58MHz, 4.43MHz PAL B/D/G/H/I/M/N, 4,43MHz
	SECAM B/D/G/K/K1/L, 4.25/4.4MHz 480i/p, 576i/p,
	720p(50/60Hz), 1080i(50/60Hz), 1080p(50/60Hz)
3D compatibility	Side-by-Side:1080i50 / 60, 720p50 / 60 Frame-pack:
	1080p24, 720p50 / 60 Over-Under: 1080p24, 720p50 / 60
3D	Full 3D
Security	Security bar, Kensington Lock, Password protected interface
OSD / display languages	25 languages: Arabic, Czech, Danish, Dutch, English, Farsi,
	Finnish, French, German, Greek, Hungarian, Indonesian, Italiar
	Japanese, Norwegian, Polish, Portuguese, Romanian, Russian
	Chinese (simplified), Spanish, Swedish, Chinese (traditional),
	Turkish, Vietnamese
Operating conditions	5°C~40°C/41°F~104°F, max altitude 3000M/9843ft, max
Demote control	humidity 85%
Remote control	Data remote with laser and mouse function
Speaker count	1
Watts per speaker	10W
In the box	AC power cord
	Remote control
	2x AAA batteries Basic user manual
Optional wireless models	HDCast Pro, QuickCast Bundle, QuickCast starter kit,
optional wireless models	WHD200
Power	
Power supply	100 ~ 240V, 50 ~ 60Hz
Power consumption (standby)	0.5W
Power consumption (standby) Power consumption (min)	200W
Power consumption (min) Power consumption (max)	
	285W
Weight and dimensions	
Weight and dimensions Dimensions (W x D x H)	12.44" × 9.61" × 4.25"
Weight and dimensions Dimensions (W x D x H) Gross weight Net weight	12.44" x 9.61" x 4.25" 8.75 lbs 7.43 lbs







Copyright © 2022 Optoma Technology, Inc. DLP® and the DLP logo are registered trademarks of Texas Instruments<sup>TM</sup>. All other trademarks are the property of their respective owners. All specifications subject to change at any time. 12092022093941