

# ThinkVision E24-29 63D0MAR3US

**Product**

ThinkVision E24-29

**Machine Type**

63D0

**Region**

LA, NA

**Display Size**

23.8"

**View Area**

527.0x296.5 mm

**Panel**

Vertical Alignment

**Aspect Ratio**

16:9

**Resolution**

1920x1080

**Pixel Pitch**

0.275x0.275 mm

**Dot / Pixel Per Inch**

93 dpi

**View Angle (H / V)**

178 / 178

**Response Time**

4 ms (Extreme mode) / 6 ms (Typical mode)

**Color Support**

16.7 Million

**Refresh Rate**

60 Hz

**Brightness**

250 nits

**Contrast Ratio**

3000:1

**Color Gamut**

72% NTSC

**Curvature**

None

**Anti-glare**

Yes

**Video Connector**

1x HDMI 1.4, 1x DP 1.2, 1x VGA

**USB Port**

None

**Camera**

None

**Microphone**

None

**Speakers**

2x 1.5W

**Power Consumption (Typical / Maximum)**

25W / 33W

**Power Adapter**

Integrated

**Stand**

Tilt, Swivel, Pivot, Height Adjust Stand

**Color**

Raven Black

**Side Bezel Width**

2.3 mm

**Dimensions with Stand (HxWxD)**

462.1x540.4x185.7 mm / 18.19x21.28x7.31 inches

**Weight (Including Stand)**

4.5 kg / 9.9 lbs.

**Cables Included**

HDMI cable

**Environmental Certification**

Energy Star Certified, TCO 8.0, TCO Edge 2.0, EPEAT Gold, RoHS

**Ergonomic Certification**

TÜV Rheinland Low Blue Light, TÜV Rheinland Eye Comfort

**Base Warranty**

3-year

**Operating System Support**

Support Windows 7, Windows 10

**Sync Technology**

None

**Tiny Support / CPU / Platform**

None / None / None

**Ethernet / Bluetooth / Wireless**

None / None / None

**Touch Screen / Digitizer Pen / Controller**

None / None / None

**Display Ram / Storage / Card Slot**

None / None / None

**EAN / UPC / JAN**

0196800962492 / 196800962492 / None

**Announce Date**

2022-07-03

 [WWW.LENOVO.COM](http://WWW.LENOVO.COM)

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product specifications Reference.

© Lenovo, 2022. All rights reserved.



Lenovo™

# ThinkVision E24-29 Monitor

## DISPLAY

### Panel Size

23.8-inch

### Screen Dimensions

534.6 mm x 308.5 mm

### Panel Type

3-side NearEdgeless VA

### Active Area

527.0 mm x 296.5 mm

### Backlight

WLED

### Aspect Ratio

16:9

### Resolution

1920 x 1080

### Pixel Pitch

0.275 mm x 0.275 mm

### Dot/Pixel Per Inch (DPI/PPI)

93

### Viewing Angle (H x V @ CR 10:1)

178° / 178°

### Response Time

4ms (Extreme Mode), 6ms (Normal Mode)

### Refresh Rate

60Hz

### Brightness (Typical)

250 cd/m<sup>2</sup>

### Contrast Ratio (Typical)

3000:1

### Dynamic Contrast Ratio (Typical)

3M:1

### Color Gamut (Coverage Ratio)

72% NTSC (CIE 1931)

### Color Support (Typical)

16.7 Million

### Color Depth

8-bit (6+FRC)

### Anti-Glare

Yes

## CONNECTIVITY

### Video Signal

1 x HDMI 1.4

1 x DP 1.2

1 x VGA

## MULTIMEDIA

### Integrated Speakers

Yes (2 x 1.5W)<sup>1</sup>

## POWER

### Power Consumption (Typ. / Max.)

25W / 33W

### Power Consumption Sleep/Off Mode

< 0.5W

### Power Consumption Switch-Off Mode

< 0.3W

### ENERGY STAR Power Consumption (Pon / E<sub>TEC</sub>)

12W / 39kWh

### Power Supply

Internal

### Voltage Required

AC 100 to 240 V (50-60Hz)

## MECHANICAL

### Tilt Angle (Front / Back)

-5° / 22°

### Swivel Angle (Left / Right)

-360° / 360°

### Lift Range

155 mm

### Pivot

-90° / 90°

### VESA Mount Capability

Yes (100 x 100 mm)

### ThinkCentre M Series Tiny Support

Yes, by Sandwich Mounting Kit

(PN: 4XHON04098)<sup>2</sup>

### Kensington Lock Slot

Yes

### Bezel Color

Raven Black

### Bezel Width (Side)

2.3 mm

### Bezel Width (Top / Bottom)

2.3 / 20.5 mm

## DIMENSION

### Size Packed (D x H x W) (mm/inch)

145.0 x 397.0 x 638.0 mm

5.71 x 15.63 x 25.12 inches

### Size Unpacked w/ Stand (D x H x W) (mm/inch) (Lowest Position)

185.7 x 336.3 x 540.4 mm

7.31 x 13.24 x 21.28 inches

### Size Unpacked w/ Stand (D x H x W) (mm/inch) (Highest Position)

185.7 x 462.1 x 540.4 mm

7.31 x 18.19 x 21.28 inches

### Size Unpacked w/o Stand (Head Only) (D x H x W) (mm/inch)

43.5 x 325.3 x 540.4 mm

1.71 x 12.81 x 21.28 inches

### Weight Packed (kg / lbs.)

6.0 kg / 13.2 lbs.

### Weight Unpacked (kg / lbs.)

4.5 kg / 9.9 lbs.

### Weight (Monitor Head Only)

2.9 kg / 6.4 lbs.

## WHAT'S IN THE BOX

### Monitor with Stand

Yes

### Power Cable (Cable Length)

1 x Power Cable (1.8 m)

### HDMI Cable (Cable Length)

1 x HDMI Cable (1.8 m)

### Quick Setup Guide

Yes

## CERTIFICATION

### ENERGY STAR Certification

Yes

### CCC

Yes

### TCO

8.0

### TCO Edge

2.0

### EPEAT

Gold

### RoHS (2011/65/EU)

Yes

### Windows Certification

Windows 7, Windows 10

### China Energy Efficiency Standard

Tier 1

### TÜV Rheinland Eye Comfort

Yes

### TÜV Rheinland Low Blue Light

Yes



<sup>1</sup> For ROW (not applicable for PRC region). | <sup>2</sup> Sold separately.

© 2022 Lenovo. All rights reserved. These products are available while supplies last. Prices shown are subject to change without notice. For any questions concerning price, please contact your Lenovo Account Executive. Lenovo is not responsible for photographic or typographic errors. Warranty: For a copy of applicable warranties, write to: Warranty Information, 500 Park Offices Drive, RTP, NC 27709, U.S.A., Attn: Dept. ZPYA/B600. Lenovo makes no representation or warranty regarding third-party products or services. Trademarks: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkVantage, ThinkVision, and ThinkColour are trademarks or registered trademarks of Lenovo. Microsoft, Windows, and Vista are registered trademarks of Microsoft Corporation. Intel, the Intel logo, Intel Inside, Intel Core, and Core Inside are trademarks of Intel Corporation in the U.S. and/or other countries. Other company, product, and service names may be trademarks or service marks of others.

Specifications may vary depending upon region.

# ThinkVision E24-29

