



## SPECIFICATIONS

<b>DYNAMIC REFRESH RATE TECHNOLOGY</b>	FreeSync
<b>ACTIVATED RANGE</b>	40 to 60Hz
<b>DCR</b>	100000000:1
<b>Adobe RGB / DCI-P3 / sRGB</b>	91.36% / 94.91% / 122.54%
<b>USB ports</b>	N/A
<b>Dimension (W x D x H)</b>	638.3 x 229.4 x 446.4 mm 638.3 x 57.1 x 375 mm (without stand)
<b>Carton Dimension (W X D X H)</b>	WW carton: 825 x 148 x 475 mm Outer carton: 840 x 163 x 500 mm
<b>Control</b>	5-way OSD navigation joystick
<b>Signal Frequency</b>	119.4~140.7 KHz(H) 40~60 Hz(V)
<b>Frameless Design</b>	Yes

## CONNECTIONS



1. 5-way joystick navigator
2. DC jack
3. 1x Display Port (1.2a)
4. 2x HDMI (2.0b)
5. Earphone Out
6. Kensington Lock

## FEATURES

### IPS PANEL

Make sure the intensity and purity of colors when gaming.

### 4K UHD Resolution

3840 x 2160

Experience the incredibly sharp and crisp images, movies and gameplay etc., to meet your sensory needs.

### VESA CERTIFIED



### VESA Certified DisplayHDR 400

Provide eye-catching detail through contrast and shadows adjustment.

### DisplayHDR

### LESS BLUE LIGHT PREMIUM



Less Blue Light Premium is using a hardware solution to reduced light emissions in the blue-violet segment of the blue light spectrum without any color or picture quality sacrifice.



### Wide Color Gamut

Game colors and details will look more realistic and refined, to push game immersion to its limits.



### Frameless Design

With the narrow bezel, you will not even notice the monitor at all in the heat of the moment.



### Night Vision

Smart black tuner to brighten your day by bringing out the fine details in dark areas.