


Key Features

- Ergonomic flexibility with quickrelease stand
- vDisplay Manager productivity software for maximized multitasking
- Dual front facing speakers for clear audio
- HDMI, DisplayPort, VGA, and USB3.2 ports for extended connectivity
- 3-side narrow bezel for uninterrupted viewing



Product Description

The ViewSonic VG2240 is a 22" Full HD ergonomic business monitor designed to increase productivity and efficiency within the home and office workspace. Providing the full spectrum of ergonomic flexibility, the VG2240 can tilt, swivel, pivot, and height adjustment to adapt to any setup or workflow, while the built-in vDisplay Manager productivity software delivers efficient multi-tasking ability and streamlined display control. Dual front-facing speakers ensure a perfect audio-visual experience to provide teams with quality remote communication and collaboration. The beautifully designed display includes a 3-sided narrow bezel for uninterrupted viewing in multi-monitor display setups as well HDMI, DisplayPort, VGA, and USB3.2 connectivity. Complete with an easy-to-install quick release stand that reduces setup time to only a few minutes, the VG2240 offers a high-performance, purpose-built display solution designed for workspace productivity.



- | | |
|--|---------------------------------|
| 1. Menu Control Panel | 7. HDMI |
| 2. VESA Compatible(Wall Mount 100 x 100mm) | 8. D-Sub |
| 3. AC In | 9. USB 3.0 Up Stream(Type B) |
| 4. Line-in | 10. USB 3.0 Down Stream(Type A) |
| 5. Headphone | 11. USB 3.0 Down Stream(Type A) |
| 6. Display Port1.2 | |

Visit Us  www.viewsonic.com

DISPLAY

Display Size (in.):	22
Viewable Area (in.):	21.5
Panel Type:	VA Technology
Resolution:	1920 x 1080
Resolution Type:	FHD (Full HD)
Static Contrast Ratio:	3,000:1 (typ)
Dynamic Contrast Ratio:	80M:1
Light Source:	LED
Brightness:	250 cd/m ² (typ)
Colors:	16.7M
Color Space Support:	8 bit true
Aspect Ratio:	16:9
Response Time (Typical GTG):	5ms
Response Time (GTG w/OD):	5ms
Viewing Angles:	178° horizontal, 178° vertical
Backlight Life (Hours):	30000 Hrs (Min)
Curvature:	Flat
Refresh Rate (Hz):	60
Blue Light Filter:	Yes
Flicker-Free:	Yes
Color Gamut:	NTSC: 72% size (Typ) sRGB: 103% size (Typ)
Pixel Size:	0.249 mm (H) x 0.241 mm (V)
Surface Treatment:	Anti-Glare, Hard Coating (3H)

COMPATIBILITY

PC Resolution (max):	1920x1080
Mac® Resolution (max):	1920x1080
PC Operating System:	Windows 10/11 certified; macOS tested
Mac® Resolution (min):	1920x1080

CONNECTOR

VGA:	1
USB 3.2 Type A Down Stream:	4
USB 3.2 Type B Up Stream:	1
3.5mm Audio In:	1
3.5mm Audio Out:	1
HDMI 1.4:	1
DisplayPort:	1
Power in:	3-pin Socket (IEC C14 / CEE22)

AUDIO

Internal Speakers:	2Watts x2
--------------------	-----------

POWER

Eco Mode (Conserve):	12.35W
Eco Mode (optimized):	14.43W
Consumption (typical):	17.18W
Consumption (max):	18.89W
Voltage:	AC 100-240V
Stand-by:	0.5W
Power Supply:	Internal Power Supply

ADDITIONAL HARDWARE

Kensington Lock Slot:	1
Cable Organization:	Yes

CONTROLS

Physical Controls:	Key 1 (eye), Key 2, Key 3, Key 4, Key 5, Key 6 (power)
On Screen Display:	Input Select, Audio Adjust, ViewMode, Color Adjust, Manual Image Adjust, Setup Menu

OPERATING CONDITIONS

Temperature:	32°F to 104°F (0°C to 40°C)
Humidity (non-condensing):	20% to 90%

WALL MOUNT

VESA Compatible:	100 x 100 mm
------------------	--------------

INPUT SIGNAL

Frequency Horizontal:	24 ~ 82KHz
Frequency Vertical:	50 ~ 75Hz

VIDEO INPUT

Digital Sync:	TMD5 - HDMI (v1.4), PCI-E - DisplayPort (v1.2)
Analog Sync:	Separate/Composite/SOG - RGB Analog

ERGONOMICS

Height Adjust (mm):	130
Swivel:	120°
Tilt (Forward/Back):	-5° / 40°
Pivot (Right/Left):	90° / 90°

WEIGHT (IMPERIAL)

Net (lbs):	11.5
Net Without Stand (lbs):	6.2
Gross (lbs):	16.8

WEIGHT (METRIC)

Net (kg):	5.2
Net Without Stand (kg):	2.8
Gross (kg):	7.6

DIMENSIONS (IMPERIAL) (WXHxD)

Packaging (in.):	21.9 x 14.9 x 8.3
Physical (in.):	19.7 x 15.23~19.56 x 8.1
Physical Without Stand (in.):	19.7 x 11.6 x 2

DIMENSIONS (METRIC) (WXHxD)

Packaging (mm):	556 x 379 x 210
Physical (mm):	501 x 386.85~496.96 x 206
Physical Without Stand (mm):	501 x 294 x 51

GENERAL

Regulations:	cTUVus, FCC-B, ICES003, Energy Star, EPEAT, CEC, NOM, Mexico Energy, CB, RoHS, REACH, WEEE
PACKAGE CONTENTS:	VG2240 x1, 3-pin Plug (IEC C13 / CEE22) x1, HDMI Cable (v1.4; Male-Male) x1, USB A/B Cable (v3.2; Male-Male) x1, Audio Cable (Male-Male) x1, Quick Start Guide x1
Recycle/Disposal:	Please dispose of in accordance with local, state or federal laws.
Warranty:	*Warranty offered may differ from market to market
Power Management:	Energy Star standards, EPEAT