

ViewSonic LCD DISPLAY **XG341C-2K**

Key Features

- AMD FreeSync™ Premium Pro for smooth and ultra-low-latency playback
- Mini-LED w/1152 zone display and full-array local dimming for peak visual performance
- VESA DisplayHDR 1400 for mind-blowing colors and contrasts
- Refresh rate overclockable to 200Hz for hyper-responsive visuals
- HDMI 2.1 Connection for console gaming compatibility



Product Description

Experience a new level of visual performance and upgrade your gameplay on the XG341C-2K, featuring Mini LED technology that redefines expectations. Curved 34-inch UWQHD monitor delivers a highly immersive gaming experience teleporting you straight into the middle of the action. Engineered with quantum dot technology, the resolution renders every detail with incredible brightness on VESA certified DisplayHDR™ 1400 panel. Rapid 200Hz (OC) refresh rate guarantees ultrasmooth gameplay, and a blazing fast 1ms (MPRT) response time to reduce in-game ghosting. Geared with AMD FreeSync™ Premium Pro technology, you'll handle even the most intense action scenes.

Visit Us  www.viewsonic.com

DISPLAY

Display Size (in.):	34
Viewable Area (in.):	34
Panel Type:	VA Technology
Resolution:	3440 x 1440
Resolution Type:	UWQHD (UltraWide QHD)
Static Contrast Ratio:	3,000:1 (typ)
Dynamic Contrast Ratio:	120M:1
Light Source:	mini LED
Brightness:	720; 1400 (w/ HDR+local dimming Peak (Min))
Colors:	16.7M
Color Space Support:	8 bit true
Aspect Ratio:	21:9
Response Time (MPRT):	1ms
Viewing Angles:	178° horizontal, 178° vertical
Backlight Life (Hours):	30000 Hrs (Min)
Curvature:	1500R
Refresh Rate (Hz):	200
Adaptive Sync:	FreeSync Premium Pro
Blue Light Filter:	Yes
Flicker-Free:	Yes
Color Gamut:	DCI-P3: 97% coverage (Typ) NTSC: 99% size (Typ) sRGB: 140% size / 99% coverage (Typ)
Pixel Size:	0.232 mm (H) x 0.232 mm (V)
Surface Treatment:	Anti-Glare, Hard Coating (3H)

COMPATIBILITY

PC Resolution (max):	3440x1440
Mac® Resolution (max):	3440x1440
PC Operating System:	Windows 10/11 certified; macOS tested
Mac® Resolution (min):	3440x1440

CONNECTOR

USB 3.2 Type A Down Stream:	3
USB 3.2 Type B Up Stream:	1
USB 3.2 Type C Up Stream; DisplayPort Alt mode :	1
3.5mm Audio Out:	1
HDMI 2.1:	2
DisplayPort:	1
Power in:	3-pin Socket (IEC C14 / CEE22)

AUDIO

Internal Speakers:	5Watts x2
--------------------	-----------

POWER

Eco Mode (Conserve):	45W
Eco Mode (optimized):	53W
Consumption (typical):	57W
Consumption (max):	60W
Voltage:	AC 100-240V
Stand-by:	0.5W
Power Supply:	Internal Power Supply

ADDITIONAL HARDWARE

Kensington Lock Slot:	1
Cable Organization:	Yes

CONTROLS

Physical Controls:	Up, Right, Down, Left, Power
On Screen Display:	Game Modes, Display, Input Select, ViewMode, Audio Adjust, Setup Menu

OPERATING CONDITIONS

Temperature:	32°F to 104°F (0°C to 40°C)
Humidity (non-condensing):	20% to 90%

WALL MOUNT

VESA Compatible:	100 x 100 mm
------------------	--------------

INPUT SIGNAL

Frequency Horizontal:	30 ~ 320KHz
Frequency Vertical:	48 ~ 200Hz

VIDEO INPUT

Digital Sync:	TMDS - HDMI (v2.1), PCI-E - DisplayPort (v1.4), Micro-Packet - Type C
---------------	---

ERGONOMICS

Height Adjust (mm):	120
Swivel:	50°
Tilt (Forward/Back):	-5° / 23°

WEIGHT (IMPERIAL)

Net (lbs):	25
Net Without Stand (lbs):	18.7
Gross (lbs):	40.3

WEIGHT (METRIC)

Net (kg):	11.4
Net Without Stand (kg):	8.5
Gross (kg):	18.3

DIMENSIONS (IMPERIAL) (WXHXD)

Packaging (in.):	37.9 x 20.4 x 13.8
Physical (in.):	31.8 x 18.94~23.67 x 15.1
Physical Without Stand (in.):	31.8 x 14.3 x 5.2

DIMENSIONS (METRIC) (WXHXD)

Packaging (mm):	963 x 518 x 351
Physical (mm):	807 x 481.11~601.11 x 384
Physical Without Stand (mm):	807 x 363 x 132

GENERAL

Regulations:	cTUVus, FCC-B, ICES003, CEC, MX-CoC, Mexico Energy, CE, CE EMC, CB, RoHS, ErP, REACH, WEEE, EAC, UkrSEPRO, UKCA, CCC, China RoHS, China Energy Label
PACKAGE CONTENTS:	XG341C-2K x1, 3-pin Plug (IEC C13 / CEE22) x1, HDMI Cable (v2.1; Male-Male) x1, DisplayPort Cable (v1.4; Male-Male) x1, USB Type-C Gen2 Cable (Male-Male) x1, USB A/B Cable (v3.2; Male-Male) x1, Quick Start Guide x1
Recycle/Disposal:	Please dispose of in accordance with local, state or federal laws.
Warranty:	*Warranty offered may differ from market to market