

Fiber TAP Cassette - Multimode, 8-Fiber MPO to MPO, 4 Monitoring Ports, 70/30 Split

MODEL NUMBER: N482TAP-4MM73M8



Installs in Tripp Lite N482-Series chassis to split optical fiber signals into two outputs, one for user and one for monitoring.

Features

Fiber Optic TAP Cassette Helps You Monitor and Analyze Network Data

This N482TAP-4MM73M8 multimode TAP (traffic access point) cassette is a passive device added to a fiber optic network to enable real-time monitoring. Its optical splitter divides the optical signal into two outputs, one for the downstream device and one for monitoring, without introducing latency or creating a single point of failure.

Creates a 70/30 Split Ratio for User Traffic and Signal Monitoring

Network monitoring is used to gather data to analyze performance issues, optimize network traffic and uncover security threats in your data center, telecom carrier network or R&D facility. This TAP cassette directs 30 percent of the light to a nearby monitoring device. The remaining 70 percent is transmitted as usual throughout the network without affecting performance.

Compatible with Multimode Cabling

This passive TAP cassette supports 40/100 Gb internally using multimode fiber optic cable, enabling you to perform monitoring and data analysis without causing delays or affecting network performance. It is compatible with recommended cables, including the N845-Series, for connecting to switches, routers and monitoring equipment.

Easy to Install with Compatible Enclosures

The multimode N482TAP-4MM73M8 works with N482-00U (fits one cassette), N482-01U (fits five cassettes), N482-02U (14 cassettes) and N482-04U (28 cassettes) chassis. The futureproof-friendly modular design allows you to remove the cassette without replacing the panel or removing other cassettes. The TAP cassette also complies with IEEE 802.3ae (10 Gb) and ANSI T11.2 (Fibre Channel) requirements. A 0.20 dB maximum insertion loss falls under IEEE 802.3ae maximum channel loss spec of <25 dB.

Factory-Terminated Ports Help Reduce Installation Time

The OM4-rated cassette has 12 QSFP 8-fiber MTP/MPO ports that allow fast, easy connection of cables. The durable plastic cassette comes with dust caps to protect unused ports.

Specifications

Highlights

- Passive OM4 multimode fiber TAP with 40/100 Gb MPO to MPO ports
- 70/30 split ratio allows real-time traffic analysis while preserving primary link performance
- Fiber TAP cassette is optimized for parallel optics and Base-8 connectivity
- Compatible with N482-00U, N482-01U, N482-02U and N482-04U panels

Applications

Monitor network activity for performance or security issues while allowing the normal flow of traffic

System Requirements

- Compatible with recommended cables, including N845-Series
- Works with N482-Series fiber enclosure panels

Package Includes

- N482TAP-4MM73M8 Multimode TAP Cassette, 70/30
- Quick Start Guide

OVERVIEW	
UPC Code	037332262622
Product Type	Passive Fiber TAP
Technology	Multimode
Optical Mode	OM4
PHYSICAL	
Number of Fibers	32
Shipping Dimensions (hwd / in.)	2.00 x 7.90 x 4.70
Shipping Weight (lbs.)	0.44
Unit Dimensions (hwd / in.)	4.720 x 3.460 x 1.180
ENVIRONMENTAL	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Relative Humidity	5% to 85% RH, Non-Condensing
COMMUNICATIONS	
Network Compatibility	40 Gbps; 100 Gbps; 400 Gbps
Wavelength	850nm
Insertion Loss	3.00 dB / 7.00 dB @ 850nm
Split Ratio	70/30
CONNECTIONS	
Monitoring Ports	4
Side A - Connector 1	12-STRAND MTP/MPO (MALE)
Side B - Connector 1	12-STRAND MTP/MPO (MALE)
Input Ports	4
Output Ports	4
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



1000 Eaton Boulevard
Cleveland, OH 44122
United States



© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.