



SPECIFICATIONS

Panel Size	27"
Panel Resolution	1920x1080 (FHD)
Refresh Rate	170Hz
Response time	1ms(MPRT)
Panel Type	VA
Brightness (nits)	300
Viewing Angle	178°(H) / 178°(V)
Aspect Ratio	16:9
Curvature	1000R
Contrast Ratio	3000:1
Active Display Area (mm)	596.736(H)x335.664(V)
Pixel Pitch (H x V)	0.3108(H)x0.3108(V)
Surface Treatment	Anti-glare
Display Colors	16.7M
DCI-P3 / sRGB	85% / 115%
Video ports	1x Display Port (1.2a) 2x HDMI (2.0b)
Audio ports	1 x Earphone out
Kensington Lock	Yes
VESA Mounting	75 x 75 mm
Power Type	Power Cable
Power Input	100~240V, 50~60Hz
DYNAMIC REFRESH RATE TECHNOLOGY	FreeSync Premium
DCR	100000000:1
Power consumption	26W
Signal Frequency	103~186.8 KHz(H) / 48~170 Hz(V)
Adjustment (Tilt)	-5° ~ 20°
Dimension (W x H x D)	606.5 x 245.6 x 482.2 mm / 23.88 x 9.67 x 18.98 inch
Carton Dimension (W X H X D)	780 x 448 x 188 mm / 30.71 x 17.64 x 7.4 inch
Weight (NW / GW)	5.6kg; 12.35 lbs / 7.8kg; 17.2 lbs
Frameless Design	Yes
Console Mode	Yes

FEATURES

- Curved Gaming™**
View more of your game. MSI Curved Gaming™ monitors are perfect for gamers to play their games.
- 1000R - The Perfect Curve**
Enjoy the most immersive gameplay with 1000R curvature rate.
- 170Hz High Refresh Rate**
Experience smooth gaming with 170Hz refresh rate, that gives you the upperhand in fast moving games.
- Less Blue Light PRO**
Use a hardware solution to reduce the light emission in the blue-violet region of the blue light spectrum (wavelength 415 to 455 nm).
- Frameless Design**
With the narrow bezel, you will not even notice the monitor at all in the heat of the moment.
- Wide Color Gamut**
Game colors and details will look more realistic and refined, to push game immersion to its limits.

Compatibility

PC, Mac, PS5™, PS4™, Xbox, Mobile, Notebook

* All trademarks and the registered trademarks are the property of their respective owners.

Note

Display Port: 1920x1080 (Up to 170Hz)

HDMI2.0: 1920x1080 (Up to 165Hz)

*sRGB and DCI-P3 follow CIE1976 standard

CONNECTIONS



1. 1x HDMI (2.0b)
2. 1x HDMI (2.0b)
3. 1x DisplayPort (1.2a)
4. 1x Earphone out
5. 1x Power Jack