

ThinkVision T24i-30 63CFMAR1US

Product

ThinkVision T24i-30

Machine Type

63CF

Region

LA, NA

Display Size

23.8"

View Area

527.0x296.5 mm

Panel

In-Plane Switching

Aspect Ratio

16:9

Resolution

1920x1080

Pixel Pitch

0.275x0.275 mm

Dot / Pixel Per Inch

93 dpi

View Angle (H / V)

178 / 178

Response Time

4 ms (Extreme mode) / 6 ms (Typical mode)

Color Support

16.7 Million

Refresh Rate

60 Hz

Brightness

250 nits

Contrast Ratio

1000:1

Color Gamut

99% sRGB

Curvature

None

Anti-glare

Yes

Video Connector

1x HDMI 1.4, 1x DP 1.2, 1x VGA

USB Port

4x USB 3.0

Network Connectivity

None

Camera

None

Microphone

None

Speakers

None

Power Consumption (Typical / Maximum)

14W / 51W

Power Adapter

Integrated

Stand

Tilt, Swivel, Pivot, Height Adjust Stand

Color

Raven Black

Side Bezel Width

2 mm

Dimensions with Stand (HxWxD)

504.8x539.8x199.7 mm / 19.87x21.25x7.86inches

Weight (Including Stand)

5.4 kg / 11.9 lbs.

Cables Included

HDMI cable, USB-A to USB-B cable

Environmental Certification

Energy Star Certified, TCO 9.0, TCO Edge 2.0, EPEAT Gold, RoHS

Ergonomic Certification

Eyesafe Display, TÜV Low Blue Light (Hardware solution), TÜV Rheinland Low Blue Light, TÜV Rheinland Flicker Free

Base Warranty

3-year

Operating System Support

Support Windows 10, Windows 11

Sync Technology

None

ThinkCentre M Series Support

None

Processor

None

Touch Screen

None

Controller

None

Display Ram / Storage / Card Slot

None / None / None

EAN / UPC / JAN

0196801904903 / 196801904903 / None

Announce Date

2022-09-15

WWW.LENOVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product specifications Reference.

© Lenovo, 2022. All rights reserved.



Lenovo™

ThinkVision T24i-30 Monitor

Display

Panel Size
23.8-inch

Screen Dimensions
535.0 mm x 313.0 mm

Panel Type
3-side NearEdgeless In-Plane Switching

Active Area
527.0 mm x 296.5 mm

Backlight
WLED

Aspect Ratio
16:9

Resolution
1920 x 1080

Pixel Pitch
0.275 mm x 0.275 mm

Dot/Pixel Per Inch (DPI/PPI)
93

Viewing Angle (H x V @ CR 10:1)
178° / 178°

Response Time
4ms (Extreme Mode), 6ms (Normal Mode)

Refresh Rate
60Hz

Brightness (Typical)
250 cd/m²

Contrast Ratio (Typical)
1000:1

Dynamic Contrast Ratio (Typical)
3M:1

Color Gamut (Coverage Ratio)
99% sRGB

Color Gamut (Color Area Ratio)
110% sRGB

Color Support (Typical)
16.7 Million

Color Depth
6-bit (Hi+FRC)

Anti-glare
Yes

Connectivity

Video Signal
1 x HDMI 1.4
1 x DP 1.2
1 x VGA

Audio Signal
1 x Audio Out (3.5 mm)

USB Hub
Yes

USB Upstream
1 x USB 3.0

USB Downstream
4 x USB 3.0

Special Features

Software
Lenovo ThinkColour (Lenovo Display Control Center)*

Natural Low Blue Light
Yes

Power

Power Consumption (Typ. / Max.)
14W / 51W

Power Consumption Sleep/Off Mode
< 0.5W

Power Consumption Switch-Off Mode
< 0.3W

ENERGY STAR Power Consumption (Pon/E_{TEC})
12W / 38kWh

Power Supply
Internal

Voltage Required
AC 100 to 240 V (50-60Hz)

Mechanical

Tilt Angle (Front / Back)
-5° / 23.5°

Swivel Angle (Left / Right)
-45° / 45°

Lift (Max. Range)
155 mm

Pivot
-90° / 90°

VESA Mount Capability
Yes (100 x 100 mm)

Kensington Lock Slot
Yes

Cable Management
Yes

Bezel Color
Raven Black

Bezel Width (Side)
2.0 mm

Bezel Width (Top / Bottom)
2.0 mm / 17.1 mm

Dimension

Size Packed (D x H x W) (mm/inch)
152.0 x 422.0 x 592.0 mm
5.98 x 16.61 x 23.31 inches

Size Unpacked w/ Stand (Lowest Position) (D x H x W) (mm/inch)
199.7 x 349.8 x 539.8 mm
7.86 x 13.77 x 21.25 inches

Size Unpacked w/ Stand (Highest Position) (D x H x W) (mm/inch)
199.7 x 504.8 x 539.8 mm
7.86 x 19.87 x 21.25 inches

Size Unpacked w/o Stand (Head Only) (D x H x W) (mm/inch)
49.0 x 321.4 x 539.8 mm
1.93 x 12.65 x 21.25 inches

Weight Packed (kg / lbs.)
7.8 kg / 17.2 lbs.

Weight Unpacked (kg / lbs.)
5.4 kg / 11.9 lbs.

Weight (Monitor Head Only) (kg / lbs.)
3.4 kg / 7.5 lbs.

What's in the Box

Monitor with Stand
Yes

Power Cable (Cable Length)
1 x Power Cable (for standalone 1.8m)

HDMI Cable (Cable Length)
1 x HDMI Cable (1.8m)

USB Cable (Cable Length)
1 x USB Type-A to Type-B (1.8m)

Quick Setup Guide
Yes

Warranty Booklet
Yes

Certification

ENERGY STAR Certification
Yes

CCC
Yes

TCO
9.0

TCO Edge
2.0

EPEAT
Gold

Volatile Organic Compound Certification
Yes

RoHS (2011/65/EU)
Yes

Windows Certification
Windows 10, Windows 11

China Energy Efficiency Standard
Tier 1

TÜV Rheinland Low Blue Light
Yes

TÜV Rheinland Flicker Free
Yes

TÜV Low Blue Light (Hardware Solution)
Yes

Eyesafe Display Certification
Yes



* This software can only be used with Windows 10 & Windows 11.

© 2022 Lenovo. All rights reserved. These products are available while supplies last. Prices shown are subject to change without notice. For any questions concerning price, please contact your Lenovo Account Executive. Lenovo is not responsible for photographic or typographic errors. Warranty: For a copy of applicable warranties, write to: Warranty Information, 500 Park Offices Drive, RTP, NC 27709, U.S.A., Attn: Dept. ZPYA/B600. Lenovo makes no representation or warranty regarding third-party products or services. Trademarks: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkVantage, ThinkVision, and ThinkColour are trademarks or registered trademarks of Lenovo. Microsoft, Windows, and Vista are registered trademarks of Microsoft Corporation. Intel, the Intel logo, Intel Inside, Intel Core, and Core Inside are trademarks of Intel Corporation in the U.S. and/or other countries. Other company, product, and service names may be trademarks or service marks of others.

Specifications may vary depending upon region.

Smarter
technology
for all

Lenovo

ThinkVision T24i-30

