

Lenovo Legion Y27-30 66F8GAC3US

Product

Lenovo Legion Y27-30

Machine Type

66F8

Region

LA, NA

Display Size

27"

View Area

596.7x335.6 mm

Panel

In-Plane Switching

Aspect Ratio

16:9

Resolution

1920x1080

Pixel Pitch

0.311x0.311 mm

Dot / Pixel Per Inch

81 dpi

View Angle (H / V)

178 / 178

Response Time

0.5 ms (MPRT) / 1 ms (Level 4) / 2 ms (Level 3) / 3ms (Level 2) / 4ms (Level 1) / 5ms (Off)

Color Support

16.7 Million

Refresh Rate

165 Hz / 180 Hz (Overclock)

Brightness

400 nits (Typical)

Contrast Ratio

1000:1

Color Gamut

99% sRGB

Curvature

None

Anti-glare

Yes

Video Connector

2x HDMI 2.0, 1x DP 1.4

USB Port

4x USB 3.2 Gen 1

Network Connectivity

None

Camera

Modular Camera Support

Microphone

None

Speakers

2x 3W

Power Consumption (Typical / Maximum)

48W / 80W

Power Adapter

Integrated

Stand

Tilt, Swivel, Pivot, Height Adjust Stand

Color

Raven Black

Side Bezel Width

2 mm

Dimensions with Stand (HxWxD)

536.5x613.7x258.8 mm / 21.12x24.16x10.19 inches

Weight (Including Stand)

6.4 kg / 14.1 lbs.

Cables Included

DP cable, USB Type-A to Type-B cable

Environmental Certification

RoHS

Ergonomic Certification

Eyesafe Display, TÜV Low Blue Light (Hardware solution), TÜV Rheinland Eye Comfort

Base Warranty

3-year

Operating System Support

Support Windows 10, Windows 11

Sync Technology

AMD FreeSync Premium, Adaptive Sync

ThinkCentre M Series Support

None

Processor

None

Touch Screen

None

Controller

None

Display Ram / Storage / Card Slot

None / None / None

EAN / UPC / JAN

0196800453686 / 196800453686 / None

Announce Date

2022-07-25

 WWW.LENOVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product specifications Reference.

© Lenovo, 2022. All rights reserved.



Lenovo™

Legion Y27-30 Monitor

Display

Panel Size
27-inch

Screen Dimensions
608.8 mm x 355.1 mm

Panel Type
3-side NearEdgeless
In-Plane Switching

Active Area
596.7 mm x 335.6 mm

Backlight
WLED

Aspect Ratio
16:9

Resolution
1920 x 1080

Pixel Pitch
0.311 mm x 0.311 mm

Dot/Pixel Per Inch (DPI/PPI)
81

Viewing Angle (H x V @ CR 10:1)
178° / 178°

Response Time
0.5ms (MPRT)¹, 1ms (Level 4),
2ms (Level 3), 3ms (Level 2),
4ms (Level 1), 5ms (Off)

Refresh Rate
165Hz (Overclock to 180Hz²)

Brightness (Typical)
400 cd/m²

Contrast Ratio (Typical)
1000:1

Dynamic Contrast Ratio (Typical)
3M:1

Color Gamut (Coverage Ratio)
99% sRGB (CIE 1931),

Color Gamut (Color Area Ratio)
110% sRGB (CIE 1931)

Color Support
16.7 Million

Color Depth
8-bit

Processor LUT
8-bit

HDR Compliance
Yes (HDR10)

Anti-Glare
Yes

Connectivity

Video Signal
2 x HDMI 2.0
1 x DP 1.4

Audio Signal
1 x Audio Out (3.5 mm)

USB Hub
Yes

USB Upstream
1 x USB 3.2 Gen 1³ Type-B

USB Downstream
4 x USB 3.2 Gen 1³ Type-A

Multimedia

Integrated Speakers
Yes (2 x 3W)

Modular Camera Support
Yes (Lenovo LC 50)

Special Features

Software
Lenovo Artery
(Lenovo Display Control Center)⁴

Sync Technology
AMD FreeSync™ Premium⁵
Adaptive Sync

Gaming Console Support
Yes

Natural Low Blue Light
Yes

Power

Power Consumption (Typ. / Max.)
48W / 80W

Power Consumption Sleep/Off Mode
< 0.5W

Power Consumption Switch-off Mode
< 0.3W

Power Supply
Internal

Voltage Required
AC 100 to 240 V (50-60Hz)

Mechanical

Tilt Angle (Front / Back)
-5° / 25°

Swivel Angle (Left / Right)
-30° / 30°

Lift Range
135 mm

Pivot
-90° / 90°

VESA Mount Capability
Yes (100 x 100 mm)

Kensington Lock Slot
Yes

Cable Management
Yes

Bezel Color
Raven Black

Bezel Width (Side)
2.0 mm

Bezel Width (Top / Bottom)
2.0 / 20.6 mm

Dimension

Size Packed (D x H x W) (mm/inch)
720.0 x 510.0 x 160.0 mm
28.35 x 20.08 x 6.30 inches

Size Unpacked w/ Stand (Lowest Position) (D x H x W) (mm/inch)
258.8 x 401.5 x 613.7 mm
10.19 x 15.81 x 24.16 inches

Size Unpacked w/ Stand (Highest Position) (D x H x W) (mm/inch)
258.8 x 536.5 x 613.7 mm
10.19 x 21.12 x 24.16 inches

Size Unpacked w/o Stand (Head Only) (D x H x W) (mm/inch)
61.0 x 365.9 x 613.7 mm
2.40 x 14.41 x 24.16 inches

Weight Packed (kg / lb)
8.4 kg / 18.5 lbs.

Weight Unpacked (kg / lb)
6.4 kg / 14.1 lbs.

Weight (Monitor Head Only) (kg / lb)
4.4 kg / 9.7 lbs.

What's in the Box

Monitor with Stand
Yes

Power Cable (Cable Length)
1 x Power Cable (1.8m)

DP Cable (Cable Length)
1 x DP Cable (1.8m)

USB Cable (Cable Length)
1 x USB Type-A to Type-B
Cable (1.8 m)

Quick Setup Guide
Yes

Warranty Booklet
Yes

Certification

CCC
Yes

Volatile Organic Compound Certification
Yes

RoHS (2011/65/EU)
Yes

Windows Certification
Windows 10, Windows 11

China Energy Efficiency Standard
Tier 1

TÜV Rheinland Eye Comfort
Yes

TÜV Rheinland Low Blue Light (Hardware Solution)
Yes

Eyesafe Display Certification
Yes



¹ Moving Picture Response Time (MPRT) improves the response time and reduces motion blur in the monitor. Enabling MPRT will disable AMD FreeSync™ Premium technology, and you may notice a negligible flicker. | ² Overclocking at 180Hz is based on laboratory test data, and this function may cause irregularities in the display. | ³ Depending on many factors such as the processing capability of peripheral devices, file attributes, and other factors related to system configuration and operating environments, the actual transfer rate using the various USB connectors on this device will vary and is typically slower than the data rates as defined by the respective USB specifications: 5 Gbit/s for USB 3.2 Gen 1; 10 Gbit/s for USB 3.2 Gen 2 & 20 Gbit/s for USB 3.2 Gen2x2. | ⁴ This software can only be used with Windows 10 & Windows 11. | ⁵ AMD FreeSync™ Premium technology only can work with AMD Radeon™ series graphics card.

© 2022 Lenovo. All rights reserved. These products are available while supplies last. Prices shown are subject to change without notice. For any questions concerning price, please contact your Lenovo Account Executive. Lenovo is not responsible for photographic or typographic errors. Warranty: For a copy of applicable warranties, write to: Warranty Information, 500 Park Offices Drive, RTP, NC 27709, U.S.A., Attn: Dept. ZPYA/B600. Lenovo makes no representation or warranty regarding third-party products or services. Trademarks: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkVantage, ThinkVision, and ThinkColour are trademarks or registered trademarks of Lenovo. Microsoft, Windows, and Vista are registered trademarks of Microsoft Corporation. Intel, the Intel logo, Intel Inside, Intel Core, and Core Inside are trademarks of Intel Corporation in the U.S. and/or other countries. Other company, product, and service names may be trademarks or service marks of others.

Specifications may vary depending upon region.

Smarter
technology
for all

Lenovo

Lenovo Legion Y27-30

