


4K400STx

Bright, True 4K UHD short throw projector for classrooms and meeting spaces









- True 4K UHD resolution HDR and HLG compatible
- Short throw projection Supersized 100" image from just a few feet away
- Lights on viewing 4000 lumens for bright images in any environment
- Extensive connectivity Dual HDMI ports, audio connections, USB power, 12V trigger and RS232



Discover the short throw version of the 4K400x, for when you want a big screen in a smaller space.

Future proof your classroom or meeting room with this high brightness True 4K UHD short throw projector. The 4K400STx delivers rich visuals in any environment even when total ambient light control is not possible.

This projector boasts two HDMI ports, audio connections, USB to power 5V devices, 12V trigger and an RS232 to integrate into your existing control solution.

Specifications

Display/image DIPTM Display technology Resolution UHD (3840x2160) Brightness 4,000 lumens 1,000,000:1 Contrast ratio Native aspect ratio 16:9 Aspect ratio - compatible 4:3

Keystone correction -+/-40° horizontal Keystone correction - vertical +/-40° Horizontal scan rate 31 ~ 135Khz Vertical scan rate 24 ~ 120Hz Uniformity 80%

36.43" ~ 300.53" diagonal Screen size

Lamp info Light source type Lamp watts 240

Lamp life hours (up to) 4000 (Bright), 15000 (Dynamic), 10000 (Eco)

Optical Throw ratio 0.5:1 Projection distance 15.75" - 129.92" Zoom Fixed Zoom type

Focal length (mm) 7.51mm Lens shift Vertical +0% Native offset 116% Connectivity

Connections Inputs 2 x HDMI 2.0

Outputs 1 x Audio 3.5mm, 1 x S/PDIF, 1 x USB-A power

Control 1 x RS232, 1 x 12V trigger

General Noise level (typical) 24dB Noise level (max) 28dB

PC compatibility UHD, WQHD, WUXGA, FHD, UXGA, SXGA, WXGA, HD, XGA,

SVGA, VGA, Mac

480i/p, 576i/p, 720p(50/60Hz), 1080i(50/60Hz), 1080p(50/60Hz), 2160p(50/60Hz) 2D compatibility

3D compatibility Frame-pack: 1080p24, 720p50 / 60

3D Full 3D

Security

Security bar, Kensington Lock, Password protected interface OSD / display languages 10 languages: English, French, German, Italian, Japanese, Portuguese, Russian, Chinese (simplified), Spanish

5°C~40°C/41°F~104°F, max altitude 3000M/9843ft, max Operating conditions

humidity 85%

Remote control Backlit home remote

Speaker count 10W

Watts per speaker In the box

AC power cord Remote control

2x AAA batteries Basic user manual

Input lag 4.00ms

Power

100 ~ 240V, 50 ~ 60Hz Power supply

Power consumption (standby) 0.5W Power consumption (min) 220W Power consumption (max) 320W

Weight and dimensions

12.4" x 10.63" x 4.65" Dimensions (W x D x H) Gross weight 10.32 lbs Net weight 8.77 lbs





