

ProductSheet
HP P32u G5 QHD USB-C Monitor (64W51AA)



Powerful Productivity

Accelerate your productivity with this massive, 31.5-inch diagonal monitor. Experience the stunning views via QHD and 99 % sRGB and the power of USB-C® connectivity. Along with the modern and functional design, it's never been easier to get more done.



One Connection to Power it All

Take advantage of the fast USB-C® connection to power through your workday. With a single cable, this monitor delivers video, data for up to 3 USB-A accessories or devices, and 65W charging to your laptop, so nothing slows you down.

See and Hear it All in Stunning Detail

Enjoy a seamless experience complete with stunning, colorful views and clear sounds. This IPS monitor boasts QHD resolution, 75Hz refresh rate[1], and 99 % sRGB for colorful, sharp images and smooth, vivid videos, while the built-in dual speakers provide full, distinct audio.

Form Meets Function

Clear your mind with a well-designed, intuitive monitor. Keep the focus on your screen through the sleek, 3-sided micro-edge bezel, neat cable management, and slim stand with adjustable height and tilt, or stay in your flow by easily changing settings with the Joypad OSD button or manage options and updates directly on-screen with HP Display Center[2] and HP Display Manager[3].

Featuring

75 Hz Refresh Rate

Experience smooth, life-like video and clear detail with a 75 Hz refresh rate that provides fluid movement from frame to frame. [1]

3-Sided Micro-Edge Bezel

See and do more on your screen with a 3-sided micro-edge bezel that maximizes your viewing area for a sleek design and virtually seamless dual-monitor setups.

Easy Joypad OSD Button

It's never been easier to configure your display with the Joypad OSD button to adjust brightness, resolution, and volume.

Low Blue Light Mode

Keep your eyes comfortable with subtly warmer display colors onscreen.

With the Environment in Mind

Meeting the latest standards with EPEAT® registered, ENERGY STAR® and TCO certifications. [4]

Specifications

Display size (diagonal)	31.5"
Panel technology	IPS
Display size (diagonal)	80 cm (31.5")
Aspect ratio	16:9 ^[1]
Native resolution	QHD (2560 x 1440) ^[1,2]
Resolutions supported	640 x 480; 720 x 400; 800 x 600; 1024 x 768; 1280 x 720; 1280 x 800; 1280 x 1024; 1440 x 900; 1600 x 900; 1680 x 1050; 1920 x 1080; 1920 x 1200; 2560 x 1440
Pixel pitch	0.27 x 0.27 mm
Brightness	350 nits ^[1]
Contrast ratio	1000:1 ^[1]
Response time (typical)	5ms GtG (with overdrive) ^[1]
Minimum dimensions (W x D x H)	71.44 x 5.4 x 42.4 cm (Without stand.)
Minimum dimensions (W x D x H)	28.13 x 2.13 x 16.69 in (Without stand.)
Dimensions With Stand (W x D x H)	71.44 x 22.53 x 56.97 cm
Weight	8.29 kg (With stand.)
Weight	18.28 lb (With stand.)
Display features	On-screen controls; Low blue light mode; Dual speakers (2W per channel); Anti-glare
Onscreen controls	Power control; Brightness; Exit; Menu control; Input control; Information; Color control; Image control; Management
Display colors	Up to 16.7 million colors supported
Display scan frequency (horizontal)	30-120 kHz
Display scan frequency (vertical)	48-75 Hz
Power	100 - 240 VAC 50/60 Hz
Power consumption	160 W (maximum), 35 W (typical), 0.5 W (standby)
Operating temperature range	5 to 35°C
Operating humidity range	20 to 80% RH
Sustainable impact specifications	Outside box and corrugated cushions are 100% sustainably sourced and recyclable; 85% ITE-derived closed loop plastic; Low Halogen
Certifications and compliances	Argentina S-Mark; Australia MEPS; CB; CE; CECP; CEL; CEL Grade 1; China CCC; cTUVus; EAC; ENERGY STAR®; ErP; EUP Lot-6; FCC; ICES; ISO 9241-307; KC (Korean) requirements; KCC (Korean) requirements; Korea e-standby; Microsoft WHQL Certification; NOM (Mexico); PSB for Singapore; RCM; RoHS; SEPA; Taiwan BSMI; TCO Certified; TCO Certified Edge; TÜV Bauart; VCCI; Vietnam MEPS; ISC; Low blue light; EUP Lot-26; EU RoHS; Ukraine Energy label; California Energy Commission (CEC); South Africa Energy; Mexico Energy; WW application; Ukraine certificates; NRCS of South Africa; TÜV Flicker free certified; India BIS
Physical security	Security lock-ready ^[9]
Management Software	HP Display Center; HP Display Manager
UPC number	196548135509
What's in the box	Monitor; Warranty card; Quick Setup Poster; Doc-kit; 1 USB Type-C® to Type-C cable; AC power cord ^[8]

Top Recommended Displays, Accessories and Services

Personal Systems Commercial Care Pack Services

HP 4y Next Business Day Response Advanced Exchange Large DisplayHardware Support	U0J12E
HP 5y Next Business Day Response Advanced Exchange Large DisplayHardware Support	U0J13E

Messaging Footnotes

- [1] All performance specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.
- [2] Host PC requires Windows 10 or higher. HP Display Center is available on the Microsoft store.
- [3] HP Display Manager software agent must be running on a web server and host PC. Some limitations may apply to legacy monitors.
- [4] Based on US EPEAT® registration according to IEEE 1680.1-2018 EPEAT®. EPEAT® status varies by country. Visit www.epeat.net for more information.

Technical Specifications Footnotes

- [1] All specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.
- [2] DisplayPort™ 1.2 or HDMI 1.4 required to drive panel at its native resolution. The video card of the connected PC must be capable of supporting 1920 x 1080 at 75 Hz with 8-bit color using one DisplayPort™, HDMI. The video card of the connected PC must be capable of supporting 1920 x 1080 and include one DisplayPort™ or one HDMI outputs to drive the monitor at the Preferred Mode.
- [8] Included cables may vary by country.
- [9] Lock sold separately.

Learn more at
hp.com

© Copyright 2022 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

EPEAT® is a registered trademark of Green Electronics Council. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. ENERGY STAR® is a registered mark owned by the U.S. government.

