





SPECIFICATIONS

Display Size:	31.5" Curved Monitor
Aspect Ratio:	16:9
Panel Type:	VA
Flat/Curved:	Curved (R1500)
Brightness (Typical):	250 nits
Factory Reset Brightness:	200 nits
Contrast Ratio:	3000:1
Resolution (HxV):	1920 x 1080
Refresh Rate (FPS):	165Hz (DP) 144Hz(HDMI)
Respond Time:	OD1:7ms OD2:5ms /MPRT 1ms
Viewing Angel (HxV):	H/V 178/178
Display Colors:	16.7M Colors

Color Gamut:	DCI-P3 90%
Ports:	1 x HDMI Port 1 x Displayport 1 x Audio Jack 3.5mm
Input Voltage:	AC 110~240V, 50/60Hz
Consumption:	On: 48W; Off: <=0.3W Standby<=0.5W
Output Voltage/Current:	19V/2.5A
Tilt Angle:	-5°~ 20°±2°
High Adjustable Arm (mm):	110±5mm
Kensington Lock:	Yes
VESA Mountable (mm):	75mm x 75mm
Power Adapter Standard:	DC 19V/2.5A



HDMI Port



Aspect Ratio



3000:1