



## SPECIFICATIONS

Display Size:	21.45" TFT(478.66mm*260.28mm)	Energy:	DC 12V 2.5A
Resolution:	1920*1080 Pixels @75Hz	Consumption:	<25W
Pixel Pitch:	0.241(H) x 0.241(V) mm	Multi-Language:	English, Spanish, French, Portuguese, Dutch German, Italian, Simplified Chinese, Korean Traditional Chinese, Japanese, Russian
Frequency:	30-80KHz	VESA Mountable:	100x100mm
Display Colors:	16.7M Colors (Typical)	Product Dimension (With Stand, W*H*D):	491.7x372.2x167.4mm
Brightness:	250cd/m2 (Typical)	Net Weight (Without Adapter)	2.3 lbs
Contrast Ratio:	3000:1 (Typical) 80,000,000:1 (Active Contrast)	Power Cable:	Included (1.5m)
Response Time:	6.5ms (Typical)	VGA Cable:	Included (1.5m)
VGA:	Yes, 15pin		
HMDI:	Yes		



VGA Cable  
Included



HDMI Port



Aspect Ratio



3000:1