




SPECIFICATIONS

Display Size:	23.8" TFT (527.04*296.46 mm)	Power Type:	DC 12V 2.5A
Resolution:	1920*1080 Pixels @75Hz	Consumption:	<25W
Pixel Pitch:	0.274(H) x 0.274(V) mm	Multi- Language:	English, French, German, Italian, Simplified Chinese, Traditional Chinese, Korean, Japanese, Espanola, Portuguese, Russian
Frequency:	30-80KHz	VESA Mountable:	100*100mm
Display Colors:	16.7M Colors (Typical)	Product Dimension:	538.4*408.2*189.4mm
Brightness:	250cd/m2	Net Weight (Without Adaptor):	2.8 Kg
Contrast Ratio:	4000:1 (Typical)	Accessories:	1 x Power Cable
	80,000,000:1 (Active Contrast)		1 x VGA Cable
Response Time:	6.5ms (Typical)		
Interface:	VGA, HDMI		



VGA Cable
Included



VGA Port



Aspect Ratio



4000:1